



CHATSWORTH
PRODUCTS

EasySwing Wall-Mount Rack



Store and secure network, communications and security equipment within a secure telecommunications or equipment room. Networking equipment, security equipment, switches, routers, telephone/voicemail, patch panels or other interconnect equipment.

- Available in three heights and four depths
- Ships flat and partially-assembled, simply unfold, secure corners, install

KEY FEATURES

- Swing-out rack-mount frame provides easy access to the rear of installed equipment.
- Fiber and copper ready with 19" EIA threaded equipment mounting rails.
- Easy to ship, inventory and install – ships flat, folds open to mount on the wall.
- Integrated cable management straps included.
- Swing gate can open to the right or to the left.
- Durable, all-steel construction.

SPECIFICATIONS

Description	<ul style="list-style-type: none"> • Open wall-mount rack with swing-out rear access to equipment • For indoor use only, in environmentally controlled areas; may not be used outdoors, in industrial or harsh environments, or in plenum-spaces • Swing gate is hinged on one side only, wall-mount frame may be installed so that the gate will open to the right or left • Includes locking latch pin to secure the gate in the closed position
Dimensions	<ul style="list-style-type: none"> • Available in three heights: <ul style="list-style-type: none"> - 11U (24.5 / 622 mm) - 19U (38.5 / 978 mm) - 26U (51.5 / 1308 mm) • Available in four depths <ul style="list-style-type: none"> - 6.5 (165 mm) - 10.5 (266 mm) - 16.5 (429 mm) - 23.5 (596 mm)
Equipment Support	<ul style="list-style-type: none"> • 1 pair L-shaped equipment mounting rails <ul style="list-style-type: none"> - 19"W, EIA-310-D compliant - Universal hole pattern, 5/8"-5/8"-1/2" (15.9 mm -15.9 mm - 12.7 mm) vertical hole spacing - Roll-formed #12-24 equipment mounting holes - Includes 12 each #12-24 black equipment mounting screws
Load Capacity	85 lb (38.6 kg) of equipment, open or closed
Certifications	EIA-310-D compliant
Material	<ul style="list-style-type: none"> • Rack: sheet and tubular steel <ul style="list-style-type: none"> - Welded and bolted, ships partially-assembled - Epoxy-polyester hybrid powder coat paint - Available in black, gray, or glacier white

Availability: US, Canada, Latin America, Europe, Middle East & Africa

United States & Canada
Simi Valley, CA
800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com
techsupport@chatsworth.com

Latin America
Mexico City, Mexico
+52-55-5203-7525
Toll Free within Mexico
800-201-7592
chatsworth.com.co

Europe
Buckinghamshire
England, UK
+44-1628-524-834

Middle East & Africa
Dubai, UAE
+971-4-2602125
Doha, Qatar
+974-4-267422

Asia Pacific
Jing'an District,
Shanghai, China
+86 21 6880-0266
chatsworth.com.cn

EasySwing Wall-Mount Racks are a family of open wall-mounted 19" EIA swing gate racks available in three heights and four depths. EasySwing Wall-Mount Racks are copper and fiber ready, are easy to install, and provide easy access to the front and rear of equipment. Use EasySwing Wall-Mount Racks to store network, communications and security equipment in telecommunication and equipment rooms or in other rooms where floor space is limited.

EasySwing Wall-Mount Rack ships flat and partially assembled. Assembly is easy — unfold the rack and install one assembly bolt per corner. The frame is punched with keyhole mounting slots located on 18.5" (470 mm) centers. Attach the rack to the wall with 1/4" installation hardware (order separately). EasySwing can swing open to the right or left, simply flip the rack over before securing it to the wall.

EasySwing Wall-Mount Rack supports 19" EIA rack-mount equipment and single-sided shelves. Equipment mounts on a hinged gate. The gate has single-sided rack-mount rails with roll-formed #12-24 threads for attaching equipment. The gate swings open to provide easy access to the rear of equipment during service work. The gate is secured in the closed position with a removable pin that latches through the wall-mount frame. EasySwing Wall-Mount Rack will support 85 lb (38.6 kg) of equipment. Premise cables are guided from the wall to the swing gate with included reusable cable management straps. The straps attach to slots in the frame and support cables as the gate opens and closes. Add other CPI accessories to customize your installation.

Contact CPI for configuration assistance.

ORDERING INFORMATION

Part Number	Usable Dimensions			Overall Dimensions			Shipping Weight lb (kg)
	Height	Width	Depth	Height	Width	Depth	
13602-X08	11U	19" EIA	6.5 (165)	24.5 (622)	20.3 (516)	8.0 (204)	22 (10.0)
13602-X12	11U	19" EIA	10.5 (266)	24.5 (622)	20.3 (516)	12.0 (305)	24 (10.9)
13602-X18	11U	19" EIA	16.5 (419)	24.5 (622)	20.3 (516)	18.0 (457)	28 (12.7)
13602-X25	11U	19" EIA	23.5 (596)	24.5 (622)	20.3 (516)	25.0 (635)	34 (15.4)
13604-X08	19U	19" EIA	6.5 (165)	38.5 (978)	20.3 (516)	8.0 (204)	27 (12.2)
13604-X12	19U	19" EIA	10.5 (266)	38.5 (978)	20.3 (516)	12.0 (305)	29 (13.2)
13604-X18	19U	19" EIA	16.5 (419)	38.5 (978)	20.3 (516)	18.0 (457)	33 (15.0)
13604-X25	19U	19" EIA	23.5 (596)	38.5 (978)	20.3 (516)	25.0 (635)	38 (17.2)
13608-X12	26U	19" EIA	10.5 (266)	51.5 (1308)	20.3 (516)	12.0 (305)	33 (15.0)
13608-X18	26U	19" EIA	16.5 (419)	51.5 (1308)	20.3 (516)	18.0 (457)	37 (16.8)

X=Color: 1=Gray, 7=Black, E=Glacier White. Note: Usable Depth is reduced at the top and bottom 2U on -X08 and -X12 models and at the top and bottom 3U on -X18 and -X25 models. For planning purposes, reduce Useable Depth by 75% and 50% on the top and bottom 2U of -X08 and -X12 racks. Reduce Usable Depth by 80%, 50% and 25% on the top and bottom 3U of -X18 and -X25 racks. Order 1/4" installation hardware separately.


Accessories		
Part Number	Description	Shipping Weight lb (kg)
40605-001	Mounting Screws; #12-24 x 1/2"L, Zinc, Pack of 50	1 (0.5)
40605-005	Mounting Screws; #12-24 x 1/2"L, Black, Pack of 50	1 (0.5)
02007-004	Installation Hardware; 1/4-10 x 2"L, Hex Lag Screw	1 (0.5)
30139-719	Universal Horizontal Cable Manager 1U x 19"W x 4.96"D (126 mm),Black	2 (0.9)

chatsworth.com

techsupport@chatsworth.com

800-834-4969

DIMENSIONS



While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.

©2023 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, Clik-Nut, CPI, CPI Passive Cooling, CUBE-iT, Secure Array, eConnect, Evolution, GlobalFrame, MegaFrame, QuadraRack, RMR, Saf-T-Grip, SeismicFrame, SlimFrame, TeraFrame, Motive, EuroFrame, Oberon, Velocity and ZetaFrame are federally registered trademarks of Chatsworth Products. H-Plane, Hi-Bar, In-Plane, M-Frame, NetPoint, Simply Efficient, Skybar, and Wi-Tile and are trademarks of Chatsworth Products. All other trademarks belong to their respective companies. 03/24 MKFCPI-304