

CCS - EFX COMBINATION CABLING SECTION EXTENDED FINGERS

KEY FEATURES


- Cable openings on the front of CCS - EFX align with RMU spaces on the rack allowing cables to exit by-RMU.
- Cable openings on the front of CCS - EFX are sized to accommodate 48 patch cords, twice the capacity of the standard CCS. Openings have rounded edges to protect cable and will not deform or break.
- The front door hinges open to the right or left for easy access to cables during MACs and locks in the closed position to protect cables from damage.
- Open rear of CCS - EFX allows large premise cable bundles to exit the manager into the rack-mount space.

APPLICATIONS

- Use CCS - EFX Combination Cabling Section - Extended Fingers Xtra Large Capacity in small to medium size facilities in Telecommunications Rooms (TR) and Equipment Rooms (ER) to support the Main Cross-Connect (MC), Intermediate Cross-Connect (IC) or Horizontal Cross-Connect (HC) and voice and network switching equipment.
- CCS - EFX is an excellent choice for managing cables from angled-face copper patch panels.

RELATED ACCESSORIES

- Standard Rack/Universal Rack
- Combination Cabling Sections
- Universal Horizontal Cable Managers
- Double-Sided Universal Horizontal Cable Managers
- Cable Distribution Spools
- Cable Runway Radius Drops
- Saf-T-Grip® Reusable Cable Management Straps



The CCS - EFX Combination Cabling Section - Extended Finger Xtra Capacity is a double-sided vertical cable management trough designed for use with CPI's Universal and Standard Racks to manage cable at the cross-connect, especially when using angled-face copper patch panels.

The front side of CCS - EFX features a patented system of large cable openings that align with each rack-mount space on the rack providing by-RMU control of patch cords. The T-shaped "fingers" extend 2-1/2" further than those used on the standard CCS providing support for patch cords as they sweep to connect with angled face patch panels. The additional depth creates a larger cable fill area. The larger cable openings allowing more patch cords to exit per RMU when racks support network switches. CCS - EFX includes a hinged front door that opens to the right or left to provide easy access to cable. The door locks in the closed position to protect cables and provide a clean, finished look.

The rear side of CCS - EFX is an open trough design with regularly spaced spin-latch closures. All edges are protected to prevent cable nicks. This design allows larger premise cable bundles to exit the trough into the rack-mount space.

The CCS - EFX is manufactured from a combination of strong, lightweight aluminum sheet and plenum-rated composite materials for maximum strength at minimal weight. CCS - EFX is packaged in a single carton for easy handling and includes installation hardware.

See reverse for product selection. Contact CPI Technical Support for configuration assistance.

SPECIFICATIONS

- Double-sided trough
- 1 RMU high cable openings (front)
- Locking hinged door (front)
- Spin open latches (rear)
- Available in three widths

• **Cable capacities:**
See the cable fill table at www.chatsworth.com/cablefill


• **Footprints:**
6.00"W x 14.94"D
10.00"W x 14.94"D
12.00"W x 14.94"D

• **Height:**
7' (84")
7'-6" (90")
8' (96")

• **Materials:**
5052-H32 aluminum sheet
UL 94V-0 Flame Resistant composite

• **Finish:**
Black CCS-EFX Total Capacity @50% cable fill without cable spools

DIMENSIONS



Part Number			Width	
7'H (84")	7'-6"H (90")	8'H (96")	A	B
40098-703	40098-705	40098-715	6.00	26.31
40099-703	40099-705	40099-715	10.00	30.31
40100-703	40100-705	40100-715	12.00	32.31

ORDERING INFORMATION

CCS-Extended Fingers					
Part Number	Description			Color	Shipping Weight
	Width	Depth	Height		
40098-703	6"	14.94"	7'	Black	38 lb
40099-703	10"	14.94"	7'	Black	52 lb
40100-703	12"	14.94"	7'	Black	56 lb
40098-705	6"	14.94"	7'-6"	Black	41 lb
40099-705	10"	14.94"	7'-6"	Black	56 lb
40100-705	12"	14.94"	7'-6"	Black	60 lb
40098-715	6"	14.94"	8'	Black	44 lb
40099-715	10"	14.94"	8'	Black	60 lb
40100-715	12"	14.94"	8'	Black	64 lb

