

# Product Information Sheet

## PATCH PANEL ENCLOSURES FOR 8" D (200 mm) RAISED ACCESS FLOORS



### TELECOMMUNICATION ENCLOSURES

The Patch Panel Enclosure for 8" D (200 mm) raised access floors are a 7" D (180 mm) consolidation point enclosure suitable for use in air handling spaces under 8" D (200 mm) raised access floors. The enclosure may be supported from the raised floor pedestals with included brackets and uses the 2' x 2' raised access floor tile as a lid.

Each enclosure has four edge-protected cable access ports that include fire rated foam sealing kits. Two styles are available with standard or large cable access ports. Equipment is supported on facing pairs of 19" W x 4 RMU high mounting rails (8 RMU total) that pivot to provide easy access to the front and rear of equipment. Cable tie points are included within the enclosure. Use Saf-T-Grip® Cable Management Straps to secure cables.

#### ■ Cable Entry/Exit

- A0822-RF Enclosures have (4) 6-3/4" W x 2" H (171 mm x 50 mm) edge-protected cable access ports
- 13772-001 Enclosures have (2) 14-3/4" W x 3-1/4" H (374 mm x 82 mm) and (2) 6-1/4" W x 7" H (158 mm x 180 mm) edge-protected cable access ports. Ideal for Cat 6a UTP Cable
- Includes approved fire-rated foam sealing kit

#### ■ Equipment Support

- 8U divided 4U+4U for 19" patch panels
- Mounting rails pivot to provide easy to access to the rear of equipment

#### ■ Materials

- Enclosure: .060" thick (1.52 mm) sheet aluminum, riveted construction
- Foam Sealing Kit: Polychloroprene latex compound
- Support Brackets: steel

#### ■ Packaging

- 1 Enclosure/Carton

#### ■ Approvals

- UL Listed - Communications Circuit Accessory
- UL File Number/E185147 (UL 1863; UL 50; UL 2043)



Part Number	Description	Shipping Weight
A0822-RF	4U + 4U Enclosure for 8" D (200 mm) Floor	23 lb (10.4 kg)
13772-001	4U + 4U Enclosure with Large Cable Access Ports for 8" D (200 mm) Floor	25 lb (11.3 kg)

#### ■ Specifications

- Enclosure: 25 1/2" W x 25 1/2" L x 7 1/2" D (648 mm x 648 mm x 190 mm)

#### ■ Installation

- Includes support brackets for 1-1/2" (38.1 mm) rectangular or round raised floor pedestals
- Use #12-24 equipment mounting screws to attach patch panels (P/N 40605-001), sold separately.
- Use Saf-T-Grip Cable Management Straps to manage cables (P/N 02006-201), sold separately.

800-834-4969 in U.S. & Canada • [www.chatsworth.com](http://www.chatsworth.com)



CHATSWORTH PRODUCTS, INC.

©2009 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, Saf-T-Grip, Seismic Frame, SlimFrame and MegaFrame are federally registered trademarks of Chatsworth Products, Inc. Cube-iT Plus, Evolution, OnTrac, QuadraRack, Simply Efficient and TeraFrame are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. Rev.2 03/09