



Featured Product


The Velocity® Standard Pack

- One part number
- One package
- One complete solution


Combining CPI's
Velocity® Cable Management
plus
Standard Rack and Installation hardware
in one convenient package.



Standard Rack
Rack-mount units
marked and numbered



Velocity Cable Management
Snaps together for
quick assembly



57011-703 Shown

Standard Rack with Velocity Single-Sided
Cable Management



CHATSWORTH PRODUCTS

+1-800-834-4969
www.chatsworth.com

Save time with the Velocity Standard Pack, combining CPI's industry leading Standard Rack with the easy-to-use, cost-effective, Velocity Cable Management.

- Easy ordering and handling – the rack, cable manager and installation hardware are conveniently packaged in a single compact carton and are ordered using a single part number.
- Quick assembly – it takes just a few minutes to unpack and assemble the rack and Velocity cable manager.
- Stay aligned – openings between the patented cable guide fingers on the cable manager align with each rack-mount unit on the rack, which are marked and numbered to speed equipment installation.
- Hide and secure cables – a sturdy, snap-on, hinged cover is included with each cabling section resulting in a closed, finished appearance.
- Customize your installation – choose between 3.6"W (91 mm) or 6"W (152 mm) single or double-sided Velocity cable managers and easily expand by adding additional accessories.

Part Number	Description	Shipping Weight lb (kg)
57011-703	(1) Standard Grounded Rack, 45U x 19"EIA, UL® Listed, Black (1) Velocity Single-Sided Vertical Cable Manager, 3.6"W (91 mm), Black (1) Rack Installation Kit for Concrete Floor, 1/2" Hardware, Zinc	47 (21.3)
57012-703	(1) Standard Grounded Rack, 45U x 19"EIA, UL® Listed, Black (1) Velocity Double-Sided Vertical Cable Manager, 3.6"W (91 mm), Black (1) Rack Installation Kit for Concrete Floor, 1/2" Hardware, Zinc	60 (27.2)
57013-703	(1) Standard Grounded Rack, 45U x 19"EIA, UL® Listed, Black (1) Velocity Single-Sided Vertical Cable Manager, 6"W (152 mm), Black (1) Rack Installation Kit for Concrete Floor, 1/2" Hardware, Zinc	50 (22.7)
57014-703	(1) Standard Grounded Rack, 45U x 19"EIA, UL® Listed, Black (1) Velocity Double-Sided Vertical Cable Manager, 6"W (152 mm), Black (1) Rack Installation Kit for Concrete Floor, 1/2" Hardware, Zinc	68 (30.8)
Part Number	Optional Accessory Description H x W x D - in (mm)	Shipping Weight lb (kg)
13930-701	Velocity Horizontal Cable Manager, 1U x 19"EIA x 5.9 (150), Black	2 (0.9)
13930-702	Velocity Horizontal Cable Manager, 2U x 19"EIA x 5.9 (150), Black	3 (1.4)
13930-703	Velocity Horizontal Cable Manager, 3U x 19"EIA x 5.9 (150), Black	3 (1.4)
13901-703	Velocity Single-Sided Vertical Cable Manager, 80.5 x 3.6 x 9.7 (2045 x 91 x 246), Black	18 (8.2)
13902-703	Velocity Single-Sided Vertical Cable Manager, 80.5 x 6 x 9.8 (2045 x 152 x 249), Black	20 (9.1)
13904-703	Velocity Single-Sided Vertical Cable Manager, 80.5 x 10 x 10.3 (2045 x 254 x 262), Black	32 (14.5)
13905-703	Velocity Single-Sided Vertical Cable Manager, 80.5 x 12 x 10.4 (2045 x 91 x 246), Black	34 (15.4)
13911-703	Velocity Double-Sided Vertical Cable Manager, 80.5 x 3.6 x 16.4 (2045 x 91 x 417), Black	25 (11.3)
13912-703	Velocity Double-Sided Vertical Cable Manager, 80.5 x 6 x 16.6 (2045 x 152 x 422), Black	28 (12.7)
13914-703	Velocity Double-Sided Vertical Cable Manager, 80.5 x 10 x 17.5 (2045 x 254 x 445), Black	40 (18.1)
13915-703	Velocity Double-Sided Vertical Cable Manager, 80.5 x 12 x 17.8 (2045 x 305 x 446), Black	43 (19.5)
13935-701	Cable Spool Kit, Pack of 4, Black	2 (0.9)
13928-001	Cable Lashing Bar, Zinc	2 (0.9)



57012-703 Shown
Standard Rack with Velocity Double-Sided Cable Management



Velocity Cable Management
Rounded edges protect cables



Easy Installation
Attaches easily to the rack

For more information about CPI Cable Management Products, visit www.chatsworth.com/cablemanagement,

call **+1-800-834-4969**

or email techsupport@chatsworth.com



CHATSWORTH PRODUCTS