

Product Cut Sheet

Top Mounted Fan For Single Rack Enclosure

10" (250 mm) Axial Fan & Cover Kit


Axial fan draws heated internal air to the top of the enclosure and exhausts it to the outside. Fan and cover kit installs quickly and easily using four screws. Pre-installed sponge tape seals cover to enclosure. Fan includes an attached 12'L (3.6 m) power cord with a NEMA 5-15P (115 VAC) or a NEMA 6-15P (230 VAC) plug.

Louver Shut-Off Panel

To achieve the most effective cooling when using the Axial Fan & Cover Kit, seal the top louvers on the enclosure with the Louver Shut-Off Panels.

Enclosure Bottom Panel

When rack rollers are used on a single rack installed inside an enclosure, the rack rollers lift the enclosure slightly off the ground, permitting unfiltered air into the enclosure.



Enclosure Bottom Panel shown installed between rack roller and rack

Part Number	Description	Shipping Weight
10" (250 mm) Axial Fan & Cover Kit		
12220-X19	For 19" Rack Enclosure, 28.5"W x 30"D (724 mm x 760 mm), 550 CFM, 115 VAC, 0.88 Amp, 50/60 Hz, NEMA 5-15P Plug	17 lb (7.7 kg)
12220-X23	For 23" Rack Enclosure, 32.5"W x 30"D (826 mm x 760 mm), 550 CFM, 115 VAC, 0.88 Amp, 50/60 Hz, NEMA 5-15P Plug	19 lb (8.6 kg)
Louver Shut-Off Panel		
12219-X01	Shut-Off Panel	1 lb (0.5 kg)
Enclosure Bottom Panel		
12297-X19	For 19" Rack Enclosure, 28.5"W x 30"D (724 mm x 760 mm)	9 lb (4.1 kg)
12297-X23	For 23" Rack Enclosure, 32.5"W x 30"D (826 mm x 760 mm)	10 lb (4.5 kg)

X=Color: 2=White, 7=Black

800-834-4969 in U.S. & Canada • www.chatsworth.com