



| Technical Specs:          |                                    |
|---------------------------|------------------------------------|
| Input Ratings             |                                    |
| Nominal Voltage (VAC)     | 110-125VAC, Single Phase, 50/60 Hz |
| Input Plug / Cord         | NEMA L5-30, 10 ft (3m)             |
| Current Rating            | 30A                                |
| Power Rating (kW)         | 1.9                                |
| Output Ratings            |                                    |
| Nominal Voltage (VAC)     | 110-125VAC, 50/60 Hz               |
| Current Rating            | 24A Total                          |
| Outlet Rating             | 5-20R: 16A max                     |
| Max Current per Breaker   | 16A Max                            |
| Outlet Combination        |                                    |
| Load Segment              | CB1,CB2: (12) 5-20R                |
| PDU Total                 | (24) 5-20R                         |
| Branch Circuit Protection | (2) 2-pole 20A UL489 Breaker       |
| Surge Suppression         | None                               |

| Features:           |  |
|---------------------|--|
| Local Display       | (1) LCD Display - Branch Monitoring, IP Setup, Alarm Notification  |
| Branch Monitoring   | Current, Voltage, Power, PF per Circuit                            |
| Outlet Monitoring   | Current, Voltage, Power, PF per Outlet                             |
| Monitoring Accuracy | +/- 1% True RMS  |
| Ethernet Port       | 10/100/1000 Mbps RJ-45   |
| Remote Monitoring   | IP v4/v6, SNMP v1/v2/v3, Serial                                    |
| IP Consolidation    | Link up to 32 PDUs under a single IP address                       |
| USB Ports (2)       | Update firmware  |
| Control Interface   | Built-in Web Browser, HTTP, SNMP, Serial RS-232                    |
| Sensor Interface    | (2) Temperature and Humidity Sensors                               |
| Auxiliary Ports (2) | Front and Rear Electric Door Locks                                 |
| Cord Retention      | Tethers included (see detail)                                      |
| Mounting System     | Multiple tool-less mounting button locations, A and B (see detail) |

| Dimensions & Weights: |             |
|-----------------------|-------------|
| Width (In[mm])        | 2.2 [55]    |
| Height (In[mm])       | 70.5 [1791] |
| Depth (In[mm])        | 2.2 [55]    |
| Weight (lbs[kg])      | 18 [8.2]    |

| Regulatory Information:   |  |
|---|--|
| UL & cUL Listed, IEC 60950-1, CSA C22.2, CE, NOM, RoHS, FCC Part 15 Class A, EN 55022 |  |

| Environmental Conditions: |                        |
|---------------------------|------------------------|
| Operating Temperature     | 32 - 149F (0 - 65C)    |
| Operating Rel Humidity    | 5 - 95%                |
| Operating Elevation       | 0-10000 ft (0-3000 m)  |
| Storage Temperature       | -13 - 149F (-25 - 65C) |
| Storage Rel Humidity      | 5 - 95%                |
| Storage Elevation         | 0-50000ft (0-15000 m)  |

| Hardware Included:   |  |
|--|--|
| Cord retention tethers<br>(2) tool less mounting buttons<br>(1) ground kit cable |  |
| Optional Accessories:  |  |
| Temp/Hum Environmental Sensor<br>P/N 35941-132                                   |  |

- Notes:
- All Dimension are in inches [millimeters] unless otherwise specified
  - Installation must conform with all related national and local codes
  - All Bracket kits are sold separately. Toolless mounting buttons are included for installation in CPI cabinets.
  - For more information, please contact Tech Support at [techsupport@chatsworth.com](mailto:techsupport@chatsworth.com)

©2017 Chatsworth Products, Inc. All rights reserved.

All products quoted are subject to availability based on manufacturing capacity and shipping dates should be considered estimates only.

While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.



eConnect Vertical (0U) PDU, Monitored Pro, L5-30 Plug, Single Phase, 110-125V Input, 30A, (24) 5-20R Outlets, 110-125V Output, Individual Outlet Monitoring