

Product Cut Sheet

STANDARD FAN DOORS

Standard Fan Doors using single-speed fans for M-Series MegaFrame Cabinet System.

- **Door Heights:**
7' (84"), 6'-6" (78"), 6' (72"), 4' (48")
4' high model includes 4 fans
All other models include 8 fans
- **Power Connection(s):**
15' long, grounded power cord
115 VAC straight plug (NEMA 5-15P)
Single connection for 4' high door
Two connections for all other doors
- **Materials:**
Aluminum extrusion frame, aluminum sheet panel
Fan assembly-metal housing, individual fans are plastic
- **Finish:**
Anodized frame, door panel painted black, computer white or gray
Fan assembly-black only
- **Per Fan Power Requirement:**
115 VAC, .19 Amp at 60 Hz
(2) detachable power cords with IEC C-13 to NEMA 5-15P plugs
- **Per Fan Power Consumption:**
13.4 Watts
- **Per Fan Air Flow:**
100 CFM (800 CFM total)
- **Per Fan Noise Level:**
42 dB (1 meter max)



Standard Fan Doors					
Part Number	Description	# of Fans	Power Cords	Air Flow (Max)	Shipping Weight
For M-Series MegaFrame Cabinet System					
13222-X10	19"W x 7'H	8	2	800 CFM	56 lb
13222-X11	19"W x 6'6"H	8	2	800 CFM	55 lb
13222-X12	19"W x 6'H	8	2	800 CFM	56 lb
13222-X15	19"W x 4'H	4	1	400 CFM	52 lb
13222-X20	23"W x 7'H	8	2	800 CFM	58 lb
13222-X21	23"W x 6'6"H	8	2	800 CFM	57 lb
13222-X22	23"W x 6'H	8	2	800 CFM	56 lb
13222-X25	23"W x 4'H	4	1	400 CFM	48 lb

Notes: X=Color: 1=Gray, 2=White, 7=Black. Doors reduce usable depth in cabinet by 1.5". MegaFrame and SlimFrame versions available with CPI Electronic Locking Systems and as double door. Contact CPI to pre-configure doors on new cabinets.

800-834-4969 in U.S. & Canada • www.chatsworth.com

US & Canada

+1-800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com

Latin America

+52-55-5203-7525
Toll Free within Mexico
01-800-01-7592
chatsworth.com.co

Europe

+44-1628-524-834
chatsworthproducts.co.uk

Middle East & Africa

Dubai, UAE
+971-4-2602125
chatsworthproducts.co.uk

Asia Pacific

+86 21 6880-0266
chatsworth.com.cn

techsupport@chatsworth.com



CHATSWORTH
PRODUCTS