

Product Information Sheet

CABINET SERVICE PARTS FOR THE T-SERIES STEELFRAME CABINETS

T-Series SteelFrame Cabinet Service Parts include doors, side panels and top panels that are used to enclose a frame-only configuration, to change a cabinet configuration to meet new equipment airflow or security requirements or to replace items that have been damaged.

Replacement doors are available in several styles including solid metal, smoked plexiglass and perforated (mesh) doors with a 63% open area to provide airflow for equipment. Single doors and double (split) doors are available. Double doors are a good choice for narrow aisles due to reduced clearance requirements. Doors are easy to remove and can be mounted on the front or rear of the cabinet to open from the left or right. Doors were upgraded in May 2009 to include a swing handle latch with a keyed lock. Doors with push-button locks, standard on T-Series SteelFrame Cabinets manufactured before May 2009, are also available.

Side panels are available in two styles: solid side panels and Therma-Stop Brush Side Panels with front and rear vertical brush-sealed cable openings. T-Series SteelFrame Cabinets can be bayed with one side panel in between cabinets. Use a Therma Stop Brush Side Panel in between bayed cabinets to block airflow between cabinets, but allow internal cabinet-to-cabinet cabling. Both styles of side panel have a keyed lock that matches the doors.

The top panels on T-Series Cabinets cannot be removed, but the top panel service part can be added to the T-Series Frame Only to enclose the frame. The top panel has six cable access ports and a vented area for an optional Fan Kit (P/N 12724-70X).

T-Series SteelFrame Cabinet Service Parts are made from steel. Select service part size and color to match the cabinet. Contact CPI Technical Support for configuration assistance.

Cabinet Doors

Select the door to match the width, height and color of the cabinet. When replacing a damaged door match door and latch style to the existing door.

Traditional Doors with Push Button Latches for T-Series SteelFrame Cabinets Manufactured Prior to May 2009	
12684	Single High-Flow Perforated Metal Door
12710	Single Solid Metal Door
12709	Single Solid Plexiglass Door
12732	Single Vented Plexiglass Door

Color	
1	Gray
2	Computer White
7	Black

Size	
10	24"W x 84"H (610 mm x 2130 mm) For T1 x 45 RMU Cabinets
11	24"W x 78"H (610 mm x 1980 mm) For T1 x 42 RMU Cabinets
20	27.3"W x 84"H (693 mm x 2130 mm) For T2 x 45 RMU Cabinets
21	27.3"W x 78"H (693 mm x 1980 mm) For T2 x 42 RMU Cabinets

12XXX - X XX



12709-721

Doors with Swing Handle Latches for T-Series SteelFrame Cabinets Manufactured After May 2009	
14360	Single Flat Perforated Metal Door
14362	Single Flat Solid Metal Door
14367	Single Flat Solid Plexiglass Door
14364	Single Flat Vented Plexiglass Door
14088	Single Curved Perforated Metal Door
14082	Single Curved Solid Metal Door
14086	Double Flat Solid Metal Door
14087	Double Flat Perforated Metal Door

Color	
1	Gray
2	Computer White
7	Black

Size	
01	24"W x 84"H (610 mm x 2130 mm) For T1 x 45 RMU Cabinets
02	24"W x 78"H (610 mm x 1980 mm) For T1 x 42 RMU Cabinets
03	27.3"W x 84"H (693 mm x 2130 mm) For T2 x 45 RMU Cabinets
04	27.3"W x 78"H (693 mm x 1980 mm) For T2 x 42 RMU Cabinets

14XXX - X XX



14088-704

800-834-4969 in U.S. & Canada • www.chatsworth.com

Product Information Sheet

CABINET SERVICE PARTS FOR THE T-SERIES STEELFRAME CABINETS

Door Latches

Replace a damaged door handle, latch or lock on flat or curved T-Series doors manufactured after May 2009. Door latches include a swing handle, single-point or two-point cam latch, and keyed lock.

- Use the two-point latch with double doors only; match to height of door
- Use the single-point latch with all other doors
- Match the door latch to the door style and cabinet width
- These latches cannot be used on doors that have push-button latches

Part Number	Description	Shipping Weight
14356-X01	For Single Curved Perforated or Single Curved Solid Metal Door for T1 Cabinet, Single-Point, Cam Latch, Keyed Lock	2 lb (0.9 kg)
14356-X02	For Single Flat Perforated or Single Flat Solid Metal Door for T1 or T2 Cabinet, Single-Point, Cam Latch, Keyed Lock	2 lb (0.9 kg)
14356-X03	For Single Curved Perforated or Single Curved Solid Metal Door for T2 Cabinet, Single-Point, Cam Latch, Keyed Lock	2 lb (0.9 kg)
14356-X04	For Single Flat Solid or Single Flat Vented Plexiglass Door for T1 or T2 Cabinet, Single-Point, Cam Latch, Keyed Lock	2 lb (0.9 kg)
14370-X00	For Double Flat Perforated or Double Flat Solid Metal Doors for T1 or T2 Cabinets, 84"H (2130 mm), Two-Point, Cam Latch, Keyed Lock, 45 RMU	4 lb (1.8 kg)
14370-X01	For Double Flat Perforated or Double Flat Solid Metal Doors for T1 or T2 Cabinets, 78"H (1980 mm), Two-Point, Cam Latch, Keyed Lock, 42 RMU	4 lb (1.8 kg)

X=color of mounting bracket: 1=Gray, 2=White, 7=Black Swing handle is black Double doors must use a two-point latch.

Rear Door Sealing Kit

Use to seal the space between the door and the cabinet to prevent hot exhaust air from escaping.

- Includes 215"L (5460 mm) adhesive backed gasket seal

Part Number	Description	Shipping Weight
14375-000	Rear Door Sealing Kit	2 lb (0.9 kg)

Color is black.

Therma-Stop Brush Side Panel

Use in between cabinets or a cabinet and External Cable Manager for T-Series SteelFrame Cabinet to block airflow between cabinets, but allow cables to pass cabinet-to-cabinet.

- Front and rear vertical brush-sealed openings for cables
- Select the side panel to match the height, depth and color of the cabinet
- Available for 84" (2130 mm) high cabinets that are 36" (910 mm) or 39" (990 mm) deep only

Part Number	Description	Shipping Weight
16143-X50	84"H (2130 mm) x 36"D (910 mm), 1 Each	63 lb (28.6 kg)
16143-X40	84"H (2130 mm) x 39"D (990 mm), 1 Each	68 lb (30.8 kg)

800-834-4969 in U.S. & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

Product Information Sheet

CABINET SERVICE PARTS FOR THE T-SERIES STEELFRAME CABINETS

Solid Side Panels

Select the side panel to match the height, depth and color of the cabinet.



Solid Side Panels	
12612	Solid Side Panel, 1 Each

Color	
1	Gray
2	Computer White
7	Black

Cabinet Depth	
6	22.6" (574 mm) Usable, 24.0" (610 mm) Outside
3	30.0" (760 mm) Usable, 31.4" (798 mm) Outside
5	36.0" (910 mm) Usable, 37.4" (950 mm) Outside
4	39.0" (990 mm) Usable, 40.4 (1026 mm) Outside
7	44.0" (1120 mm) Usable, 45.4" (1153 mm) Outside

Cabinet Height	
0	84" (2130 mm) Overall
1	78" (1980 mm) Overall


12612	-	X	X	X
-------	---	---	---	---

Top Panels (for Frame Only)

For use with the T-Series SteelFrame Frame Only style (P/Ns TXXX2-X02 or TXXX5-X02) to cover the opening on the top of the frame. This top panel is not compatible with other T-Series SteelFrame Cabinets which include top panels that cannot be removed. Select the top panel to match the width, depth and color of the frame.



12880-X17



12880-X27

Top Panel - For Frame Only	
12880	Vented with (6) Cable Ports, 1 Each

Color	
1	Gray
2	Computer White
7	Black

Cabinet Width	
1	24" (610 mm) Overall (19" Rack-Mount)
2	27.3" (693 mm) Overall (19" Rack-Mount)

Cabinet Depth	
6	22.6" (574 mm) Usable, 24.0" (610 mm) Outside
3	30.0" (760 mm) Usable, 31.4" (798 mm) Outside
5	36.0" (910 mm) Usable, 37.4" (950 mm) Outside
4	39.0" (990 mm) Usable, 40.4 (1026 mm) Outside
7	44.0" (1120 mm) Usable, 45.4" (1153 mm) Outside

12612	-	X	X	X
-------	---	---	---	---

800-834-4969 in U.S. & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

©2009 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, Saf-T-Grip, Seismic Frame, SlimFrame and MegaFrame are federally registered trademarks of Chatsworth Products, Inc. Cube-IT Plus, Evolution, OnTrac, QuadraRack, Simply Efficient and TeraFrame are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. 05/09