

Hinged Panel Mounting Bracket

Hinged Panel Mounting Bracket


Provides easy access to back of wall or rack-mounted panels.

- Can be mounted to open left or right
- Available in 2, 3, 4, 5 or 6 mounting space, 1.75"H (44.45 mm), 4" or 8"D (100 mm or 200 mm) and 19"W
- Mounting hardware not included; supports up to 30 lb (13.6 kg) load




Versatile 1.75" H rack mounting hinges provide rear access to patch panels or other shallow equipment by allowing them to swing outward. Made from high strength black composite material.


- Supports up to 30 lb per pair
- Sold in pairs with mounting hardware included











ORDERING INFORMATION

Part Number	Description- in (mm)	Shipping Weight Ib (kg)
11521-X04	3.50 (88.9), 2U High, 4 (100) Deep	2 (0.9)
11522-X04	5.25 (133.4), 3U High, 4 (100) Deep	2 (0.9)
11523-X04	7.00 (177.8), 4U High, 4 (100) Deep	2 (0.9)
11524-X04	8.75 (222.3), 5U High, 4 (100) Deep	2 (0.9)
11525-X04	10.5 (267.0), 6U High, 4 (100) Deep	2 (0.9)
11520-001	Hinges, Pair	1 (0.5)

X=color: 1=Gray, 5=Clear, 7=Black, E=Glacier White