Horizontal, Rack-Mount Power Strip

Power strips distribute single-phase power to multiple pieces of equipment from a single power connection. NEMA style outlets and plugs; includes thernal circuit breakers to protect circuits from overload.

Streamlined, durable steel body is fitted with bracket for mounting.

- 17"L (430 mm), uses 1U, Black
- For use in temperatures of 14°F-113°F (-10°C-45°C)
- Circuit breaker, six or eight outlets, non-surge or surge-protected,10' (3 m) cord
- UL Listed





ORDERING INFORMATION

Part Number	Input			Output		Dimension - in (mm)		
	Amp	kW	Plug	Breakers	Outlets	H	W	D
110-125 Volt, Single-Phase Power Strip								
12816-701	15	1.4	NEMA 5-15P	1 x 20A	(8) 5-20R	1U	19"EIA/23"	1.4 (36)
12816-702	15	1.4	NEMA L5-15P	1 x 20A	(8) 5-20R	1U	19"EIA/23"	1.4 (36)
12816-705	20	1.9	NEMA 5-20P	1 x 20A	(8) 5-20R	1U	19"EIA/23"	1.4 (36)
12816-706	20	1.9	NEMA L5-20P	1 x 20A	(8) 5-20R	1U	19"EIA/23"	1.4 (36)
110-125 Volt, Single-Phase Power Strip, Surge-Protected								
12816-703	15	1.4	NEMA 5-15P	1 x 20A	(6) 5-20R	1U	19"EIA/23"	1.4 (36)
12816-704	15	1.4	NEMA L5-15P	1 x 20A	(6) 5-20R	1U	19"EIA/23"	1.4 (36)
12816-707	20	1.9	NEMA 5-20P	1 x 20A	(6) 5-20R	1U	19"EIA/23"	1.4 (36)
12816-708	20	1.9	NEMA L5-20P	1 x 20A	(6) 5-20R	1U	19"EIA/23"	1.4 (36)

Notes: Input current is the breaker rating. The Input Amp column lists the maximum rated value of the Input Plug/inlet and circuit breaker rating. UL/NEC regulatory code requires current ratings on product labels to be derated to 80% of the maximum rated values (for example: 20 Amp = 16 Amp on UL product label). For the Input kW column, all values are derated calculations per UL for use in North America.Input kW is the listed rating. Includes 19"EH and 23" W horizontal rack-mount brackets. All power strips have IEC C20 inlets and include a power cord. Cords with locking plugs are 10"L (3 m). Cords with straight plugs are 8"2"L (2.4 m).

For product CSI Specs, visit the Support & Downloads page on <u>www.chatsworth.com</u>.

US & Canada

+1-800-834-4969 Toronto, Ontario, Canada +905-850-7770 chatsworth.com

echsupport@chatsworth.com

Latin America +52-55-5203-7525 Toll Free within Mexico 01-800-01-7592 chatsworth.com.co

Europe +44-1628-524-834 chatsworth.com

524-834 1.com

Middle East & Africa Dubai, UAE +971-4-2602125

Asia Pacific +86 21 6880-0266 chatsworth.com.cr



©2016 Chatsworth Products, Inc. All rights reserved. All trademarks belong to their respective companies. 12/17