RMR Enclosure Gland Seal

RG M63-gland seals by Roxtec, combine the traditional gland technique with unique technology for flexibility and adaptability. The result is a new generation of glands with improved capacity and functionality. RG M63 has a compact design that makes it well suited for small areas. It can seal between one to nine cables with diameters ranging from 0.138" to 1.280".

SPECIFICATIONS

Type: Roxtec Gland M63

External dimensions: Ø 2.874" x 2.047"

Packing Space* (mm): 40 x 40

Hole dimension in cabinet: Ø 2.500" - 2.520"

Material: Nickel plated brass, PA 6, galvanized mild steel, EPDM rubber

UL/NEMA 4, 4x, 12 and 13 Rating: CSA 4, 4x, 12 and 13

IP 66/67 according to IEC 60529

- Maximum thickness of cabinet wall is 0.158" with lock nut.
- Also available in stainless steel
- Recommended knockout punch: Greenlee hole punch (size 2.52"/ISO 63)



37916-001



37917-001

ORDERING INFORMATION

Part Number	Roxtec Model Frame/Modules	Cutout Size Width in (mm)	Depth in (mm)	# of Cables	Cable Diameter Range in (mm)	Shipping Weight Ib (kg)
37916-001	RG M63/4	2.5 (63) Ø	.157 (4)	4	.138650 (3.5-16.5)	4 (1.9)
37917-001	RG M63/9	2.5 (63) Ø	.157 (4)	9	.138413 (3.5-10.5)	4 (1.9)

The RG M63 frame is 2"H (51.5 mm). Refer to installation instructions for exact cutout dimensions.

For product CSI Specs, visit the Support & Downloads page on www.chatsworth.com

US & Canada +1-800-834-4969

+905-850-7770

Latin America

+52-55-5203-7525

+44-1628-524-834

Middle East & Africa

Asia Pacific +86 21 6880-0266

