
Vertical Cable Manager for ZetaFrame® Cabinet

Vertical Cable Manager

- Fully compatible with Air Dam Kit and Cable Lashing Panel
- Openings between fingers align with each U on the mounting rail
- Short or long plastic T-shaped finger options
- Rail setback:
- 7-1/4 (184 mm) for Managers with long fingers
- 4-3/4 (121 mm) for Managers with short fingers
- Long fingers pass up to (48) cables per U space through openings
- Short fingers pass up to (24) cables per U space through openings
- · Hinged cover included with managers in cabinets wider than 600 mm
- Material: aluminum panels, fingers are black, hinges/latches are blue
- Finish: Black or Glacier White; fingers are black, hinges/latches are blue
- Select part number to match cabinet usable height, width and color of the cabinet



Part Number - Cabinet Width Shipping Height Weight Ib (kg) 31.5"W (800 mm 23.6"W 27.6"W (700 mm 29.5"W (750 mm) (U) (600 mm) Vertical Cable Manager with Long Fingers N/A 38647-X11 38647-X22 38647-X33 42 9(4.1) N/A 38647-X14 38647-X25 38647-X36 45 10 (4.5) N/A 38647-X17 38647-X28 38647-X39 48 10 (4.5) N/A 38647-X21 38647-X32 38647-X43 52 10 (4.5) Vertical Cable Manager with Short Fingers 39835-X00 38646-X11 38646-X22 38646-X33 42 9 (4.1) 39835-X03 38646-X14 38646-X25 38646-X36 45 10 (4.5) 10 (4.5) 39835-X06 38646-X17 38646-X28 38646-X39 48 39835-X10 38646-X21 38646-X32 38646-X43 52 10 (4.5)

Note: X=color: 7=Black, E=Glacier White. Shipping weights are for 800 mm Cabinets.

Inside Dimensions, Usable Internal Area, Rail Setback, U Opening					
Cabinet Width	Width in (mm)	Depth in (mm)	Cable Area in² (mm²)	Rail Setback in (mm)	U Opening in² (mm²)
Vertical Cable Manager with Long Fingers					
27.6 (700)	2.2 (56)	7.5 (191)	17.0 (10 967)	10.1 (257)	6.6 (460)
29.5 (750)	3.2 (81)	7.5 (191)	24.5 (15 806)	10.1 (257)	6.6 (460)
31.5 (800)	4.2 (107)	7.5 (191)	31.9 (20 580)	10.1 (257)	6.6 (460)
Vertical Cable Manager with Short Fingers					
23.6 (600)	0.4 (10)	5 (127)	1.8 (1161)	7.6 (193)	3.5 (2260)
27.6 (700)	2.2 (56)	5 (127)	11.2 (7225)	7.6 (193)	3.5 (2260)
29.5 (750)	3.2 (81)	5 (127)	16.2 (10 451)	7.6 (193)	3.5 (2260)
31.5 (800)	4.2 (107)	5 (127)	21.2 (13 677)	7.6 (193)	3.5 (2260)

Rail setback is the minimum distance required between the front edge of the cabinet frame and the front edge of the equipment mounting rail. U opening is the size of the side opening at each U space between T-shaped fingers.

United States Agoura Hills, CA

800-834-4969 Canada

Toronto, Ontario, Canada +905-850-7770 Europe Buckinghamshire, UK +441628524834 Middle East & Africa Dubai, UAE +971-4-2602125

Doha, Qatar +974-4-267422 Latin America +52-55-5203-7525 Toll Free within Mexico 800-201-7592 chatsworth.com.co Asia Pacific +86 21 6880-0266 chatsworth.com.cr



chatsworth.com • techsupport@chatsworth.com

©2021 Chatsworth Products, Inc. All rights reserved. All trademarks belong to their respective companies. 01/2