

Intelligent Fan Kit for ThinLine II Wall-Mount Cabinet

The ThinLine II Intelligent Fan Kit uses a solid state temperature control to vary fan speed from an ultra quiet low speed at low air temperature through increasingly higher speeds as temperature rises.



13051-001 Intelligent Fan Specifications:

Minimum Fan Speed (air temp 77° or less)	Maximum Fan Speed (air temp 104° or greater)
65 CFM (Free Air)	120 CFM (Free Air)
34 dB (Noise Level)	51 dB (Noise Level)

13051-002 Intelligent Fan Specifications:

Minimum Fan Speed (air temp 77° or less)	Maximum Fan Speed (air temp 113° or greater)
36 CFM (Free Air)	49 CFM (Free Air)
28 dB (Noise Level)	33 dB (Noise Level)

ORDERING INFORMATION

Part Number	Description	Shipping Weight lb (kg)
13051-001	115 VAC, 60 Hz, 4U/6U Cabinets	2 (0.9)
13051-002	115 VAC, 60 Hz, 2U Cabinets	2 (0.9)

For product CSI Specs, visit the Support & Downloads page on www.chatsworth.com.

US & Canada

+1-800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com
techsupport@chatsworth.com

Latin America

+52-55-5203-7525
Toll Free within Mexico
01-800-01-7592
chatsworth.com.co

Europe

+44-1628-524-834
chatsworthproducts.co.uk

Middle East & Africa

Dubai, UAE
+971-4-2602125
chatsworth.ae

Asia Pacific

+86 21 6880-0266
chatsworth.com.cn



CHATSWORTH
PRODUCTS