


1442 BACKBOX






- Includes:**
- (1) Backbox
 - (1) Trim, Specific to Access Point
 - (1) Speed Link Support Wire
 - Access Point Attachment Hardware
 - (1) Fire Stop Grommet
 - (1) Conduit Adaptor
 - (1) Trim Safety Lanyard

UL Listed - File Number E348543
HCAI OPM-0110

DRAWN	RLC	9/19/2025	Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801		
CHECKED	RLC	9/19/2025	TITLE		
QA			Model 1442-XX Series Mounts		
MFG	RLC	9/19/2025	DWG NO		
APPROVED	RLC	9/19/2025	SPEC-OB1442		
TOLERANCE:		.0 = +/- .030	SIZE	C	REV
		.00 = +/- .015	SCALE		1
		.000 = +/- .005	SHEET 1 OF 6		

NOTE: All materials used in the construction of Oberon products must be RoHS compliant and meet RoHS2 Directive 2011/65/EU. Contact Oberon engineering if RoHS compliant materials are not available.






ISOMETRIC VIEW

NOTES:

- Weight: 3 lbs.
- Material: 16 Ga. Aluminum Back Box

DRAWN	9/19/2025	Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801		
CHECKED	9/19/2025	TITLE		
RLC		Model 1442-XX Series Mounts		
QA				
MFG	9/19/2025	DWG NO		
RLC		SPEC-OB1442		
APPROVED	9/19/2025	REV		
RLC		1		
TOLERANCE:	.0 = +/- .030	SIZE	C	
	.00 = +/- .015	SCALE		
	.000 = +/- .005	SHEET 2 OF 6		

ANTMNT TRIM



DETAIL B
SCALE 2 / 3

NOTES:




- Weight: 3 lbs.
- Material: 20 Ga. White Powder Coated Steel Trim

INCLUDES:

- Mounting Pattern to Accommodate Most Antennas
- Torsion Springs

DRAWN	RLC	9/19/2025	Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801		
CHECKED	RLC	9/19/2025	TITLE		
QA			Model 1442-XX Series Mounts		
MFG	RLC	9/19/2025	DWG NO		
APPROVED	RLC	9/19/2025	SPEC-OB1442		
TOLERANCE:		.0 = +/- .030	SIZE	C	REV
		.00 = +/- .015	SCALE		1
		.000 = +/- .005	SHEET 3 OF 6		

AP FACED TRIMS






- NOTES:**
- Weight: 3 lbs.
 - Material: 20 Ga. White Powder Coated Steel Trim

- INCLUDES:**
- AP Specific Bracket
 - Torsion Springs

DRAWN RLC	9/19/2025	Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801		
CHECKED RLC	9/19/2025	TITLE		
QA		Model 1442-XX Series Mounts		
MFG RLC	9/19/2025	DWG NO		
APPROVED RLC	9/19/2025	SPEC-OB1442		
TOLERANCE:		SIZE C	SCALE	REV 1
		.0 = +/- .030		
		.00 = +/- .015		
		.000 = +/- .005		
		SHEET 4 OF 6		

FXL TRIM



ISOMETRIC VIEW

- NOTES:**
- Weight: 3 lbs.
 - Material: UL 94-5VA Polycarbonate Plastic Trim

- INCLUDES:**
- T-Bar Bracket
 - Cisco Mounting Bracket
 - Torsion Springs

DRAWN RLC	9/19/2025	Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801		
CHECKED RLC	9/19/2025	TITLE		
QA		Model 1442-XX Series Mounts		
MFG RLC	9/19/2025			
APPROVED RLC	9/19/2025			
TOLERANCE:	.0 = +/- .030 .00 = +/- .015 .000 = +/- .005	SIZE C	DWG NO SPEC-OB1442	REV 1
		SCALE		SHEET 5 OF 6

CONFIGURATION TABLE

TABLE		
MODEL NUMBER	TRIM PART NUMBER	ACCESS POINT
1442-ANTMNT	37-144X-ANTMNT	For Antennas
1442-ARAP515	37-144X-ARAP515	Aruba AP515
1442-ARAP535	37-144X-ARAP535	Aruba AP535
1442-ARAP555	37-144X-ARAP555	Aruba AP555
1442-ARAP635	37-144X-ARAP635	Aruba AP635
1442-ARAP655	37-144X-ARAP655	Aruba AP655
1442-ARAP735	37-144X-ARAP635	Aruba AP735
1442-ARAP755	37-144X-ARAP655	Aruba AP755
1442-ARSTC360	37-144X-ARSTC360	Aruba C360
1442-COAP9120	37-144X-COAP9120	Cisco 9120 Series AP
1442-COAP9130	37-144X-COAP9130	Cisco 9130 Series AP
1442-COAP9136	37-144X-COAP9136	Cisco 9136 Seriea AP
1442-CW9166	37-144X-CW9166	Cisco 9164, 9166 Series AP
1442-CW9172	37-144X-CW9172	Cisco 9172
1442-CW9176	37-144X-CW9176	Cisco 9176
1442-CW9178	37-144X-CW9178	Cisco 9178
1442-FXL	37-144X-FXL	General Purpose for APs w/ Internal Antennas
1442-JNAP43	37-144X-JNAP43	Juniper AP43
1442-JNAP45	37-144X-JNAP45	Juniper AP45
1442-JNAP47	37-144X-JNAP47	Juniper AP47
1442-NT	NT	N/A (No Trim Included)

DRAWN RLC	9/19/2025	Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801		
CHECKED RLC	9/19/2025			
QA		TITLE		
MFG RLC	9/19/2025	Model 1442-XX Series Mounts		
APPROVED RLC	9/19/2025			
TOLERANCE: .0 = +/- .030 .00 = +/- .015 .000 = +/- .005		SIZE C	DWG NO SPEC-OB1442	REV 1
		SCALE	SHEET 6 OF 6	