



- Notes:
- 1 All Dimension are in inches [millimeters] unless otherwise specified
  - 2 Installation must conform with all related national and local codes
  - 3 All Bracket kits are sold separately. Toolless mounting buttons are included for installation in CPI cabinets.
  - 4 For more information, please contact Tech Support at [techsupport@chatsworth.com](mailto:techsupport@chatsworth.com)

| Technical Specs:                 |   |
|----------------------------------|---|
| <b>Input Ratings</b>             |   |
| Nominal Voltage (VAC)            | 208V 1ph  |
| Input Plug / Cord                | NEMA L6-30P   |
| Current Rating                   | 24A   |
| Power Rating (kW)                | 4.99  |
| <b>Output Ratings</b>            |   |
| Nominal Voltage (VAC)            | 208V  |
| Current Rating                   | 24A   |
| Outlet Rating                    | C13 10A max C19 16A max   |
| Max Current per Breaker          | 12A Balanced; 20A Unbalanced  |
| <b>Outlet Combination</b>        |   |
| Load Segment                     | Refer to Simplified Wire Schematic                                      |
| PDU Total                        | (8)C13, (4)C19  |
| <b>Branch Circuit Protection</b> | (2) 20A, 5kAIC, Double Pole   |
| <b>Surge Suppression</b>         | None  |
| <b>Features:</b>                 |   |
| Branch Monitoring                | Not Supported   |
| Outlet Monitoring                | Not Supported   |
| Monitoring Accuracy              | Not Supported   |
| Ethernet Port                    | Not Supported   |
| Remote Monitoring                | Not Supported   |
| Remote Control                   | Not Supported   |
| IP Consolidation                 | Not Supported   |
| USB Ports (2)                    | Not Supported   |
| Controller Module                | Not Supported   |
| Auxiliary Port (2)               | Not Supported   |
| Cord Retention                   | Locking Receptacles   |
| Mounting System                  | Pre-installed Mounting brackets   |
| <b>Dimensions &amp; Weights:</b> |   |
| Width (In[mm])                   | 17[431.8]   |
| Height (In[mm])                  | 1.72[43.69]   |
| Depth (In[mm])                   | 12[304.8]   |
| Weight (lbs[kg])                 | 18[8.2]   |
| <b>Regulatory Compliance:</b>    | NEMKO Listed to UL/IEC 62368-1, CE, RoHS, FCC Part 15 Class A, EN 55022 |
| <b>Regulatory Part Number:</b>   | K12-2D096-409-72A   |
| <b>Environmental Conditions:</b> |   |
| Operating Temperature            | 32 - 149F (0 - 65C)@ Input Pwr Rating (kW)                              |
| Operating Rel Humidity           | 5 - 95%   |
| Operating Elevation              | 0-10000 ft (0-3000 m)   |
| Storage Temperature              | -13 - 149F (-25 - 65C)  |
| Storage Rel Humidity             | 5 - 95%   |
| Storage Elevation                | 0-50000ft (0-15000m)  |
| <b>Hardware Included:</b>        | (2) Pre-installed mounting brackets<br>(1) ground kit cable             |
| <b>Warranty</b>                  | 3 yrs. Standard, 2 add'l yrs. Opt'l                                     |
| <b>Optional Accessories:</b>     | Not Supported   |

©2021 Chatsworth Products, Inc.  
All rights reserved.

All products quoted are subject to availability based on manufacturing capacity and shipping dates should be considered estimates only.

While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.



eConnect Horizontal 1U PDU, Basic,  
L6-30, 10ft (3m),  
208V Single Phase Input, 30A,  
(8) C13 (4) C19 Outlets, 208V Output



**E0-1271-X** ISS

SHEET 1 OF 1