

Fixed Wall-Mount Equipment Rack

Fixed Wall-Mount Equipment Rack

The Fixed Wall-Mount Equipment Rack is a sturdy platform for wall mounting equipment.

- U spaces are marked and numbered, tapped with #12-24 roll-formed threads
- Includes (50) #12-24 equipment mounting screws. Black painted racks ship with black screws; other racks ship with zinc screws
- Supports single-sided and double-sided shelves
- Supports 200 lb (90.7 kg) of equipment when securely mounted to wall or backboard using all eight leg mounting holes



ORDERING INFORMATION

Part Number	Height	Width	Depth	Height	Width	Depth	Shipping Weight lb (kg)
	Usable Dimensions			Overall Dimensions			
11960-X06	12U	19"	6 (150)	27.4 (696)	22.4 (569)	6.6 (168)	9 (4.1)
11960-X12	12U	19"	12 300)	27.4 (696)	22.4 (569)	12.6 (320)	12 (5.4)
11960-X18	12U	19"	18 (457)	27.4 (696))	22.4 (569)	18.6 (472)	13 (5.9)
11961-X06	20U	19"	6 (150)	41.4 (1052)	22.4 (569)	6.6 (168)	10 (4.5)
11961-X12	20U	19"	12 300)	41.4 (1052)	22.4 (569)	12.6 (320)	13 (5.9)
11961-X18	20U	19"	18 (457)	41.4 (1052)	22.4 (569)	18.6 (472)	15 (6.8)
11962-X06	40U	19"	6 (150)	76.4 (1941)	22.4 (569)	6.6 (168)	15 (6.8)
11962-X12	40U	19"	12 300)	76.4 (1941)	22.4 (569)	12.6 (320)	16 (7.3)
11962-X18	40U	19"	18 (457)	76.4 (1941)	22.4 (569)	18.6 (472)	20 (9.1)
11963-X06	12U	23"	6 (150)	27.4 (696)	26.4 (671)	6.6 (168)	10 (4.5)
11963-X12	12U	23"	12 300)	27.4 (696)	26.4 (671)	12.6 (320)	11 (5.0)
11963-X18	12U	23"	18 (457)	27.4 (696)	26.4 (671)	18.6 (472)	13 (5.9)
11964-X06	20U	23"	6 (150)	41.4 (1052)	26.4 (671)	6.6 (168)	11 (5.0)
11964-X12	20U	23"	12 300)	41.4 (1052)	26.4 (671)	12.6 (320)	12 (5.4)
11964-X18	20U	23"	18 (457)	41.4 (1052)	26.4 (671)	18.6 (472)	15 (6.8)
11965-X06	40U	23"	6 (150)	76.4 (1941)	26.4 (671)	6.6 (168)	16 (7.3)
11965-X12	40U	23"	12 300)	76.4 (1941)	26.4 (671)	12.6 (320)	17 (7.7)
11965-X18	40U	23"	18 (457)	76.4 (1941)	26.4 (671)	18.6 (472)	19 (8.6)

X=Color: 1=Gray, 5=Clear, 7=Black, E=Glacier White