



CHATSWORTH
PRODUCTS

Universal Input Line Cord Options for eConnect PDUs with Universal Input

Universal Input – A single PDU design with detachable input cords supports global AC power standards, streamlining procurement, reducing inventory complexity, accelerating deployment, and ensuring reliable high-power performance across worldwide data centers.



ORDERING INFORMATION

Universal Input Line Cord Options				
Part Number	Input Amperage	Nominal Input Voltage	Input Plug	kW Capacity
Single-Phase Input				
CU-09-D2-C8	30A	208V	NEMA L6-30P	5 kW
CU-42-Y1-C8	32A	220-240V	IEC 60309 32A 1P+N+E	7.7 kW
Three-Phase Input				
CU-13-D3-C8	30A	208V	NEMA L15-30P	8.6 kW
CU-22-D3-C8	30A	120/208V	NEMA L21-30P	8.6 kW
CU-34-D3-C8	50A	208V	CS8365C	14.4 kW
CU-52-D3-C8	60A	208V	IEC 60309 60A 3P+E	17.2 kW
CU-62-Y3-C8	32A	220-240V/380-415V	IEC 60309 32A 3P+N+E	23 kW
CU-66-Y3-C8	63A	220-240V/380-415V	IEC 60309 60A 3P+N+E	34.5 kW

United States & Canada
Simi Valley, CA
800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com
techsupport@chatsworth.com

Latin America
Mexico City, Mexico
+52-55-5203-7525
Toll Free within Mexico
800-201-7592
chatsworth.com.co

Europe
Buckinghamshire
England, UK
+44-1628-524-834

Middle East & Africa
Dubai, UAE
+971-4-2602125

Asia Pacific
Jing'an District,
Shanghai, China
+86 21 6880-0266
chatsworth.com.cn