

Aisle Containment Door Assembly




Aisle Containment Door Assembly

Use with all CPI containment solutions. The door assembly encloses the end of an aisle between adjacent cabinet rows. Available in single- and double-door assemblies. Fits snugly against the cabinets, and features an integrated interior handle, full height vertical edge seals, height adjustable brush floor seals and a magnetic door seal. Automatic close system ensures maximum performance by minimizing airflow disruptions. Low-profile design conceals installation hardware.


- Door frames feature an integrated interior handle, full-height vertical edge seals, height-adjustable brush floor seals and a magnetic door seal
- Automatic close system ensures maximum performance by minimizing airflow disruptions and includes a speed control damper for safe operation
- Detects open feature for easy access during extended service periods
- No threshold under the door when opened
- Low-profile design conceals floor installation hardware
- Door frames are anodized aluminum with a large, full-height, transparent polycarbonate window
- Door track is aluminum extrusion; end panels, cover and brackets are steel
- Not compatible with cabinets/frames less than 42" D (1050 mm) on 7 tile, 168" (4200 mm) pitch
- End panels are painted glacier white or black; option for paint matched door frames available

Dimensions (H x W x D), in (mm)

- 1 size, assembly is 88.5"H x 87.8"W x 5.4"D (2248 mm x 2231 mm x 137 mm) with an 82"H x 32"W (2083 mm x 810 mm) door opening
- Spans 36"W to 48"W (910 mm x 1200 mm) aisles (1.5 to 2 tiles)
- Retrofit solution for narrower 36" (910 mm) aisle clearance



*Aisle Containment
Door Assembly Single
Door, Open to the Right*



*Aisle Containment
Door Assembly Single Door,
Open to the Left*

ORDERING INFORMATION

Part Number	Description	Shipping Weight lb (kg)
32780-X02	Single-Door, Opens to the Right, With Painted Door Frames	290 (127.0)
32780-X04	Single-Door, Opens to the Right, With Anodized Aluminum Door Frames	290 (127.0)
32780-X02	Single-Door, Opens to the Left, With Painted Door Frames	290 (127.0)
32780-X04	Single-Door, Opens to the Left, With Anodized Aluminum Door Frames	290 (127.0)

X=color; 7=Black, E=Glacier White

Notes: Single door is right or left opening, spans two tile aisles and has a 32"W (812 mm) door opening. Order one Floor Mounting Template for each site.