Product Cut Sheet


AISLE CONTAINMENT UNIVERSAL CABINET PANEL

Universal Cabinet Panel is an optional accessory that is used with the Frame Supported Hot Aisle Containment (HAC) Solution and the Cabinet Supported Cold Aisle Containment (CAC) Solution. In both instances the panel is added when cabinets vary in width and height to seal the space between the top of the cabinet and the Frame Supported Exhaust Duct or Cabinet Supported Ceiling Panel Kit.

- Alternative to Adjustable Height Filler Panel (See 32728_CUT)
- · Adjusts in width to match odd cabinet sizes
- Use above short cabinets to fill gaps between the top of the cabinet and the Frame Supported Exhaust Duct or the Cabinet Supported Ceiling Panel Kit
- Attaches to the beams on the Frame Supported Exhaust Duct (See 32990_CUT) or Cabinet Supported Ceiling Panel Kit (See 32710-32711_CUT)
- Contains air in the enclosed aisle between adjacent rows of cabinets
- Includes vertical and horizontal seals
- Fits snug against the top of the short cabinet and the sides of the adjacent cabinets
- Adjusts in width and height, available for 3U, 6U, 9U and 11U cabinet height differences
- Aluminum panel and steel brackets are painted glacier white or black
- Match to width of cabinet and height of opening above cabinet

Use With:

- Frame Supported Exhaust Duct (See 32990_CUT) used as part of the Frame Supported Hot Aisle Containment (HAC) Solution to form the exhaust duct over the contained aisle
- Cabinet Supported Ceiling Panel Kit (See 32710-32711_CUT) used as part of the Cabinet Supported Cold Aisle Containment (CAC) Solution to form a ceiling over the contained aisle



Adjusts in height and width. Back and front shown

Part Number & Finish		Description	Shipping Weight
Black	Glacier White	Description	lb (kg)
For up to 3U High Cabinet Height Difference			
32720-701	32720-E01	Adjusts from 15.8"W (400 mm) to 23.6"W (600 mm)	6 (2.7)
32720-704	32720-E04	Adjusts from 19.7"W (500 mm) to 27.6"W (700 mm)	6 (2.7)
32720-707	32720-E07	Adjusts from 21.7"W (551 mm) to 29.5"W (750 mm)	7 (3.2)
32720-710	32720-E10	Adjusts from 23.6"W (600 mm) to 31.5"W (800 mm)	7 (3.2)
32720-713	32720-E13	Adjusts from 32.1"W (815 mm) to 40.0"W (1016 mm)	8 (3.6)
	For up	to 6U High Cabinet Height Difference	•
32720-702	32720-E02	Adjusts from 15.8"W (400 mm) to 23.6"W (600 mm)	7 (3.2)
32720-705	32720-E05	Adjusts from 19.7"W (500 mm) to 27.6"W (700 mm)	7 (3.2)
32720-708	32720-E08	Adjusts from 21.7"W (551 mm) to 29.5"W (750 mm)	8 (3.6)
32720-711	32720-E11	Adjusts from 23.6"W (600 mm) to 31.5"W (800 mm)	8 (3.6)
32720-714	32720-E14	Adjusts from 32.1"W (815 mm) to 40.0"W (1016 mm)	9 (4.1)
	For up	to 9U High Cabinet Height Difference	
32720-703	32720-E03	Adjusts from 15.8"W (400 mm) to 23.6"W (600 mm)	8 (3.6)
32720-706	32720-E06	Adjusts from 19.7"W (500 mm) to 27.6"W (700 mm)	8 (3.6)
32720-709	32720-E09	Adjusts from 21.7"W (551 mm) to 29.5"W (750 mm)	9 (4.1)
32720-712	32720-E12	Adjusts from 23.6"W (600 mm) to 31.5"W (800 mm)	10 (4.5)
32720-715	32720-E15	Adjusts from 32.1"W (815 mm) to 40.0"W (1016 mm)	11 (5.0)
	For up t	o 11U High Cabinet Height Difference	
32720-716	32720-E16	Adjusts from 15.8"W (400 mm) to 23.6"W (600 mm)	8 (3.6)
32720-717	32720-E17	Adjusts from 19.7"W (500 mm) to 27.6"W (700 mm)	9 (4.1)
32720-718	32720-E18	Adjusts from 21.7"W (551 mm) to 29.5"W (750 mm)	10 (4.5)
32720-719	32720-E19	Adjusts from 23.6"W (600 mm) to 31.5"W (800 mm)	10 (4.5)
32720-720	32720-E20	Adjusts from 32.1"W (815 mm) to 40.0"W (1016 mm)	12 (5.4)

800-834-4969 in US & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

©2012 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-iT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products, Inc. eConnect and Simply Efficient are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies.