

Product Information Sheet


24" (610 mm) BAYING & FASCIA KIT FOR F-SERIES TERAFRAME™ CABINET



The 24" (610 mm) Baying & Fascia Kit allows you to bay and center two 23.6"W (600 mm) Gen 2 F-Series TeraFrame Cabinets over 24"W (610 mm) raised access floor tiles. The kit includes two brackets and hardware to space and connect the cabinets together and two fascias that cover and hide the 0.4" (10 mm) gap between the cabinets.

- Each kit includes two 3.6"W x .8"H x 2.0"D (92 mm x 20 mm x 51 mm) C-shaped brackets and installation hardware to bay the cabinets
- The brackets attach to the tops of the cabinet frames at the front and rear of the cabinet and space the cabinets so they are centered over 24" (610 mm) raised access floor tiles
- Each kit also includes two 1"W (25 mm) T-shaped fascias and installation hardware
- The fascias attach to the side of the cabinet frame through mounting holes at the top and bottom of frame and can be used with or without side panels
- Cabinets must be the same height and depth
- Select the 24" (610 mm) Baying and Fascia Kit to match the height (RMU) and color of the bayed cabinets
- If one or both side panels are omitted between cabinets, seal the gap using a Seal Kit (P/N 35081-001 or 35081-002)
- Designed for use with Gen 2 F-Series TeraFrame Cabinets only

For assistance in configuring your TeraFrame Cabinet, contact Technical Support at 800-834-4969 or visit CPI's Product Configurator at www.chatsworth.com/configurator.



24" (610 mm) Baying & Fascia Kit		
Part Number	Description	Shipping Weight
35080-X00	For 24 RMU Cabinet	9 lb (4.1 kg)
35080-X01	For 36 RMU Cabinet	11 lb (5.0 kg)
35080-X02	For 42 RMU Cabinet	12 lb (5.4 kg)
35080-X03	For 43 RMU Cabinet	12 lb (5.4 kg)
35080-X04	For 44 RMU Cabinet	12 lb (5.4 kg)
35080-X05	For 45 RMU Cabinet	13 lb (5.9 kg)
35080-X06	For 46 RMU Cabinet	13 lb (5.9 kg)
35080-X07	For 47 RMU Cabinet	13 lb (5.9 kg)
35080-X08	For 48 RMU Cabinet	13 lb (5.9 kg)
35080-X09	For 49 RMU Cabinet	13 lb (5.9 kg)
35080-X10	For 50 RMU Cabinet	14 lb (6.4 kg)
35080-X11	For 51 RMU Cabinet	14 lb (6.4 kg)

X=color: C=Black, D=Signature Blue, E=Glacier White, F=Steel Gray. Use with Side Seal Kit (P/N 35081-001) if one side panel is omitted or with Side Seal Kit (P/N 35081-002) if both side panels are omitted between cabinets.

800-834-4969 in U.S. & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

©2009 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, Saf-T-Grip, Seismic Frame, SlimFrame and MegaFrame are federally registered trademarks of Chatsworth Products, Inc. Cube-IT Plus, Evolution, OnTrac, QuadraRack, Simply Efficient and TeraFrame are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. 07/09