

NEW CATALOG ITEM



BENEFITS:

- Double-sided design and pass-through slots allow easy organization of front and rear cables.
- Standard fingers in front and extended fingers in back more than double the horizontal manager's cable capacity.
- Alignment with CPI's double-sided vertical cabling sections creates a smooth cable pathway system.
- Patented cable guide fingers ensure proper cable bend and withstand wear.
- Snap-on, hinged covers create a professional look.

An Employee Owned Corporation



**CHATSWORTH
PRODUCTS, INC.**

Organizing. Storing. Securing.

800-834-4969

techsupport@chatsworth.com
www.chatsworth.com

DOUBLE-SIDED UNIVERSAL HORIZONTAL CABLE MANAGER

Maximize Front and Rear Cable Management

Chatsworth Products, Inc. (CPI) expands the functionality of the Universal Horizontal Cable Manager with the introduction of a new double-sided version for easy organization of front and rear cables in racks or cabinets. Pass-through slots facilitate routing of cords and cables between the two sides. The double-sided design supports more than twice as much cable and frees up valuable mounting space for other equipment. In addition, the Double-Sided Universal Horizontal Cable Manager aligns with CPI's double-sided vertical cabling sections to create an integrated cable pathway system.

The new horizontal manager uses the same patented cable guide fingers, spaced 1.75" apart, as single-sided models to ensure proper cable bend and improved system performance. Fingers have standard 3.21" depth in front and extended 5.75" depth – protruding 4" behind the rack channel – in the rear. In addition, they are made of durable, flame-retardant (UL 94V-0) plastic.

Snap-on, hinged covers hide the cables, giving the installation a professional appearance. The covers swing 180 degrees up and down for easy access to cables. The product ships assembled and is available in 19" and 23" widths and 1 RMU, 2 RMU and 3 RMU heights.

For more information, contact an authorized CPI distributor or call CPI Technical Support at 800-834-4969.

Double-Sided Cable Manager		
Part Number	Description	Shipping Weight
30529-719	19"W x 11.73"D x 1 RMU, Black	5 lb
30529-723	23"W x 11.73"D x 1 RMU, Black	6 lb
30530-719	19"W x 11.73"D x 2 RMU, Black	6 lb
30530-723	23"W x 11.73"D x 2 RMU, Black	7 lb
30531-719	19"W x 11.73"D x 3 RMU, Black	6 lb
30531-723	23"W x 11.73"D x 3 RMU, Black	7 lb

Single-Sided Cable Manager		
Part Number	Description	Shipping Weight
30139-719	19"W x 4.96"D x 1 RMU, Black	2 lb
30139-723	23"W x 4.96"D x 1 RMU, Black	3 lb
30130-719	19"W x 5.14"D x 2 RMU, Black	3 lb
30130-723	23"W x 5.14"D x 2 RMU, Black	4 lb
30131-719	19"W x 5.14"D x 3 RMU, Black	4 lb
30131-723	23"W x 5.14"D x 3 RMU, Black	5 lb
30339-719*	19"W x 6.26"D x 1 RMU, Black	3 lb
30339-723*	23"W x 6.26"D x 1 RMU, Black	3 lb
30330-719*	19"W x 6.44"D x 2 RMU, Black	4 lb
30330-723*	23"W x 6.44"D x 2 RMU, Black	5 lb
30331-719*	19"W x 6.44"D x 3 RMU, Black	5 lb
30331-723*	23"W x 6.44"D x 3 RMU, Black	6 lb



*Deep Panel is used when Double-Sided MCS Master Cabling Sections are center-mounted on 3" Deep Racks.