



## CABLE MANAGER

PRIOR TO MOUNTING THE SHELF, DETERMINE WHICH SIDE OF THE SHELF THAT THE CABLES SHOULD FEED INTO. THE SHELF IS ASSEMBLED SO THAT THE CABLES FEED INTO THE LEFT SIDE. TO CHANGE TO THE RIGHT SIDE FOLLOW THESE INSTRUCTIONS.

1. LAY SHELF DOWN BOTTOM FACING UP.
2. REMOVE THE FOUR CABLE MANAGER ATTACHMENT KNOBS AND THEN REMOVE THE MANAGER.
3. REMOVE THE TWO FRONT MOUNTING BRACKET ATTACHMENT KNOBS AND THEN THE BRACKET.
4. REMOVE THE TWO REAR MOUNTING BRACKET SCREWS AND THEN THE BRACKET.
5. REATTACH THE BRACKETS TO THE OPPOSITE SIDES AND THEN MOUNT THE CABLE MANAGER TO THE BRACKETS.

**CPI** CHATSWORTH PRODUCTS, INC.

## INSTALLATION INSTRUCTIONS, EXTRA HEAVY DUTY 4-POINT SLIDING SHELF

THIS DRAWING CONTAINS INFORMATION PROPRIETARY TO CHATSWORTH PRODUCTS, INC. ANY REPRODUCTION DISCLOSURE OR USE OF THIS DRAWING IS EXPRESSLY FORBIDDEN EXCEPT AS AGREED TO IN WRITING BY CHATSWORTH PRODUCTS, INC.

**MOUNTING SHELF**

6. LOOSEN THE MOUNTING BRACKET KNOBS AND ADJUST THE DISTANCE BETWEEN THE FRONT AND REAR MOUNTING FLANGES SO THAT IT IS SLIGHTLY MORE THAN THE RAIL DEPTH (THE SHELF IS DESIGNED TO FIT DEPTHS BETWEEN 20" AND 34"). DEPENDING ON THE DEPTH, THE KNOBS MAY NEED TO BE MOVED TO ONE OF THE OTHER STUDS, ALWAYS USE THE STUDS THAT ARE CLOSEST TO THE ENDS OF THE REAR BRACKET. SLIGHTLY TIGHTEN THE KNOBS.
7. MOUNT THE SHELF TO THE RACK RAILS WITH 8 SCREWS (NOT PROVIDED). BE SURE THAT ALL SCREWS ARE FULLY TIGHTENED. HAND TIGHTEN THE MOUNTING BRACKET KNOBS.

**SHELF OPERATION**

8. THE SHELF CAN SUPPORT A MAXIMUM OF 300 POUNDS.
9. SECURE EQUIPMENT CABLE IN THE CABLE MANAGER USING THE EIGHT CABLE CLIPS.
10. THE SHELF LOCKS IN THE CLOSED AND OPENED POSITION. TO UNLOCK, PUSH THE LEVER, LOCATED ON THE FRONT RIGHT SIDE OF THE SHELF, TO THE RIGHT. MOVE THE SHELF TO THE DESIRED POSITION AND RELEASE THE LEVER.

