

# Product Information Sheet

## 14" RAISED FLOOR ENCLOSURE FOR ACTIVE COMPONENTS



The A1411-RF-HR is a "telecommunications enclosure" suitable for use in air handling spaces. Support 5U of 19" patch panels and 2U of active components under 14" deep raised floors. A1411-RF-HR may be supported from the raised floor pedestals with included brackets and uses the 2' x 2' raised floor tile as a lid.

A1411-RF-HR has two edge-protected cable access ports that include fire rated foam sealing kits. The enclosure includes a removable tray that provides 5U of mounting space divided into 2U-1U-2U spaces for patch panels and 2U of mounting space for active components measuring up to 15" deep. The enclosure includes a junction box for a single duplex power outlet and a filtered fan to remove heat from the enclosure.

### ■ Cable Entry/Exit

- (2) 3" wide x 6" high edge-protected cable access ports
- Includes approved fire-rated foam sealing kits

### ■ Equipment Support

- Removable tray-mounted assembly for 19" rack-mount patch panels and active equipment
- 5U divided 2U-1U-2U for patch panels/cable managers, 1" of usable depth.
- 2U for active components up to 15" deep
- Includes a junction box with a position for a single duplex outlet, and a two-bolt ground
- Ventilation fan and filters, 9 CFM, includes 115V AC/DC Transformer.

### ■ Materials

- Enclosure: .060" thick sheet aluminum, riveted construction
- Foam Sealing Kit: Polychloroprene latex compound
- Installation Brackets: steel

### ■ Packaging

- 1 Enclosure/Carton

### ■ Approvals

- UL Listed - Communications Circuit Accessory
- UL File Number/E185147 (UL 1863; UL 50; UL 2043)



| Part Number | Description                                           | Shipping Weight |
|-------------|-------------------------------------------------------|-----------------|
| A1411-RF-HR | 7U Enclosure for Active Components and 14" Deep Floor | 30 lb           |

### ■ Specifications

- Enclosure: 24" wide x 24" long x 12-1/2" deep
- Weight: 30 lb

### ■ Installation

- Includes mounting brackets for 1-1/2" rectangular or round raised floor pedestals
- Use #12-24 equipment mounting screws to attach patch panels (P/N 40605-001).
- Use Saf-T-Grip Cable Management Straps to manage cables (P/N 02006-201).

800-834-4969 US & Canada • [www.chatsworth.com](http://www.chatsworth.com)



CHATSWORTH PRODUCTS, INC.

©2003 Chatsworth Products, Inc. All rights reserved. CPI is a registered trademark of Chatsworth Products, Inc. All other trademarks belong to their respective companies 04/03