

# Product Information Sheet

## PATCH PANEL ENCLOSURES FOR 14" D (360 mm) RAISED ACCESS FLOORS



### TELECOMMUNICATION ENCLOSURES

The Patch Panel Enclosure for 14" D (360 mm) raised access floors are a 12-1/2" D (318 mm) consolidation point enclosure suitable for use in air handling spaces. Support 11U of 19" patch panels under 14" D (360 mm) raised access floors. The enclosure may be supported from the raised floor pedestals with included brackets and uses the 2' x 2' raise floor tile as a lid.

Each enclosure has four edge-protected cable access ports that include fire rated foam sealing kits. Two styles are available with standard or large cable access ports. There is 6-3/4" (171 mm) of open space below the rails and 4-3/4" (120 mm) of open space above the rails within the enclosure to allow for proper bend radii.

#### ■ Cable Entry/Exit

- A1422-RF Enclosures have (4) 9-3/4"W x 2-3/4"H (247 mm x 69 mm) edge-protected cable access ports
- 13772-002 Enclosures have (6) 14-3/4"W x 3-1/4"H (374 mm x 82 mm) edge-protected cable access ports. Ideal for Cat 6a UTP Cable.
- Includes approved fire-rated foam sealing kit

#### ■ Equipment Support

- 11U for 19" patch panels
- A1422-RF mounting rails are fixed
- 13772-002 mounting rails pivot

#### ■ Materials

- Enclosure: .060" thick (1.52 mm) sheet aluminum, riveted construction
- Foam Sealing Kit: Polychloroprene latex compound
- Installation Brackets: steel

#### ■ Packaging

- 1 Enclosure/Carton

#### ■ Approvals

- UL Listed - Communications Circuit Accessory
- UL File Number/E185147 (UL 1863; UL 50; UL 2043)

#### ■ Specifications

- Enclosure: 24"W x 27-1/2"L x 12-1/2"D (610 mm x 700 mm x 318 mm)



Part Number	Description	Shipping Weight
A1422-RF	11U Enclosure for 14"D (360 mm) Floor	30 lb (13.6 kg)
13772-002	4+4U Enclosure with Large Cable Access Ports for 14"D (360 mm) Floor	30 lb (13.6 kg)

#### ■ Installation

- Includes mounting brackets for 1-1/2" (38.1 mm) rectangular or round raised floor pedestals
- Use #12-24 equipment mounting screws to attach patch panels (P/N 40605-001) Sold Separately.

800-834-4969 in U.S. & Canada • [www.chatsworth.com](http://www.chatsworth.com)