


# Product Information Sheet

## REAR DOORS FOR TERAFRAME™ CABINET SYSTEM

Three rear door panel styles are available for the TeraFrame Cabinet System: solid metal, single perforated (vented) metal and double perforated (vented) metal. The double door reduces the amount of aisle space required to access the rear of the cabinet. Double doors must be used with two-point latches and cannot be used with the Standalone Electronic Keypad.

Match the width, height and color to the cabinet. Select the door latch separately. Colors available; C=Black, D=Signature Blue, E=Glacier White, F=Steel Gray. The door inserts color match the door.

For assistance in configuring your TeraFrame Cabinet, contact Technical Support at 800-834-4969 or visit CPI's Product Configurator at [www.chatsworth.com/configurator](http://www.chatsworth.com/configurator).



Single Solid Rear Door

Single Perforated Rear Door

Double Perforated Rear Door

Single Solid Rear Door for TeraFrame				
Part Number			Height (RMU)	Shipping Weight*
600 mm	700 mm	800 mm		
35054-X00	35054-X12	35054-X24	24	40 lb (15.4 kg)
35054-X01	35054-X13	35054-X25	36	50 lb (22.7 kg)
35054-X02	35054-X14	35054-X26	42	55 lb (24.9 kg)
35054-X03	35054-X15	35054-X27	43	56 lb (25.4 kg)
35054-X04	35054-X16	35054-X28	44	56 lb (25.4 kg)
35054-X05	35054-X17	35054-X29	45	57 lb (25.9 kg)
35054-X06	35054-X18	35054-X30	46	59 lb (26.8 kg)
35054-X07	35054-X19	35054-X31	47	60 lb (27.2 kg)
35054-X08	35054-X20	35054-X32	48	61 lb (27.7 kg)
35054-X09	35054-X21	35054-X33	49	62 lb (28.1 kg)
35054-X10	35054-X22	35054-X34	50	63 lb (28.6 kg)
35054-X11	35054-X23	35054-X35	51	64 lb (29.0 kg)

Single Perforated Rear Door for TeraFrame				
Part Number			Height (RMU)	Shipping Weight*
600 mm	700 mm	800 mm		
35044-X00	35044-X12	35044-X24	24	25 lb (11.3 kg)
35044-X01	35044-X13	35044-X25	36	29 lb (13.2 kg)
35044-X02	35044-X14	35044-X26	42	31 lb (14.1 kg)
35044-X03	35044-X15	35044-X27	43	32 lb (14.5 kg)
35044-X04	35044-X16	35044-X28	44	32 lb (14.5 kg)
35044-X05	35044-X17	35044-X29	45	32 lb (14.5 kg)
35044-X06	35044-X18	35044-X30	46	34 lb (15.4 kg)
35044-X07	35044-X19	35044-X31	47	34 lb (15.4 kg)
35044-X08	35044-X20	35044-X32	48	34 lb (15.4 kg)
35044-X09	35044-X21	35044-X33	49	35 lb (15.9 kg)
35044-X10	35044-X22	35044-X34	50	35 lb (15.9 kg)
35044-X11	35044-X23	35044-X35	51	36 lb (16.3 kg)

Double Perforated Rear Door for TeraFrame				
Part Number			Height (RMU)	Shipping Weight*
600 mm	700 mm	800 mm		
35030-X00	35030-X12	35030-X24	24	33 lb (15.0 kg)
35030-X01	35030-X13	35030-X25	36	40 lb (18.1 kg)
35030-X02	35030-X14	35030-X26	42	43 lb (19.5 kg)
35030-X03	35030-X15	35030-X27	43	44 lb (20.0 kg)
35030-X04	35030-X16	35030-X28	44	44 lb (20.0 kg)
35030-X05	35030-X17	35030-X29	45	45 lb (20.4 kg)
35030-X06	35030-X18	35030-X30	46	47 lb (21.3 kg)
35030-X07	35030-X19	35030-X31	47	47 lb (21.3 kg)
35030-X08	35030-X20	35030-X32	48	48 lb (21.8 kg)
35030-X09	35030-X21	35030-X33	49	49 lb (22.2 kg)
35030-X10	35030-X22	35030-X34	50	49 lb (22.2 kg)
35030-X11	35030-X23	35030-X35	51	50 lb (22.7 kg)

X=color; C=Black, D=Signature Blue, E=Glacier White, F=Steel Gray.

\*Shipping weights are based on 800 mm doors.

800-834-4969 in U.S. & Canada • [www.chatsworth.com](http://www.chatsworth.com)



CHATSWORTH PRODUCTS, INC.

©2009 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, Saf-T-Grip, Seismic Frame, SlimFrame and MegaFrame are federally registered trademarks of Chatsworth Products, Inc. Cube-IT Plus, Evolution, OnTrac, QuadraRack, Simply Efficient and TeraFrame are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. Rev.3 01/09