


Product Cut Sheet

AISLE CONTAINMENT DOOR MOUNTING BRACKET KIT

- Use with Cabinet Supported Aisle Containment Solutions only
- Secures the Aisle Containment Door Assemblies to the tops of the cabinets, includes two brackets
- Three height ranges; bracket height adjusts to match the difference between the cabinet height and door height
- Flush mount and offset mount versions; use offset mount versions with the Door Standoff Kit (P/N 32870-XXX)

Flush Mount Brackets




3" H (75 mm),
Minimum

3" H (75 mm),
Maximum

5" H (125 mm)
Maximum

10" H (254 mm),
Maximum

Offset Mount Brackets



3" H (75 mm),
Minimum

3" H (75 mm),
Maximum

5" H (125 mm)
Maximum

10" H (254 mm),
Maximum

Door Mounting Bracket Kit			
Part Number & Finish		Description	Shipping Weight lb (kg)
Black	Glacier White		
Flush Mount For Use Without Door Standoff Kit			
32805-700	32805-E00	Adjusts Up To 3"H (75 mm), For 85.3"H (2167 mm) to 91.4"H (2322 mm) Cabinets	2 (0.9)
32805-701	32805-E01	Adjusts Up To 5"H (125 mm), For 82.6"H (2098 mm) to 94.2"H (2393 mm) Cabinets	3 (1.4)
32805-702	32805-E02	Adjusts Up To 10"H (254 mm), For 77.8"H (1976 mm) to 98.9"H (2512 mm) Cabinets	4 (1.8)
Offset Mount For Use With Door Standoff Kit			
32805-703	32805-E03	Adjusts Up To 3"H (75 mm), For 85.3"H (2167 mm) to 91.4"H (2322 mm) Cabinets	2 (0.9)
32805-704	32805-E04	Adjusts Up To 5"H (125 mm), For 82.6"H (2098 mm) to 94.2"H (2393 mm) Cabinets	3 (1.4)
32805-705	32805-E05	Adjusts Up To 10"H (254 mm), For 77.8"H (1976 mm) to 98.9"H (2512 mm) Cabinets	4 (1.8)

800-834-4969 in US & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

©2012 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-iT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products, Inc. eConnect and Simply Efficient are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies.