

Product Cut Sheet


AISLE CONTAINMENT SINGLE DOOR ASSEMBLY

Aisle Containment Doors are used on the ends of two adjacent rows of cabinets. The doors are part of a complete Aisle Containment Solution that captures or vents hot or cold air from an enclosed aisle.


- Encloses the end of an aisle between adjacent cabinet rows
- Compatible with F-Series TeraFrame® Cabinets and GF-Series GlobalFrame® Cabinets
- Right-hand or left-hand opening models
- Fits snug against cabinets
- Sliding action minimizes clearance requirements
- Door frames feature an integrated interior handle, full height vertical edge seals, height adjustable brush floor seals and a magnetic door seal
- Automatic close system ensures maximum performance by minimizing airflow disruptions and includes a speed control damper for safe operation
- Detents open feature for easy access during extended service periods
- No threshold under the door when opened
- Low profile design conceals floor installation hardware
- Door frames are anodized aluminum with a large, full-height, transparent polycarbonate window
- Door track is aluminum extrusion; end panels, cover and brackets are steel
- One size, assembly is 88.5" (2248 mm) high by 87.8" (2231 mm) wide by 5.4" (137 mm) deep with an 82" (2083 mm) high by 32" (810 mm) wide door opening
- Spans 36" (910 mm) to 48" (1200 mm) wide aisles (one-and-a-half to two tiles)
- Retrofit solution for narrower 36" (910 mm) aisle clearance
- Provides clearance for building columns and structures at the end of a cabinet row
- Not compatible with cabinets/frames less than 42" (1050 mm) deep on six tile, 144" (3600 mm) pitch
- End panels are painted white or black; option for paint matched door frames available

Key Accessories

- Floor Mounting Template (See 32875_CUT) – required to correctly locate floor mounting holes
- Door Mounting Bracket Kit (See 32805_CUT) – required to attach doors to cabinets
- GlobalFrame Door Rail Support Kit (See 32771_CUT) – additional bracket required to attach Door Mounting Bracket Kit to GF-Series GlobalFrame Cabinet
- Door Top Seal Kit (See 32817_CUT) – required when the tops of cabinets are over 88" (2235 mm) tall to cover the gap above the door
- Door Standoff Kit (See 32870_CUT) – optional baffle used to offset doors over raised access floor tiles



Aisle Containment Single Door Assembly –
Opens Left



Aisle Containment Single Door Assembly –
Opens Right

Aisle Containment Single Door Assembly			
Part Number & Finish		Description	Shipping Weight lb (kg)
Black	Glacier White		
Door Opens to the Left			
32780-701	32780-E01	With Painted Door Frames, Opens Left	280 (127.0)
32780-703	32780-E03	With Anodized Aluminum Door Frames, Opens Left	280 (127.0)
Door Opens to the Right			
32780-702	32780-E02	With Painted Door Frames, Opens Right	280 (127.0)
32780-704	32780-E04	With Anodized Aluminum Door Frames, Opens Right	280 (127.0)

Note: Additional mounting brackets are required to attach door to cabinets.

800-834-4969 in U.S. & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

©2012 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-iT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products, Inc. eConnect and Simply Efficient are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies.