


Mounting Plates for RMR Wall-Mount Enclosure Systems

Mounting Plates are flat panels that provide a way of attaching a variety of network, automation or control equipment devices into the enclosure for flexible support configurations.

- Fixed Mounting Plates are solid metal panels that are installed in a side-to-side orientation at the rear of the enclosure onto the back of the frame and can be ordered with the enclosure
- Adjustable Mounting Plates are solid metal panels that attach in a side-to-side orientation in the middle section of the enclosure and can be adjusted in depth by one-inch increments and are ordered as accessories



ORDERING INFORMATION

RMR Wall-Mount Enclosure Fixed Depth Mounting Plate					
Part Number Enclosure Width in (mm)		Enclosure Height in (mm)	Plate Height in (mm)	Plate Width in (mm)	Shipping Weight lb (kg)
23.6 (600)	27.6 (700)				
37075-X01	37075-X31	19.1 (486)	14 (356)	*	15 (6.9)
37075-X04	37075-X34	24.4 (619)	20 (508)	*	19 (8.7)
37075-X05	37075-X35	26.1 (664)	21 (534)	*	20 (9.1)
37075-X07	37075-X37	29.7 (753)	25 (635)	*	22 (10.0)
37075-X10	37075-X40	34.9 (886)	30 (762)	*	26 (11.8)
37075-X13	37075-X43	40.1 (1019)	35 (889)	*	30 (13.7)
37075-X18	37075-X48	48.9 (1241)	44 (1118)	*	36 (16.4)

X=Color; C=Black, G=Hammer Gray. *Plate width is 20"W (508 mm) for 23.6"W (600 mm) enclosures and 24"W (610 mm) for 27.6"W (700 mm) enclosures. *Shipping weights are for 27.6"W (700 mm) models.

RMR Wall-Mount Enclosure Adjustable Depth Mounting Plate					
Part Number Enclosure Width in (mm)		Enclosure Height in (mm)	Plate Height in (mm)	Plate Width in (mm)	Shipping Weight lb (kg)
23.6 (600)	27.6 (700)				
37076-X01	37076-X31	19.1 (486)	14 (356)	*	15 (6.9)
37076-X04	37076-X34	24.4 (619)	20 (508)	*	19 (8.7)
37075-X07	37075-X37	29.7 (753)	25 (635)	*	22 (10.0)
37075-X10	37075-X40	34.9 (886)	30 (762)	*	26 (11.8)
37075-X13	37075-X43	40.1 (1019)	35 (889)	*	30 (13.7)
37075-X18	37075-X48	48.9 (1241)	44 (1118)	*	36 (16.4)

X=Color; C=Black, G=Hammer Gray. *Plate width is 20"W (508 mm) for 23.6"W (600 mm) enclosures and 24"W (610 mm) for 27.6"W (700 mm) enclosures. *Shipping weights are for 27.6"W (700 mm) models.

For product CSI Specs, visit the Support & Downloads page on www.chatsworth.com.

US & Canada

+1-800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com
techsupport@chatsworth.com

Latin America

+52-55-5203-7525
Toll Free within Mexico
01-800-01-7592
chatsworth.com.co

Europe

+44-1628-524-834
chatsworthproducts.co.uk

Middle East & Africa

Dubai, UAE
+971-4-2602125
chatsworth.ae

Asia Pacific

+86 21 6880-0266
chatsworth.com.cn



CHATSWORTH
PRODUCTS