

Product Information Sheet

VERTICAL MOUNT POWER STRIP FOR UNIVERSAL RACKS

Streamlined, durable steel body is fitted with bracket for vertical mounting on CPI Universal Racks.

- Eight outlets
- 10' (3 m) cord
- UL Listed
- Does not work in conjunction with (vertical) cabling sections



Part Number	Inlet			Outlet Receptacles		Circuit Breakers	Surge Protection	Size	Shipping Weight
	Volts	Amps	Plug/Inlet	Qty	Type				
12819-709	125	15	NEMA 5-15P	8	NEMA 5-15R	-	-	A	6 lb (2.7 kg)
12819-701	125	15	NEMA 5-15P	8	NEMA 5-15R	1 x 15A (T)	-	A	6 lb (2.7 kg)
12819-703	125	15	NEMA 5-15P	8	NEMA 5-15R	1 x 15A (T)	Yes	A	6 lb (2.7 kg)
12819-710	125	15	NEMA L5-15P	8	NEMA 5-15R	-	-	A	6 lb (2.7 kg)
12819-702	125	15	NEMA L5-15P	8	NEMA 5-15R	1 x 15A (T)	-	A	6 lb (2.7 kg)
12819-704	125	15	NEMA L5-15P	8	NEMA 5-15R	1 x 15A (T)	Yes	A	6 lb (2.7 kg)
12819-709	125	20	NEMA 5-20P	8	NEMA 5-20R	-	-	A	6 lb (2.7 kg)
12819-701	125	20	NEMA 5-20P	8	NEMA 5-20R	1 x 20A (T)	-	A	6 lb (2.7 kg)
12819-703	125	20	NEMA 5-20P	8	NEMA 5-20R	1 x 20A (T)	Yes	A	6 lb (2.7 kg)
12819-710	125	20	NEMA L5-20P	8	NEMA 5-20R	-	-	A	6 lb (2.7 kg)
12819-702	125	20	NEMA L5-20P	8	NEMA 5-20R	1 x 20A (T)	-	A	6 lb (2.7 kg)
12819-704	125	20	NEMA L5-20P	8	NEMA 5-20R	1 x 20A (T)	Yes	A	6 lb (2.7 kg)

Size = W x H x D

A = 2.7" x 17" x 3" (69 mm x 430 mm x 80 mm)

800-834-4969 in U.S. & Canada • www.chatsworth.com



CHATSWORTH PRODUCTS, INC.

©2009 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, Saf-T-Grip, Seismic Frame, SlimFrame and MegaFrame are federally registered trademarks of Chatsworth Products, Inc. Cube-iT Plus, Evolution, OnTrac, QuadraRack, Simply Efficient and TeraFrame are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. 12/09