


# Product Cut Sheet

## AISLE CONTAINMENT CABINET TO FLOOR SEAL KIT FOR F-SERIES TERAFRAME® GEN 2 CABINET

Aisle Containment Cabinet To Floor Seal Kits are used at the bottom of cabinets to seal the space between the bottom of the cabinet and the floor when leveling feet or casters are in use. Eliminating this source of bypass airflow is essential due to the high pressure typically experienced in this area.

- Compatible with F-Series TeraFrame® Gen 2 Cabinets (F-Series TeraFrame Gen 2 Cabinets have one-piece side panels.)
- Blocks bypass airflow underneath cabinets to prevent leakage from the contained aisle
- Fits snug against cabinets and the floor
- Includes sheet steel mounting brackets with a flexible black PVC seal along the base
- Front and Side Seals are ordered separately
- Use one front seal kit on each cabinet; select to match the overall width of the cabinet
- Use one side seal kit on each cabinet row; select to match the depth of the cabinet/frame



F-Series TeraFrame Gen 2 Cabinet

Cabinet To Floor Seal Kit For F-Series TeraFrame® Gen 2 Cabinet			
Part Number & Finish		Description	Shipping Weight lb (kg)
Black	Glacier White		
<b>Front Seal Kits</b>			
32809-700	32809-E00	For a 23.6"W (600 mm) Cabinet	3 (1.4)
32809-701	32809-E01	For a 27.6"W (700 mm) Cabinet	4 (1.8)
32809-702	32809-E02	For a 31.5"W (800 mm) Cabinet	4 (1.8)
<b>Side Seal Kits</b>			
32812-700	32812-E00	For a 31.5"D (800 mm) Cabinet Frame	6 (2.7)
32812-701	32812-E01	For a 32.5"D (825 mm) Cabinet Frame	6 (2.7)
32812-702	32812-E02	For a 33.5"D (850 mm) Cabinet Frame	6 (2.7)
32812-703	32812-E03	For a 34.4"D (875 mm) Cabinet Frame	6 (2.7)
32812-704	32812-E04	For a 35.4"D (900 mm) Cabinet Frame	6 (2.7)
32812-705	32812-E05	For a 36.4"D (925 mm) Cabinet Frame	6 (2.7)
32812-706	32812-E06	For a 37.4"D (950 mm) Cabinet Frame	6 (2.7)
32812-707	32812-E07	For a 38.4"D (975 mm) Cabinet Frame	7 (3.2)
32812-708	32812-E08	For a 39.4"D (1000 mm) Cabinet Frame	7 (3.2)
32812-709	32812-E09	For a 40.4"D (1025 mm) Cabinet Frame	7 (3.2)
32812-710	32812-E10	For a 41.3"D (1050 mm) Cabinet Frame	7 (3.2)
32812-711	32812-E11	For a 42.3"D (1075 mm) Cabinet Frame	7 (3.2)
32812-712	32812-E12	For a 43.3"D (1100 mm) Cabinet Frame	7 (3.2)
32812-713	32812-E13	For a 44.3"D (1125 mm) Cabinet Frame	7 (3.2)
32812-714	32812-E14	For a 45.3"D (1150 mm) Cabinet Frame	7 (3.2)
32812-715	32812-E15	For a 46.3"D (1175 mm) Cabinet frame	7 (3.2)
32812-716	32812-E16	For a 47.2"D (1200 mm) Cabinet frame	7 (3.2)

*Note: Order Front and Side Seal Kits separately to match cabinet size. For Side Seal Kits, cabinet frame depth is the depth at the base of the cabinet frame (side panels are slightly deeper). Overall cabinet depth (door to door) is approximately 3.8" (97 mm) deeper.*



F-Series TeraFrame Gen 2 Cabinet To Floor Seal Kits



Front Seal Kit

Side Seal Kit

800-834-4969 in US & Canada • [www.chatsworth.com](http://www.chatsworth.com)



CHATSWORTH PRODUCTS

©2013 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, GlobalFrame, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, Cube-IT Plus, Evolution, OnTrac, Velocity and QuadraRack are federally registered trademarks of Chatsworth Products. eConnect and Simply Efficient are trademarks of Chatsworth Products. All other trademarks belong to their respective companies.