

Product Cut Sheet

DISTRIBUTIONFRAME CABINET SYSTEM SERVICE PARTS

Service Parts

Replace cabinet components or upgrade for new applications using the following service parts.

To identify the correct size component, locate the product part number on the label on the bottom front corner of the cabinet frame, or take overall measurements of the cabinet frame. Please contact CPI Technical Support at +86 21 6880-0266 for assistance.


Equipment Mounting Rails

Includes one pair of 19" EIA square-punched equipment mounting rails and installation hardware.

- Punched with the industry-standard EIA/ECA-310-E Universal hole pattern with 1.75" (44.45 mm) rack-mount spaces/units (U), which supports most rack-mount equipment
- All rails have slots along the sides for securing cables with Saf-T-Grip® Straps or zip ties
- The 800 mm rails also have slots along the front edge of the rails, four 5.5"H (140 mm) x 2.0"W (51 mm) cable openings and eight attachment points for cable rings (cable rings are sold separately)
- Select to match the height and width of the cabinet

DistributionFrame Equipment Mounting Rails			
Part Number - Cabinet Width		Description Height (U)	Shipping Weight lb (kg)
23.6"W 600 mm	31.5"W 800 mm		
25831-701	25831-702	For 42U Cabinets	20 (9.1)
25831-703	N/A	For 27U Cabinets	11 (5.0)

Color is Black. Shipping Weight is for the 800 mm part number.




Tempered Glass Front Door

Includes one clear tempered glass door with hinges, latch and keys.

- Door fits the front or the rear of DistributionFrame
- Select to match the height and width of the cabinet

DistributionFrame Tempered Glass Front Door			
Part Number - Cabinet Width		Description Height (U)	Shipping Weight lb (kg)
23.6"W 600 mm	31.5"W 800 mm		
25847-701	25847-702	For 42U Cabinets	43 (19.5)
25847-703	N/A	For 27U Cabinets	25 (11.3)

Color is Black. Shipping Weight is for the 800 mm part number.



Perforated Metal Front/Rear Door

Includes one perforated metal door with hinges, latch and keys.

- Door fits the front or the rear of DistributionFrame
- Select to match the height and width of the cabinet

DistributionFrame Perforated Door			
Part Number - Cabinet Width		Description Height (U)	Shipping Weight lb (kg)
23.6"W 600 mm	31.5"W 800 mm		
25822-701	25822-702	For 42U Cabinets	33 (15.0)
25822-703	N/A	For 27U Cabinets	20 (9.1)

Color is Black. Shipping Weight is for the 800 mm part number.

+86 21 6880-0266 • www.chatsworth.com.cn

+86 21 6880-0266

Shanghai Office
Pudong, Shanghai, China
www.chatsworth.com.cn



CHATSWORTH PRODUCTS

While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.
©2014 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, CPI, CPI Passive Cooling, eConnect, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-iT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products. Simply Efficient is a trademark of Chatsworth Products.
All other trademarks belong to their respective companies. Rev.3 04/14

Product Cut Sheet

DISTRIBUTIONFRAME CABINET SYSTEM SERVICE PARTS

Side Panels

Includes one solid metal side panel with latch and key.

- Side Panel fits the side of DistributionFrame
- Select to match the height and depth of the cabinet

DistributionFrame Side Panels				
Part Number - Cabinet Depth			Description Height (U)	Shipping Weight lb (kg)
23.6"D 600 mm	31.5"D 800 mm	39.4"D 1000 mm		
25827-701	25827-702	25827-703	For 42U Cabinets	20 (9.1)
N/A	25827-704	N/A	For 27U Cabinets	20 (9.1)

Color is Black. Shipping Weight is for the 800 mm part number.




Grounding Kit

Includes the hardware needed to electrically bond the side panels and doors to the cabinet frame and to bond/ground the cabinet to the Telecommunication Grounding Busbar.

- Recommended when cabinets house active electronics or shielded cable terminations
- Install before adding equipment to the cabinet
- Includes: ground block kit, ground straps and installation hardware
- Material: Aluminum, steel, copper
- Finish: Varies

Part Number	Description	Shipping Weight lb (kg)
25842-001	Grounding Kit, for 42U DistributionFrame, Black	3 (1.4)



+86 21 6880-0266 • www.chatsworth.com.cn

+86 21 6880-0266

Shanghai Office
Pudong, Shanghai, China
www.chatsworth.com.cn



CHATSWORTH PRODUCTS

While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.
©2014 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, CPI, CPI Passive Cooling, eConnect, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, GlobalFrame, Cube-iT Plus, Evolution, OnTrac, QuadraRack and Velocity are federally registered trademarks of Chatsworth Products. Simply Efficient is a trademark of Chatsworth Products.
All other trademarks belong to their respective companies. Rev.3 04/14