




Model 1006 series for HPE Aruba Access Points



PARTS LIST		
ITEM	QTY	DESCRIPTION
1	1	Right Angle Bracket
2	1	Mounting Plate
3	2	#8-32 Keps Nut
4	2 or 4	Snap Cap
5	2 or 4	Drywall Anchor

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801			
TITLE			
Model 1006 Customer Print			
SIZE		DWG NO	DATE
C		CUT-OB1006	3/7/2025
SCALE		SHEET 1 OF 8	



Configurations			
Access Point	A	B	C
1006-AP225	10.3" (262 mm)	10.3" (262 mm)	N/A
1006-AP305	8.4" (214 mm)	8.4" (214 mm)	N/A
1006-AP315	9.0" (229 mm)	9.4" (239 mm)	N/A
1006-AP325	10.3" (262 mm)	10.6" (270 mm)	8.7" (222 mm)
1006-AP335	11.0" (280 mm)	11.6" (295 mm)	9.5" (242 mm)
1006-ARAP505	8.2" (209 mm)	8.3" (211 mm)	N/A
1006-ARAP515	10.0" (254 mm)	10.3" (262 mm)	N/A
1006-ARAP535	11.5" (293 mm)	11.9" (303 mm)	N/A
1006-ARAP555	12.8" (326 mm)	13.0" (331 mm)	11.3" (288 mm)
1006-ARAP615	8.5" (216 mm)	8.5" (216 mm)	N/A
1006-ARAP635	11.1" (282 mm)	11.1" (282 mm)	9.6" (244 mm)
1006-ARAP655	12.9" (328 mm)	13.1" (333 mm)	11.3" (288 mm)
1006-ARAP735	11.8 (300 mm)	11.8 (300 mm)	10.3 (262 mm)
1006-ARAP755	14.2" (361 mm)	14.2" (361 mm)	12.7" (323 mm)

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801

TITLE

Model 1006 Customer Print

SIZE
C

DWG NO
CUT-OB1006


DATE
3/7/2025

SCALE



SHEET 2 OF 8

Model 1006 Series for Cisco Access Points

PARTS LIST		
ITEM	QTY	DESCRIPTION
1	1	Right Angle Bracket
2	1	Mounting Plate
3	2	Thumb Nut
4	2 or 4	Snap Cap
5	2 or 4	Drywall Anchor





Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801			
TITLE			
Model 1006 Customer Print			
SIZE		DWG NO	DATE
C		CUT-OB1006	3/7/2025
SCALE		SHEET 3 OF 8	



Configurations			
Access Point	A	B	C
1006-CCOAP	11.0" (280 mm)	11.0" (280 mm)	9.5" (242 mm)
1006-CCOAP3800	11.0" (280 mm)	11.0" (280 mm)	9.5" (242 mm)
1006-COAP9115	10.3" (262 mm)	10.3" (262 mm)	8.8" (224 mm)
1006-COAP9117	11.0" (280 mm)	11.0" (280 mm)	9.5" (242 mm)
1006-COAP9120	10.8" (275 mm)	11.1" (282 mm)	9.3" (237 mm)
1006-COAP9130	12.0" (305 mm)	12.0" (305 mm)	10.5" (267 mm)
1006-COAP9136	13.1" (333 mm)	13.1" (333 mm)	11.3" (288 mm)
1006-CW9162	10.5" (268 mm)	10.8" (275 mm)	9.5" (241 mm)
1006-CW9166	12.5" (318 mm)	12.5" (318 mm)	10.9" (277 mm)
1006-CW9176	11.9" (302 mm)	13.4" (340 mm)	13.3" (339 mm)
1006-CW9178	13.9" (353 mm)	13.9" (353 mm)	12.4" (315 mm)


Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801			
TITLE			
Model 1006 Customer Print			
SIZE C		DWG NO CUT-OB1006	DATE 3/7/2025
SCALE		SHEET 4 OF 8	



Other Configurations			
Access Point	A	B	C
1006-JNAP45	11.5" (293 mm)	11.9" (303 mm)	10" (254 mm)
1006-MIST43	11.0" (280 mm)	11.0" (280 mm)	9.5" (242 mm)
1006-UBI	6.9" (176 mm)	8.3" (211 mm)	N/A

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801			
TITLE			
Model 1006 Customer Print			
SIZE C		DWG NO CUT-OB1006	DATE 3/7/2025
SCALE	SHEET 5 OF 8		

1006-ANTMNT OVERVIEW






PARTS LIST		
ITEM	QTY	DESCRIPTION
1	1	Model 1006-ANTMNT
2	4	Drywall Anchor
3	4	Snap Cap
4	4	Cross Recessed Pan Head Tapping Screw - Type F - Type I


- Wieght: 3 lbs.
- Material: 8 Gauge Aluminum Base
White Powder Coat

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801			
TITLE			
Model 1006 Customer Print			
SIZE		DWG NO	DATE
C		CUT-OB1006	3/7/2025
SCALE		SHEET 6 OF 8	

1006-ANTMNT DIMENSIONS



Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801			
TITLE			
Model 1006 Customer Print			
SIZE		DWG NO	DATE
C		CUT-OB1006	3/7/2025
SCALE	SHEET 7 OF 8		



MOUNTING LEGEND

A - Single Gang

B - Double Gang

C - Square-Pattern Antennae

D - Dot Antenna

E - Cable Tie Connection

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801

TITLE

Model 1006 Customer Print

SIZE
C

DWG NO
CUT-OB1006

DATE
3/7/2025

SCALE

SHEET 8 OF 8