


1075-MPDOME & 1075-MTDOME



- NOTES:**
- Weight: 11 lbs.
  - Material: 16 Ga. Galvaneal Backbox  
14 Ga. White Powder Coated Steel Door  
18 Ga. White Powder Coated Steel Flange  
UL94-5VA Dome





- Includes:**
- (1) Enclosure and Interchangeable Door
  - (1) Swing Down Panel Mounting Bracket
  - (1) Dual Cable Egress Firestop Grommet
  - (1) 1 in. Trade Size Conduit Connector
  - (1) Speed Link Support Wire
  - (2) Keys for Lock
  - (1) Grounding Screw
  - Access Point Attachment Hardware

- UL Listed File No. E348543

|                                                            |  |              |            |
|------------------------------------------------------------|--|--------------|------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 |  |              |            |
| TITLE                                                      |  |              |            |
| Model 1075-XXXX                                            |  |              |            |
| SIZE                                                       |  | DWG NO       | DATE       |
| C                                                          |  | 1075-XXXX    | 11/10/2023 |
| SCALE                                                      |  | SHEET 1 OF 8 |            |

1075-MPDOME & 1075-MTDOME


D  
C  
B  
A



D  
C  
B  
A

|                                                            |  |              |            |
|------------------------------------------------------------|--|--------------|------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 |  |              |            |
| TITLE                                                      |  |              |            |
| Model 1075-XXXX                                            |  |              |            |
| SIZE                                                       |  | DWG NO       | DATE       |
| C                                                          |  | 1075-XXXX    | 11/10/2023 |
| SCALE                                                      |  | SHEET 2 OF 8 |            |

# 1075-MPDOME & 1075-MTDOME MOUNTING LEGEND



## MOUNTING LEGEND:

- A - Aruba Direct Mount
- B - Cisco Direct Mount
- C - Cisco Set Screws
- D - Single Gang Outlet Box
- E - Double Gang Outlet Box
- F - Direct T-Bar Mount
- G - Oberon T-Bar Accessory

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801

TITLE

Model 1075-XXXX

SIZE  
C


DWG NO  
1075-XXXX

DATE  
11/10/2023

SCALE

SHEET 3 OF 8


1075 WITH AP FACED DOORS



- NOTES:**
- Weight: 11 lbs.
  - Material: 16 Ga. Galvaneal Backbox  
14 Ga. White Powder Coated Steel Door  
18 Ga. White Powder Coated Steel Flange
- Includes:**
- (1) Enclosure and Interchangeable Door
  - (1) Dual Cable Egress Firestop Grommet
  - (1) 1 in. Trade Size Conduit Connector
  - (1) Speed Link Support Wire
  - (2) Keys for Lock
  - (1) Grounding Screw
  - Access Point Attachment Hardware
- UL Listed File No. E348543


|                                                            |              |           |            |
|------------------------------------------------------------|--------------|-----------|------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 |              |           |            |
| TITLE                                                      |              |           |            |
| Model 1075-XXXX                                            |              |           |            |
| SIZE                                                       |              | DWG NO    | DATE       |
| C                                                          |              | 1075-XXXX | 11/10/2023 |
| SCALE                                                      | SHEET 4 OF 8 |           |            |

1075 WITH AP FACED DOORS



|                                                            |  |              |            |
|------------------------------------------------------------|--|--------------|------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 |  |              |            |
| TITLE                                                      |  |              |            |
| Model 1075-XXXX                                            |  |              |            |
| SIZE                                                       |  | DWG NO       | DATE       |
| C                                                          |  | 1075-XXXX    | 11/10/2023 |
| SCALE                                                      |  | SHEET 5 OF 8 |            |


1075 WITH ANTMNT DOOR



- NOTES:**
- Weight: 11 lbs.
  - Material: 16 Ga. Galvaneal Backbox  
14 Ga. White Powder Coated Steel Door  
18 Ga. White Powder Coated Steel Flange
- Includes:**
- (1) Enclosure and Interchangeable Door
  - (1) Dual Cable Egress Firestop Grommet
  - (1) 1 in. Trade Size Conduit Connector
  - (1) Speed Link Support Wire
  - (2) Keys for Lock
  - (1) Grounding Screw
- UL Listed File No. E348543

|                                                            |              |           |            |
|------------------------------------------------------------|--------------|-----------|------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 |              |           |            |
| TITLE                                                      |              |           |            |
| Model 1075-XXXX                                            |              |           |            |
| SIZE                                                       |              | DWG NO    | DATE       |
| C                                                          |              | 1075-XXXX | 11/10/2023 |
| SCALE                                                      | SHEET 6 OF 8 |           |            |

1075 WITH ANTMNT DOOR



|                                                            |  |              |            |
|------------------------------------------------------------|--|--------------|------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 |  |              |            |
| TITLE                                                      |  |              |            |
| Model 1075-XXXX                                            |  |              |            |
| SIZE                                                       |  | DWG NO       | DATE       |
| C                                                          |  | 1075-XXXX    | 11/10/2023 |
| SCALE                                                      |  | SHEET 7 OF 8 |            |

CONFIGURATION TABLE

| Configuration Table |           |                                       |                                              |
|---------------------|-----------|---------------------------------------|----------------------------------------------|
| MODEL NUMBER        | AP DOOR   | ACCESS POINT                          | TO ORDER DOOR SEPARATELY - USE DOOR P/N ONLY |
| 1075-ANTMNT         | ANTMNT    | Antenna Mounting Door                 | 38-1075-ANTMNT                               |
| 1075-ARSC1535       | ARSC1535  | Aruba APSC35                          | 38-1075-ARSC1535                             |
| 1075-ASAV1500       | ARSV1500  | Airspan AirVelocity 1500              | 38-1075-ASAV1500                             |
| 1075-3100           | 3100      | GE Healthcare ApexPro FHAP            | 38-1075-3100                                 |
| 1075-ARAP535        | ARAP535   | Aruba AP535                           | 38-1075-ARAP535                              |
| 1075-ARAP555        | ARAP555   | Aruba AP555                           | 38-1075-ARAP555                              |
| 1075-ARAP635        | ARAP615   | Aruba AP635                           | 38-1075-ARAP635                              |
| 1075-ARAP655        | ARAP635   | Aruba AP6535                          | 38-1075-ARAP655                              |
| 1075-ARAP735        | ARAP735   | Aruba AP735                           | 38-1075-ARAP735                              |
| 1075-ARAP755        | ARAP755   | Aruba AP755                           | 38-1075-ARAP755                              |
| 1075-ARSTC330       | ARSTC330  | Arista C-330                          | 38-1075-ARST330                              |
| 1075-ARSTC360       | ARSTC360  | Arista C-360                          | 38-1075-ARSTC460                             |
| 1075-ARSTC400       | ARSTC400  | Arista C-400                          | 38-1075-ARSTC400                             |
| 1075-ARSTC460       | ARSTC460  | Arista C-460                          | 38-1075-ARSTC460                             |
| 1075-BLANK          | None      | Used as a cover / AP not been defined | 38-1075-BLANK                                |
| 1075-CCOAP3800      | CCOAP3800 | Cisco 2800, 3800 Series APs           | 38-1075-CCOAP3800                            |
| 1075-COAP4800       | COAP4800  | Cisco 4800 Series APs                 | 38-1075-COAP4800                             |
| 1075-COAP9120       | COAP9120  | Cisco 9120 Series APs                 | 38-1075-COAP9120                             |
| 1075-COAP9130       | COAP9130  | Cisco 9130 Series APs                 | 38-1075-COAP9130                             |
| 1075-COAP9136       | COAP9136  | Cisco 9136 Series APs                 | 38-1075-COAP9136                             |
| 1075-CW9166         | CW9166    | Cisco 9166 Series APs                 | 38-1075-CW9166                               |
| 1075-CW9172         | CW9172    | Cisco 9172 Series APs                 | 38-1075-CW9172                               |
| 1075-CW9176         | CW9176    | Cisco 9176 Series APs                 | 38-1075-CW9176                               |
| 1075-CW9178         | CW9178    | Cisco 9178 Series APs                 | 38-1075-CW9178                               |
| 1075-EXAP5010       | EXAP5010  | Extreme Networks AP 5010              | 38-1075-EXAP5010                             |
| 1075-EXAP5020       | EXAP5020  | Extreme Networks AP 5020              | 38-1075-EXAP5020                             |
| 1075-MPDOME         | LPDOME    | General Purpose, Works With Most APs  | 38-1075-MPDOME                               |
| 1075-MTDOME         | LTDOME    | General Purpose, Works With Most APs  | 38-1075-MTDOME                               |
| 1075-JNAP43         | MIST43    | Juniper/Mist AP 43                    | 38-1075-JNAP43                               |
| 1075-JNAP45         | JNAP45    | Juniper/Mist AP 45                    | 38-1075-JNAP45                               |
| 1075-JNAP47         | JNAP47    | Juniper/MistAP 47                     | 38-1075-JNAP47                               |
| 1075-JNBT11         | JNBT11    | Mist BT111                            | 38-1075-JNBT11                               |
| 1075-MR46           | MR45      | Meraki MR46                           | 38-1075-MR46                                 |
| 1075-MR56           | MR56      | Meraki MR56                           | 38-1075-MR56                                 |
| 1075-ND             | ND        | N/A (No Door Included)                | ND                                           |

Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801

TITLE

Model 1075-XXXX

SIZE

C

DWG NO

1075-XXXX

DATE

11/10/2023

SCALE

SHEET 8 OF 8