

CPI Solutions Guide

CABLE MANAGEMENT PRODUCTS

M Evolution® Cable Management

For Rack Systems. For high-density applications; features moveable mid-sections, cable guides and doors with two-point latches.

35511-703	g1 Single-Sided Vertical, 7'H x 6"W x 13.2"D (2.1 m x 150 mm x 335 mm), Black
35512-703	g1 Single-Sided Vertical, 7'H x 8"W x 13.2"D (2.1 m x 200 mm x 335 mm), Black
35514-703	g1 Single-Sided Vertical, 7'H x 12"W x 13.2"D (2.1 m x 300 mm x 335 mm), Black
35521-703	g2 Double-Sided Vertical, 7'H x 6"W x 24.5"D (2.1 m x 150 mm x 622 mm), Black
35522-703	g2 Double-Sided Vertical, 7'H x 8"W x 24.5"D (2.1 m x 200 mm x 622 mm), Black
35524-703	g2 Double-Sided Vertical, 7'H x 12"W x 24.5"D (2.1 m x 300 mm x 622 mm), Black
35571-703	g3 Combination Vertical, 7'H x 6"W x 20.2"D (2.1 m x 150 mm x 513 mm), Black
35572-703	g3 Combination Vertical, 7'H x 8"W x 20.2"D (2.1 m x 200 mm x 513 mm), Black
35574-703	g3 Combination Vertical, 7'H x 12"W x 20.2"D (2.1 m x 300 mm x 513 mm), Black
35441-701	Horizontal, Single-Sided, 1U x 19"EIA x 8.2"D (208 mm), Black
35441-702	Horizontal, Single-Sided, 2U x 19"EIA x 8.2"D (208 mm), Black
35441-703	Horizontal, Single-Sided, 3U x 19"EIA x 8.2"D (208 mm), Black

Other heights and widths available.

O Velocity™ Cable Management

For Rack Systems. Cost-effective solution; features snap-together design, cable guides and snap on covers.

13902-703	Single-Sided Vertical, 80.5"H x 6"W x 9.8"D (2045 mm x 152 mm x 249 mm), Black
13904-703	Single-Sided Vertical, 80.5"H x 10"W x 10.3"D (2045 mm x 254 mm x 262 mm), Black
13905-703	Single-Sided Vertical, 80.5"H x 12"W x 10.4"D (2045 mm x 305 mm x 264 mm), Black
13912-703	Double-Sided Vertical, 80.5"H x 6"W x 16.6"D (2045 mm x 152 mm x 422 mm), Black
13914-703	Double-Sided Vertical, 80.5"H x 10"W x 17.5"D (2045 mm x 254 mm x 445 mm), Black
13915-703	Double-Sided Vertical, 80.5"H x 12"W x 17.8"D (2045 mm x 305 mm x 446 mm), Black
13930-701	Horizontal, Single-Sided, 1U x 19"EIA x 5.9"D (150 mm), Black
13930-702	Horizontal, Single-Sided, 2U x 19"EIA x 5.9"D (150 mm), Black
13930-703	Horizontal, Single-Sided, 3U x 19"EIA x 5.9"D (150 mm), Black

Other heights and widths available.

G Master Cabling Section (MCS)

For Rack Systems. Features cable guides and hinged latching covers.

30092-703	Single-Sided, 7'H x 6"W x 8.08"D (2.1 m x 150 mm x 205.2 mm)
30093-703	Single-Sided, 7'H x 10"W x 8.08"D (2.1 m x 250 mm x 205.2 mm)
30095-703	Double-Sided, 7'H x 6"W x 16.15"D (2.1 m x 150 mm x 410.2 mm)
30096-703	Double-Sided, 7'H x 10"W x 16.15"D (2.1 m x 250 mm x 410.2 mm)
40092-703	Single-Sided, Extended Fingers, 7'H x 6"W x 10.62"D (2.1 m x 150 mm x 269.7 mm)
40093-703	Single-Sided, Extended Fingers, 7'H x 10"W x 10.62"D (2.1 m x 250 mm x 269.7 mm)
40095-703	Double-Sided, Extended Fingers, 7'H x 6"W x 21.23"D (2.1 m x 150 mm x 539.2 mm)
40096-703	Double-Sided, Extended Fingers, 7'H x 10"W x 21.23"D (2.1 m x 250 mm x 539.2 mm)

Color listed is black. Other heights and finishes available.

H Combination Cabling Section (CCS)

For Rack Systems. Double-Sided combination cable manager with cable guides and hinged latching covers.

30161-703	7'H x 3.65"W x 12.24"D (2.1 m x 92.7 mm x 310.8 mm)
30162-703	7'H x 6"W x 12.24"D (2.1 m x 150 mm x 310.8 mm)
30163-703	7'H x 10"W x 12.24"D (2.1 m x 250 mm x 310.8 mm)
40098-703	Extended Fingers, 7'H x 6"W x 14.94"D (2.1 m x 150 mm x 379.5 mm)
40099-703	Extended Fingers, 7'H x 10"W x 14.94"D (2.1 m x 250 mm x 379.5 mm)
40100-703	Extended Fingers, 7'H x 12"W x 14.94"D (2.1 m x 300 mm x 379.5 mm)

Color listed is black. Other heights and finishes available.

Vertical Cable Management for Cabinets

Vertical Cable Managers for 45U F-Series TeraFrame® Cabinet System. Extended Finger options available. Color is black.

34421-C01	Single-Sided, 1.9"W x 10.5"D (48 mm x 267 mm), for 23.6"W (600 mm) cabinets
35090-C05	Single-Sided, 3.1"W x 11.6"D (79 mm x 295 mm), for 27.6"W (700 mm) cabinets
35095-C05	Single-Sided, 5.0"W x 11.6"D (127 mm x 295 mm), for 31.5"W (800 mm) cabinets

Cable Lashing Bar/Bracket for 42U F-Series TeraFrame® HD Cabinet System. Color is black.

16272-C02	Cable Lashing Bar, 1.5"W (38 mm) for 42U
-----------	--

Fiber Managers for 45U N-Series TeraFrame® Network Cabinet. Color is black.

34719-C05	Fiber Trunk Cable Manager, 9.7"D (246 mm) for 31.5"W (800 mm) cabinets
34707-C05	Vertical Furcation Bracket, 5.1"D (130 mm) for 31.5"W (800 mm) cabinets
34701-C05	Universal Accessory Rail, for 31.5"W (800 mm) cabinets

34716-C02 Swivel Cable Spool, for Universal Accessory Rail, pack of six

Cable Ring Kit for GlobalFrame™ Cabinet System. Color is black.



25104-001	Eight Rings, 1.7"W x 5.0"D (43 mm x 127 mm) for 23.6"W (600 mm) cabinets
25105-001	Eight Rings, 4.5"W x 9.8"D (114 mm x 249 mm) for 29.5"W (750 mm) cabinets
25106-001	Eight Rings, 5.5"W x 9.8"D (140 mm x 249 mm) for 31.5"W (800 mm) cabinets

Cable Ring Manager for 45U M-Series MegaFrame® Cabinets. Color is black.

12465-707	2.3"W x 5.5"D (58 mm x 140 mm) for 27.3"W (694 mm) cabinets
-----------	---

Cable Ring Manager for 43U C-Series SlimFrame® Cabinets. Color is black.

11809-700	Narrow, 1.4"W x 4.1"D (36 mm x 105 mm) for 24"W (610 mm) cabinet
-----------	--



For Additional Product Information, see tables included in this document:

- A - F-Series TeraFrame® Cabinet System
- B - F-Series TeraFrame® Cabinet System with Vertical Exhaust Duct
- C - F-Series TeraFrame® HD Cabinet System
- D - N-Series TeraFrame® Network Cabinet
- E - GlobalFrame™ Cabinet System
- F - GlobalFrame™ Cabinet System with Vertical Exhaust Duct
- G - MCS Master Cabling Section
- H - CCS Combination Cabling Section
- I - Two-Post Rack System
- J - Seismic Frame® Two-Post Rack
- K - Adjustable QuadraRack®
- L - Adjustable Rail ServerRack
- M - Evolution® Cable Management
- N - Velocity™ Standard Pack
- O - Velocity™ Cable Management
- P - Cube-iT PLUS® Cabinet System
- Q - ThinLine II Wall-Mount Cabinet
- R - Wall-Mount Rack Systems
- S - Cable Management Rings
- T - Telecommunications Grounding Busbar
- U - Cable Runway
- V - Raised Floor Enclosures
- W - Zone Cabling Ceiling Enclosures
- X - Wireless Enclosures
- Y - OnTrac® Wire Mesh Cable Tray

CP CHATSWORTH PRODUCTS, INC. | Optimize. Store. Secure.

+1-800-834-4969 • www.chatsworth.com • techsupport@chatsworth.com

Reproduction in any format, printed or electronic, without written consent is strictly prohibited.

©2011 Chatsworth Products, Inc. All rights reserved. CPI, CPI Passive Cooling, MegaFrame, Saf-T-Grip, Seismic Frame, SlimFrame, TeraFrame, Cube-iT Plus, Evolution, OnTrac, and QuadraRack are federally registered trademarks of Chatsworth Products, Inc. GlobalFrame, Simply Efficient and Velocity are trademarks of Chatsworth Products, Inc. All other trademarks belong to their respective companies. Rev 6 01/11 MKT-60020-138

RACK SYSTEMS	
I Two-Post Rack Systems	
<i>High strength, fixed two-post racks with small footprints.</i>	
48353-703	Universal Rack, 7'H (2.1 m) x 19"EIA x 15"D (381 mm), 45U, UL Listed, Supports 1500 lb (680 kg)
55053-703	Standard Rack, 7'H (2.1 m) x 19"EIA x 15"D (381 mm), 45U, UL Listed, Supports 1000 lb (453.6 kg)
66383-703	Standard Rack, 7'H (2.1 m) x 23"W x 18"D (381 mm), 45U, UL Listed, Supports 1000 lb (453.6 kg)
<i>Other heights, colors and styles available.</i>	
Shelves and Trays for Rack Systems	
10758-701	Small Peripheral Rack, 19"W x 2U x 10"D (254 mm), Supports 50 lb (22.7 kg)
11054-719	26" Deep Shelf, 19"W x 5U x 26"D (660 mm), Supports 150 lb (68.0 kg)
11164-719	Heavy-Duty Equipment Shelf, 19"W x 5U x 20"D (504 mm), Supports 200 lb (90.7 kg)
11231-719	Double-Sided Vented Shelf, 19"W x 4U x 21.75"D (552.5 mm), Supports 100 lb (45.4 kg)
11245-719	Adjustable Monitor Shelf, 19"W x 3U x 18"D (460 mm), Supports 110 lb (49.9 kg)
11359-719	Low Profile Shelf, Vented, 19"W x 2U x 20"D (504 mm), Supports 60 lb (27.2 kg)
13082-719	Lockable Storage Drawer, 19"W x 2U x 20"D (510 mm), Supports 100 lb (45.4 kg)
40074-700	Single-Sided Shelf, 19"W x 3U x 15"D (380 mm), Supports 50 lb (22.7 kg)
40117-719	Single-Sided Vented Shelf, 19"W x 3U x 15"D (380 mm), Supports 50 lb (22.7 kg)
40108-719	Double-Sided Shelf, 19"W x 4U x 21.75"D (552.5 mm), Supports 100 lb (45.4 kg)
2-Post Rack System Accessories	
10629-119	Raised Floor Rack Support, 10"-16"H (250 mm to 410 mm), 19"W x 15"D (381 mm)
40604-003	Rack Installation Kit, Concrete Floor, (4) 1/2" Thread Components
12091-719	Equipment Tie-Down Bracket, 19"W, for Siesmic Areas
12752-719	anyServer Bracket, 19"W x 2U, 9"-13"D (230 mm - 330 mm), Supports 120 lb (54.4 kg)
J Seismic Frame™ Two-Post Rack	
<i>NEBS Zone 4 with 1000 lb (453.6 kg) load rating for siesmic areas.</i>	
13853-703	7'H (2.1 m) x 19"EIA x 15"D, (380 mm) base, 44U, Supports 1000 lb (453.6 kg)
13883-703	7'H (2.1 m) x 23"W x 15"D (380 mm) base, 44U, Supports 1000 lb (453.6 kg)
13704-703	Vertical Cabling Section, Double-Sided, 6"W (150 mm)
13702-001	Seismic Frame Two-Post Rack Concrete Floor Anchor Kit
<i>Includes threaded zinc rails. Other styles available.</i>	
K Adjustable QuadraRack® (AQR)	
<i>Threaded equipment mounting rails for network switches and shelves.</i>	
15216-703	7'H (2.1 m) x 19"EIA, 22.6"D - 28.5"D (575 mm - 725 mm), 45U, Supports 2000 lb (907.2 kg)
15217-703	7'H (2.1 m) x 19"EIA, 29.5"D - 35.4"D (750 mm - 900 mm), 45U, Supports 2000 lb (907.2 kg)
15218-703	7'H (2.1 m) x 19"EIA, 36.4"D - 42.3"D (925 mm - 1075 mm), 45U, Supports 2000 lb (907.2 kg)
<i>Other sizes available. Square-punched equipment mounting rails also available.</i>	
Adjustable QuadraRack® (AQR) Accessories	
15255-702	Vented Shelf, 19"W x 1U x 20.7"D (526.5 mm), Supports 200 lb (90.7 kg)
15255-703	Vented Shelf, 19"W x 1U x 27.6"D (701.6 mm), Supports 200 lb (90.7 kg)
15255-704	Vented Shelf, 19"W x 1U x 34.5"D (876.5 mm), Supports 200 lb (90.7 kg)
15235-705	Equipment Support Rails, 35.4"D - 39.3"D (900 mm - 1000 mm), Supports 200 lb (90.7 kg)
15235-706	Equipment Support Rails, 40.3"D - 44.2"D (1025 mm - 1125 mm), Supports 200 lb (90.7 kg)
15205-701	Mounting Bracket, for 6"W - 24"W (150 mm - 600 mm), Cable Runway
<i>Other sizes and styles available.</i>	
L Adjustable Rail ServerRack (ARSR)	
<i>Square-punched equipment mounting rails use cage nuts to mount a variety of server equipment.</i>	
15253-703	7'H (2.1 m) x 19"EIA x 23.6"D (600 mm), 45U, 2200 lb (1000 kg)
15254-703	7'H (2.1 m) x 19"EIA x 35.4"D (900 mm), 45U, 2200 lb (1000 kg)
<i>Other sizes available. threaded equipment mounting rails also available.</i>	
Adjustable Rail ServerRack (ARSR) Accessories	
15270-702	Adjustable Rail ServerRack Side Panel, 7'H x 23.6"D (2.1 m x 600 mm), Black
15285-701	Equipment Support Rails, for 23.6"D (600 mm) Racks
N Velocity™ Standard Pack	
<i>Easy to use solution for managing equipment and cabling at the cross-connect.</i>	
57011-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Single-Sided Vertical Cable Manager 3.6"W (91 mm); and (1) Rack Installation Kit for Concrete Floors, Black
57012-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Double-Sided Vertical Cable Manager 3.6"W (91 mm); and (1) Rack Installation Kit for Concrete Floors, Black
57013-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Single-Sided Vertical Cable Manager 6.0"W (150 mm); and (1) Rack Installation Kit for Concrete Floors, Black
57014-703	(1) Standard Rack, 45U x 19"EIA; (1) Velocity Double-Sided Vertical Cable Manager 6.0"W (150 mm); and (1) Rack Installation Kit for Concrete Floors, Black

+1-800-834-4969 • www.chatsworth.com • techsupport@chatsworth.com

CABINET & ENCLOSURE SYSTEMS	
A F-Series TeraFrame® Cabinet System	
<i>Stores servers in enterprise data centers, computer rooms and network facilities.</i>	
FF1L-113B-C42	83.5"H x 23.6"W x 41.3"D (2121 mm x 600 mm x 1050 mm), 45U, Supports 2500 lb (1134 kg)
FF1U-113B-C42	83.5"H x 23.6"W x 47.2"D (2121 mm x 600 mm x 1200 mm), 45U, Supports 2500 lb (1134 kg)
FF2L-113B-C22	83.5"H x 27.6"W x 41.3"D (2121 mm x 700 mm x 1050 mm), 45U, Supports 2000 lb (907.2 kg)
FF2U-113B-C22	83.5"H x 27.6"W x 47.2"D (2121 mm x 700 mm x 1200 mm), 45U, Supports 2000 lb (907.2 kg)
FF3U-113B-C22	83.5"H x 31.5"W x 47.2"D (2121 mm x 800 mm x 1200 mm), 45U, Supports 2000 lb (907.2 kg)
<i>Color is Black. Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options available.</i>	
B F-Series TeraFrame® Cabinet System with Vertical Exhaust Duct	
<i>Isolate and remove hot exhaust air from the cabinet to an overhead return.</i>	
FF1U-111B-C52	83.5"H x 23.6"W x 47.2"D (2121 mm x 600 mm x 1200 mm), 45U, with 20" - 34"H (508 mm - 863 mm) Vertical Exhaust Duct, Supports 2500 lb (1134 kg)
FF1U-111B-C62	83.5"H x 23.6"W x 47.2"D (2121 mm x 600 mm x 1200 mm), 45U, with 34" - 60"H (863 mm - 1523 mm) Vertical Exhaust Duct, Supports 2500 lb (1134 kg)
<i>Color is Black. Cabinet includes top panel with duct, two side panels, perforated front door and a solid rear door. Order thermal, power and cable management accessories separately. Other options available.</i>	
C F-Series TeraFrame® HD Cabinet System	
<i>Safe transportation of up to 3000 lb (1360 kg) of pre-installed equipment.</i>	
FHD-C1M-113B-C42	82.5"H x 23.6"W x 42.3"D (2096 mm x 600 mm x 1075 mm), 42U, Supports 3000 lb (1360 kg)
FHD-C1U-113B-C42	82.5"H x 23.6"W x 47.2"D (2096 mm x 600 mm x 1200 mm), 42U, Supports 3000 lb (1360 kg)
<i>Color is Black. Cabinet includes a top panel, two side panels, perforated front and rear doors, casters and is shipped on a shock pallet with a reusable carton. Order accessories separately.</i>	
F F-Series TeraFrame® HD Cabinet System with Vertical Exhaust Duct (not shown)	
<i>Isolate and remove hot exhaust air from the cabinet to an overhead return.</i>	
FHD-C1U-111B-C52	82.5"H x 23.6"W x 47.2"D (2096 mm x 600 mm x 1200 mm), 42U, with 20" - 34"H (508 mm - 863 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg)
FHD-C1M-111B-C62	82.5"H x 23.6"W x 47.2"D (2096 mm x 600 mm x 1200 mm), 42U, with 34" - 60"H (863 mm - 1523 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg)
<i>Color is Black. Cabinet includes a top panel with duct, two side panels, perforated front door, a solid rear door, and casters and is shipped on a shock pallet with a reusable carton. Order accessories separately.</i>	
D N-Series TeraFrame™ Network Cabinet	
<i>Offset doors and side panels and an internal duct manage side-to-side airflow for network switches and high-density cabling.</i>	
NF2K-113C-C42	83.5"H x 31.5"W x 40.4"D, 45U, (2122 mm x 800 mm x 1025 mm), Supports 2500 lb (1134 kg), for Cisco® Catalyst 6506, 6509, 6513 Switches and MDS 9509 Director
NF3K-113C-C42	83.5"H x 31.5"W x 40.4"D, 45U, (2122 mm x 800 mm x 1025 mm), Supports 2500 lb (1134 kg), for Cisco® MDS 9513 Director
NF5U-143C-C42	83.5"H x 40.4"W x 47.2"D, 45U, (2122 mm x 1016 mm x 1200 mm), Supports 2500 lb (1134 kg), for Cisco® Nexus 7018 Switch
NF0U-113C-C42	83.5"H x 31.5"W x 47.2"D, 45U, (2122 mm x 800 mm x 1200 mm), Supports 2500 lb (1134 kg), for Cisco® Nexus 7010 Switches, fiber enclosures (no duct)
<i>Color is Black. Cabinet includes top panel, two side panels, side airflow duct and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options available.</i>	
E GlobalFrame™ Cabinet System	
<i>Cost effective, general purpose cabinet for computer and equipment rooms.</i>	
GF-1A320	79.3"H x 23.6"W x 41.3"D, 42U, (2013 mm x 600 mm x 1050 mm), Supports 3000 lb (1360 kg)
GF-1A420	79.3"H x 23.6"W x 47.2"D, 42U, (2013 mm x 600 mm x 1200 mm), Supports 3000 lb (1360 kg)
GF-1B320	79.3"H x 29.5"W x 41.3"D, 42U, (2013 mm x 750 mm x 1050 mm), Supports 3000 lb (1360 kg)
GF-1B420	79.3"H x 29.5"W x 47.2"D, 42U, (2013 mm x 750 mm x 1200 mm), Supports 3000 lb (1360 kg)
GF-1C220	79.3"H x 31.5"W x 39.4"D, 42U, (2013 mm x 800 mm x 1000 mm), Supports 3000 lb (1360 kg)
GF-1C420	79.3"H x 31.5"W x 47.2"D, 42U, (2013 mm x 800 mm x 1200 mm), Supports 3000 lb (1360 kg)
<i>Color is Black. Cabinet includes top panel, two side panels, perforated front and rear doors and casters. Order thermal, power and cable management accessories separately. Other options available.</i>	
F GlobalFrame™ Cabinet System with Vertical Exhaust Duct	
<i>Isolate and remove hot exhaust air from the cabinet to an overhead return.</i>	
GF-1A421	79.3"H x 23.6"W x 47.2"D, 42U, (2013 mm x 600 mm x 1200 mm), with 20" - 34"H (508 mm - 863 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg)
GF-1A422	79.3"H x 23.6"W x 47.2"D, 42U, (2013 mm x 600 mm x 1200 mm), with 34" - 60"H (863 mm - 1523 mm) Vertical Exhaust Duct, Supports 3000 lb (1360 kg)
<i>Color is Black. Cabinet includes top panel with duct, two side panels, perforated front door, solid rear door and casters. Order thermal, power and cable management accessories separately. Other options available.</i>	

+1-800-834-4969 • www.chatsworth.com • techsupport@chatsworth.com

CABINET & ENCLOSURE SYSTEMS	
M-Series MegaFrame® Cabinet System (not shown)	
<i>General purpose, light weight aluminum cabinet delivers partially assembled for easier handling.</i>	
M1033-741	84"H x 27.3"W x 32.1"D (2130 mm x 694 mm x 816 mm), 45U, Supports 2000 lb (907.2 kg)
M1053-741	84"H x 27.3"W x 38.1"D (2130 mm x 694 mm x 968 mm), 45U, Supports 2000 lb (907.2 kg)
M1043-741	84"H x 27.3"W x 41.1"D (2130 mm x 694 mm x 1045 mm), 45U, Supports 2000 lb (907.2 kg)
<i>Color is Black. Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options available.</i>	
C-Series SlimFrame® Cabinet System (not shown)	
<i>Minimal 24"W (600 mm) footprint for use on raised floors; cable management included.</i>	
C1033-741	84"H x 24"W x 32.1"D (2130 mm x 610 mm x 816 mm), 43U, Supports 2000 lb (907.2 kg)
C1053-741	84"H x 24"W x 38.1"D (2130 mm x 610 mm x 968 mm), 43U, Supports 2000 lb (907.2 kg)
<i>Color is Black. Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options available.</i>	
Seismic Frame® Cabinet System (not shown)	
<i>Steel inner-frame; Rated Zone 4 compliant to Bellcore GR-63-CORE for NEBS, Section 4.4.1.1</i>	
11972-742	84"H x 27.3"W x 38.1"D (2130 mm x 694 mm x 968 mm), 43U, Supports 800 lb (362.9 kg)
<i>Color is Black. Cabinet includes top panel, two side panels and perforated front and rear doors. Order thermal, power and cable management accessories separately. Other options available.</i>	
Thermal Management Accessories or Cabinet & Enclosure Systems	
<i>CPI thermal management accessories prevent re-circulation of air within the cabinet.</i>	
34521-C05	Air Dam Kit for 23.6"W (600 mm) x 45U F-Series TeraFrame Cabinet
34522-C05	Air Dam Kit for 27.6"W (700 mm) x 45U F-Series TeraFrame Cabinet
34523-C05	Air Dam Kit for 31.5"W (800 mm) x 45U F-Series TeraFrame Cabinet
16270-C02	Air Dam Kit for 23.6"W (600 mm) x 42U F-Series TeraFrame HD Cabinet
13336-710	Air Dam Kit for M-Series MegaFrame Cabinet
25250-700	Rail Seal Kit for 29.5"W (750 mm) x 42U GlobalFrame Cabinet
25252-700	Rail Seal Kit for 31.5"W (800 mm) x 42U GlobalFrame Cabinet
34537-000	Snap-In Filler Panel, 1U x 19"EIA
34538-000	Snap-In Filler Panel, 2U x 19"EIA
<i>Color is Black. Add Air Dam Kit/Rail Seal Kit and Snap-In Filler Panels to cabinets to block airflow around rack-mount equipment. Bottom Panels and Fan Kits are also available.</i>	
Accessories for Cabinet & Enclosure Systems	
<i>See Page 1 for Cable Management Accessories.</i>	
13517-701	Rack-Mount Cable Shelf, 1U x 19"W
11913-719	Sliding Vented Shelf, 19"W x 2U, 32"D (810mm), Supports 160 lb (72.6 kg)
13083-719	Lockable Storage Drawer, 19"W x 3U x 20"D (510 mm), Supports 100 lb (45.4 kg)
12700-719	Extra Heavy-Duty Sliding Shelf, 19"W x 2U, 26"D (660 mm), Supports 300 lb (136.1 kg)
12610-719	Low Profile Fixed Vented Shelf, 19"W x 1U, 20" - 36"D (510 mm - 910 mm), Supports 100 lb (45.4 kg)
35051-C01	Caster Kit for F-Series TeraFrame Cabinet, Set of four
34628-C01	Caster Kit for N-Series TeraFrame Network Cabinet, Set of four
13203-001	Caster Kit for MegaFrame Cabinet
13204-001	Caster Kit for SlimFrame and Co-Location Cabinets
<i>Other accessory options available.</i>	
Installation Hardware for Cabinet & Enclosure Systems	
12637-001	Equipment Mounting Hardware, M6, Pack of 25
12639-019	Equipment Mounting Hardware, #12-24, Pack of 25
40604-003	Universal Rack/Cabinet Installation Kit, Concrete Floor, 1/2" Hardware
Keyboard, Video and Mouse (KVM Switches)	
<i>Share a common set of peripherals with all rack-mount equipment and for access equipment remotely over an IP connection through a KVM switch. Contact CPI Technical Support for configuration assistance.</i>	
Electronic Locking System (ELS)	
<i>Upgrade to electronic locks on F-Series and N-Series TeraFrame Cabinets for automated and remote access control. Contact CPI Technical Support for configuration assistance.</i>	
Power Distribution Units (PDUs)	
<i>Single-phase and three-phase, basic, metered, IP monitored and IP controlled vertical and rack-mount PDUs are available for all cabinet systems. Contact CPI Technical Support for configuration assistance.</i>	
Environmental Monitoring Solutions	
<i>Provide critical automated environmental monitoring, logging & reporting within cabinets and equipment rooms. Contact CPI Technical Support for configuration assistance.</i>	

WALL-MOUNT SYSTEMS	
P CUBE-iT PLUS® Cabinet System	
<i>Wall-mounted equipment storage with easy access to the rear of equipment. 60"H (1520 mm) and 72"H (1830 mm) are wall mounted and floor supported. Color is black.</i>	
11890-724	24"H (610 mm) x 19"EIA x 18"D (460 mm), 12U, Supports 200 lb (90.7 kg)
11840-724	24"H (610 mm) x 19"EIA x 24"D (610 mm), 12U, Supports 200 lb (90.7 kg)
11890-736	36"H (910 mm) x 19"EIA x 18"D (460 mm), 18U, Supports 200 lb (90.7 kg)
11840-736	36"H (910 mm) x 19"EIA x 24"D (610 mm), 18U, Supports 200 lb (90.7 kg)
11890-748	48"H (1220 mm) x 19"EIA x 18"D (460 mm), 26U, Supports 200 lb (90.7 kg)
11840-748	48"H (1220 mm) x 19"EIA x 24"D (610 mm), 26U, Supports 200 lb (90.7 kg)
13492-760	60"H (1520 mm) x 19"EIA x 24"D (610 mm), 33U, Supports 1000 lb (453.6 kg)
13493-760	60"H (1520 mm) x 19"EIA x 30"D (760 mm), 33U, Supports 1000 lb (453.6 kg)
13492-772	72"H (1830 mm) x 19"EIA x 24"D (610 mm), 40U, Supports 1000 lb (453.6 kg)
13493-772	72"H (1830 mm) x 19"EIA x 30"D (760 mm), 40U, Supports 1000 lb (453.6 kg)
CUBE-iT PLUS® Cabinet System Accessories	
12803-701	Light for CUBE-iT, 115 VAC, 8 Watts, 6'L cord with NEMA 5-15P plug
12804-701	Fan Kit, 115 VAC, 100 CFM, Black
12805-701	Filter Kit for Fan
12796-501	45° Mounting Bracket, 3U, for back of cabinet
13285-501	90° Mounting Bracket, 2U, for back of cabinet
12820-703	Power Strip, Surge-Protected, 115V, 15 A, 8 Outlets, 10'L cord, NEMA 5-15P plug
13485-760	Vertical Cable Manager for 60"H (1520 mm) Cabinet
13485-772	Vertical Cable Manager for 72"H (1830 mm) Cabinet
<i>Other CUBE-iT cabinets and accessories available.</i>	
Q ThinLine II Wall-Mount Cabinet System	
<i>Space saving wall-mounted cabinet. Color is black.</i>	
13050-711	26"H x 26"W x 5"D (660 mm x 660 mm x 130 mm), 2U, Supports 100 lb (45.4 kg)
13050-712	26"H x 26"W x 8.5"D (660 mm x 660 mm x 216 mm), 4U, Supports 100 lb (45.4 kg)
13050-713	26"H x 26"W x 12"D (660 mm x 660 mm x 300 mm), 6U, Supports 100 lb (45.4 kg)
13050-721	36"H x 26"W x 5"D (910 mm x 660 mm x 130 mm), 2U, Supports 100 lb (45.4 kg)
13050-722	36"H x 26"W x 8.5"D (910 mm x 660 mm x 216 mm), 4U, Supports 100 lb (45.4 kg)
13050-723	36"H x 26"W x 12"D (910 mm x 660 mm x 300 mm), 6U, Supports 100 lb (45.4 kg)
ThinLine II Wall-Mount Cabinet System Accessories	
13051-001	Intelligent Fan Kit, 4U & 6U Cabinet
13051-002	Intelligent Fan Kit, 2U Cabinet
R Fixed Wall-Mount Equipment Rack	
11960-718	24.5"H (622 mm) x 19"W x 18"D (460 mm), 13U, Supports 200 lb (90.7 kg)
11961-718	38.5"H (978 mm) x 19"W x 18"D (460 mm), 21U, Supports 200 lb (90.7 kg)
11962-718	73.5"H (1867 mm) x 19"W x 18"D (460 mm), 41U, Supports 200 lb (90.7 kg)
<i>Color is Black. 12" Deep Rack (-X12), 6" Deep Rack (-X06).</i>	
R Standard Swing Gate Rack	
11790-718	24.5"H (622 mm) x 19"W x 18"D (460 mm), 13U, Supports 100 lb (45.4 kg)
11791-718	38.5"H (978 mm) x 19"W x 18"D (460 mm), 21U, Supports 100 lb (45.4 kg)
11792-718	73.5"H (1867 mm) x 19"W x 18"D (460 mm), 41U, Supports 100 lb (45.4 kg)
<i>Color is Black. 12" Deep Rack (-X12), 25" Deep Rack (-X25). 23"W also available.</i>	
Heavy-Duty Wall-Mount Equipment Rack (not shown)	
15320-718	38.5"H (978 mm) x 19"W x 18"D (460 mm), 20U, Supports 350 lb (158.8 kg)
15321-718	73.5"H (1867 mm) x 19"W x 18"D (460 mm), 40U, Supports 350 lb (158.8 kg)
<i>Color is Black. 24" Deep Rack (-X24).</i>	
EasySwing Wall-Mount Rack (not shown)	
<i>Easy to ship, inventory and install — ships flat, folds open to mount on the wall.</i>	
13602-708	24.5"H (622 mm) x 19"W x 8"D (200 mm), 11U, Supports 85 lb (38.6 kg)
13604-708	38.5"H (978 mm) x 19"W x 8"D (200 mm), 19U, Supports 85 lb (38.6 kg)
13608-712	51.5"H (1308 mm) x 19"W x 12"D (300 mm), 26U, Supports 85 lb (38.6 kg)
<i>Color is Black. 12" Deep Rack (-X12), 18" Deep Rack (-X18) and 25" Deep Rack (-X25).</i>	
Universal Swing Gate Rack (not shown)	
<i>Full-feature swing gate rack with built-in cable management capabilities. Color is black.</i>	
11347-719	35"H (890 mm) x 19"W x 12"D (300 mm), 20U, Supports 150 lb (68.0 kg)
11348-719	35"H (890 mm) x 19"W x 18"D (460 mm), 20U, Supports 150 lb (68.0 kg)
Wall-Mount Rack System Accessories	
11799-001	Vertical Cable Management Rings, Set of 6, Black Only
11583-719	