

Determine your power needs using the table below. Contact CPI Technical Support for unique requirements not shown or to order a product.

- | | | | | |
|---|---|--|---|--|
| <input type="checkbox"/> Basic
No Monitoring or Switching | <input type="checkbox"/> Monitored
PDU Monitoring | <input type="checkbox"/> Monitored Pro
PDU and Outlet Monitoring | <input type="checkbox"/> Switched
Outlet Switching and PDU Monitoring | <input type="checkbox"/> Switched Pro
Outlet Switching, PDU Monitoring and Outlet Monitoring |
|---|---|--|---|--|

1 Determine your power input requirements. (Input Plug Type, Voltage, Phase, Amperage, Kilowatts)

North America


- | | |
|--|--|
| <input type="checkbox"/> C20 Inlet (100-240V Single-Phase Input, 20A North America 1.9/3.3 kW) | <input type="checkbox"/> NEMA L15-30 Plug (208V Three-Phase Input, 30A, 8.6 kW) |
| <input type="checkbox"/> NEMA L5-20 Plug (120V Single-Phase Input, 20A, 1.9 kW) | <input type="checkbox"/> NEMA L21-20 Plug (120/208V Three-Phase Input, 20A, 5.7 kW) |
| <input type="checkbox"/> NEMA L5-30 Plug (120V Single-Phase Input, 30A, 2.8 kW) | <input type="checkbox"/> NEMA L21-30 Plug (120/208V Three-Phase Input, 30A, 8.6 kW) |
| <input type="checkbox"/> NEMA L6-20 Plug (208V Single-Phase Input, 20A, 3.3 kW) | <input type="checkbox"/> CS8365C Plug (208V Three-Phase Input, 35A, 9.9 kW) |
| <input type="checkbox"/> NEMA L6-30 Plug (208V Single-Phase Input, 30A, 4.9 kW) | <input type="checkbox"/> CS8365C Plug (208V Three-Phase Input, 50A, 14.3 kW) |
| <input type="checkbox"/> NEMA L14-20 Plug (120/208V Single-Phase Input, 20A, 3.3 kW) | <input type="checkbox"/> IEC 60A 3P+E Plug (208V Three-Phase Input, 60A, 17.2 kW) |
| <input type="checkbox"/> NEMA L14-30 Plug (120/208V Single-Phase Input, 30A, 4.9 kW) | <input type="checkbox"/> NEMA L22-20 Plug (240/415V Three-Phase Input, 20A, 11.4 kW) |
| <input type="checkbox"/> NEMA L15-20 Plug (208V Three-Phase Input, 20A, 5.7 kW) | <input type="checkbox"/> NEMA L22-30 Plug (240/415V Three-Phase Input, 30A, 17.2 kW) |

Outside North America

- C20 Inlet (100-240V Single-Phase Input, 16A Outside North America 3.6 kW)
- IEC 16A 2P+E Plug (220-240V Single-Phase Input, 16A, 3.6 kW)
- IEC 32A 2P+E Plug (220-240V Single-Phase Input, 32A 7.3 kW)
- IEC 16A 3P+N+E Plug (220-240/380-415V Three-Phase Input, 16A 11.0 kW)
- IEC 32A 3P+N+E Plug (220-240/380-415V Three-Phase Input, 32A, 22.1 kW)

2 Determine your output requirements by identifying type and number of outlets. (Number, Output Plugs, Output Voltage)

- | | | | |
|--|--|--|---|
| <input type="checkbox"/> (24) 5-20R (120 V) | <input type="checkbox"/> (12) C13 (12) C19 (208V)* | <input type="checkbox"/> (24) C13 (6) C19 (208V) | <input type="checkbox"/> (36) C13 (6) C19 Outlets (208V)* |
| <input type="checkbox"/> (36) 5-20R (120V) | <input type="checkbox"/> (12) C13 (18) C19 (208V)* | <input type="checkbox"/> (24) C13 (12) C19 (208V)* | <input type="checkbox"/> (48) C13 (208V) |
| <input type="checkbox"/> (24) C13 (6) C19 (6) 5-20R (208/120V) | <input type="checkbox"/> (18) C13 (6) C19 (208V) | <input type="checkbox"/> (30) C13 (6) C19 (208 V) | <input type="checkbox"/> (60) C13 (208V)* |
| <input type="checkbox"/> (24) C13 (9) C19 (3) 5-20R (208/120V) | <input type="checkbox"/> (24) C13 (208V) | <input type="checkbox"/> (36) C13 (208V) | |



*These configurations are included in models that are 75"H (1905 mm) or 77.9"H (1978 mm), which must be placed in 45U or taller cabinets. All other configurations will fit into 42U or taller cabinets.

3 Evaluate your accessory needs for a fully deployable power solution.



Input power cords for use with eConnect PDUs with an IEC C20 inlet.

IEC C20 PDU Input Power Cords

- | | |
|--|---|
| <input type="checkbox"/> IEC Power Cord IEC C20 Plug | <input type="checkbox"/> IEC Power Cord with NEMA L5-15P Plug |
| <input type="checkbox"/> IEC Power Cord with NEMA 5-15P Plug | <input type="checkbox"/> IEC Power Cord with NEMA L5-20P Plug |
| <input type="checkbox"/> IEC Power Cord with NEMA 5-20P Plug | <input type="checkbox"/> IEC Power Cord with NEMA L6-15P Plug |
| <input type="checkbox"/> IEC Power Cord with NEMA 6-15P Plug | <input type="checkbox"/> IEC Power Cord with NEMA L6-20P Plug |
| <input type="checkbox"/> IEC Power Cord with NEMA 6-20P Plug | <input type="checkbox"/> IEC Power Cord IEC 16A 1P+N+E Plug |



Temperature and Humidity Probes

- One Temperature/Humidity Probe
- Two Temperature/Humidity Probes

Environmental probes and accessories for local temperature and humidity monitoring.

Try the easy-to-use eConnect product selector at www.chatsworth.com/econnect-selector.

