GT-Series GlobalFrame® Gen 2 Cabinet System


An easy-to-use, computer and network equipment storage cabinet that complies with data center, computer room and premise network equipment room requirements.

KEY FEATURES

- · Cabinet solution adaptable to server, network or mixed-use application
- Standard configuration includes perforated front and rear doors to support front-to-rear airflow
- · Vertical Exhaust Duct configuration for high-density applications
- · Sized to match industry standards
- Supports up to 1300 kg (2866 lb) of equipment
- Thermal, power and cable management accessories



ADVANTAGES





SPECIFICATIONS

Description	Freestanding equipment cabinet provides front and rear support for 482.6 mm (19"W) EIA rack-mount equipment and shelves							
Environment	For indoor use only, in environmentally controlled areas; not harsh environments or in air-handling spaces							
	Welded and bolted steel four-post frame							
	Equipment mounting rails, two pairs							
	Factory installed grounding/bonding system							
Includes	Leveling feet and casters; Baying kit							
	Solid top panel with two or four brush-covered cable access ports							
	Perforated metal front door; Double perforated or solid metal rear door							
	Solid metal side panels (optional)							
Load Capacity	1300 kg (2866 lb), stationary on leveling feet							
Equipment Space	See Height, Width and Depth tables under ordering information							
Material/Construction	Steel; Welded/bolted frame, mounting rails screw to frame							
Grounding/Bonding:	Mounting rails, top panel, side panels and doors are electrically bonded to the cabinet frame. A mounting location for a ground lug is provided on the cabinet frame.							
Finish Epoxy-polyester hybrid powder coat in Black and Glacier White								

USEWITH

- PDU Mounting Brackets
- Bottom Panel
- Cable Lashing Bracket
- Clik-Nut[®] Hardware Kit

RELATED PRODUCTS

- Snap-In Filler Panels
- · Rack-Mount Shelf
- Rack-Mount PDUs

Availability: Asia Pacific

United States Agoura Hills, CA 800-834-4969 Canada Toronto, Ontario, Canada +905-850-7770 chatsworth.com • techsupport@chatsworth.com

Europe

Middle East & Africa Doha, Qatar

+974-4-267422

Latin America +52-55-5203-7525 800-01-7592

Asia Pacific

+86 21 6880-0266



SPECIFICATIONS

	Front door is curved, perforated metal						
Doors/Latches	Rear door is flat, perforated or solid metal						
DUUIS/Latches	Swing handle latch with keyed lock						
	Easy to remove; reversible to open from the right or left						
	Order with cabinet or as an accessory						
Side Panels	Solid, two-piece interlocking panels (half-height, full-depth) with a single recessed lock located near the top, center of the panel, keyed to match the front/rear door						
Top Popol	Solid top panel with four rectangular 100 mm x 225 mm (3.9"W x 8.9"D) brush-covered cable openings (one per corner) on the standard configuration						
Top Panel	Tool-less installation and removal (after removing shipping fasteners), spring-release pins secure the panel on the cabinet frame						
	Two pairs of equipment mounting rails in the cabinet						
	Adjustable depth; fixed 25 mm (1.0") increments, rails screw into frame						
	Marks on frame for easy vertical alignment						
	44.45 mm (1.75"H) U spacing, marked and numbered bottom-to-top on all rails						
Equipment Support	Universal, 19"W, 15.9 mm $-$ 15.9 mm $-$ 12.7 mm (5/8" - 5/8" - 1/2") vertical hole spacing complies with EIA/ECA-310-E						
	Square-punched mounting holes accept Clik-Nut Hardware Kits and standard cage nuts						
	Includes attachment points for accessory snap on Cable Ring Kits, order separately						

The GT-Series GlobalFrame[®] Gen 2 Cabinet System is an easy-to-use, computer and network equipment storage cabinet that complies with data center, computer room and premise network equipment room requirements.

The GT-Series GlobalFrame Gen 2 Cabinet will support up to 1300 kg (2866 lb) of equipment load. Equipment mounting rails are adjustable in depth in fixed 25 mm (1 in) increments and the markings on the frame provide easy vertical alignment during adjustment. The rails feature a Z-shaped design and have attachment points along the sides for accessory cable rings that create a vertical pathway for cables. Every cabinet includes a top panel, front and rear doors, transport casters and leveling feet.

The GT-Series GlobalFrame Gen 2 Cabinet is configured standard with perforated metal front and rear doors to support front-to-rear airflow in traditional hot aisle/ cold aisle applications. The standard configuration features a solid top panel with four brush-covered openings for cable access (one per corner) and a double (vertically split) rear door for easy access to equipment. The side panel is a two-piece panel (top half/bottom half) for easier handling. A high-density Vertical Exhaust Duct configuration is also available for 42U and 45U height cabinets.

Create a cabinet solution that fits your needs by selecting specific thermal, cable and power management accessories. See inside for product details. Contact CPI Technical Support or visit the CPI website (<u>www.chatsworth.com.cn</u> or <u>www.chatsworth.com.cn/gt-series</u> for additional product information.)

DIMENSION TABLES


Height Dimensions – mm (in)								
Rail Height	42U	45U	48U					
Overall Height, Casters included	2013 (79.3)	2147 (84.5)	2281 (89.7)					
Frame Opening, Front	1876 (73.9)	2010 (79.1)	2144 (84.3)					

Width Dimensions –	mm (in)			
Nominal Width	600	800		
Overall Width	600 (23.6)	800 (31.5)		
Frame Opening, Front	508 (20.0)	708 (27.9)		
Panel Width	482.6 (19" EIA)	482.6 (19" EIA)		

Depth Dimensions – mm (in)										
Nominal Depth	800	1000	1100	1200						
Overall Depth with	829	1029	1124	1229						
Doors	(32.6)	(40.5)	(44.3)	(48.4)						
Frame Depth, At Base,	800	1000	1100	1200						
No Doors	(31.5)	(39.4)	(43.3)	(47.2)						
Min./Max. Rail Depth,	N/A	183 (7.2)/	183 (7.2)/	183 (7.2)/						
600 mm Cabinet ¹		879 (34.6)	979 (38.5)	1079 (42.5)						
Min./Max. Rail Depth,	173 (6.8)/	173 (6.8)/	173 (6.8)/	173 (6.8)/						
800 mm Cabinet ¹	668 (26.3)	868 (34.2)	968 (38.1)	1068 (42.0)						


Dimension Notes:


 When adjusted to maximum depth, mounting rails wrap around the frame uprights (corner posts). Cable Ring Kits cannot be attached to the rails when they are set to maximum depth.



DIMENSIONAL DRAWINGS:

Front View





ORDERING INFORMATION

Use the part number matrix below to select a GT-Series GlobalFrame Gen 2 Cabinet. Choose the Width, Depth and Side Panels to form a part number. Example Part Number: GT-1C420-CA

- Standard Top Panel Configuration has perforated front/rear doors. Vertical Exhaust Duct configuration has perforated front/solid rear doors.
- · Four frame sizes to choose from-two heights, four widths, two depths.
- Includes a cabinet frame, two pairs of 482.6 mm (19"W) EIA square-punched equipment mounting rails, a solid or Vertical Exhaust Duct top panel, a perforated front door, a double perforated or solid rear door, swing handle latches, keyed locks, casters, leveling feet and baying kit.
- Supports 1300 kg (2866 lb) static load on leveling feet. Casters are designed for moving an empty cabinet into position before loading equipment. The leveling feet should be extended prior to adding equipment to the cabinet.

W D S

		1. H	eight			2. V	Vidth		3. I	Depth		4. 5	Side Panels	5.	Configuration	-	6. Color	7. Frame
			U	mm	in		mm	in		mm	in	De	scription	De	scription		Description	Description
		1	42	2013	79.3	Α	600	23.6	2	1000	39.4	0	No Sides	0	Standard Top Panel/Standard Pallet		C Black	A 4-Slide
GT	-	2	45	2147	84.5				5	1100	43.3	1	One Side]	E Glacier	
		3	48	2281	89.7				4	1200	47.2	2	Two Sides]			White	

	1. H	leight			2. V	Vidth		3. D	Depth		4. \$	Side Panels	5. (Configuration	-	6. Color	7. Frame
		U	mm	in		mm	in		mm	in	De	scription	De	scription		Description	Description
	1	42	2013	79.3	C	800	31.5	1	800	31.5	0	No Sides	0	Standard Top Panel/Standard Pallet		C Black	A 4-Slide
GT-	2	45	2147	84.5				2	1000	39.4	1	One Side				E Glacier	
	3	48	2281	89.7	1			5	1100	43.3	2	Two Sides	1			White	
								4	1200	47.2							4

	1. H	leight			2. V	Vidth		3. E	Depth		4. Side Panels			4. Side Panels 5. Configuration		-	6. Color	7. Frame
		U	mm	in		mm	in		mm	in	De	scription	De	scription		Description	Description	
от	1	42	2013	79.3	Α	600	23.6	4	1200	47.2	0	No Sides				C Black	A 4-Slide	
GT-	2	45	2147	84.5	C	800	31.5				1	One Side	1	1 Vertical Exhaust Duct, 20-34 in (500-850 mm)				
								•			2	Two Sides	1	(500-650 1111)				

Orderina Notes:

1. Height: Three heights are available: 42U, 45U and 48U. Height is listed as rack-mount units (U). Vertical Exhaust Duct

GT

- option is only available for 42U and 45U heights. See DIMENSIONS for overall height dimension. 2. Width: Two widths are available: 600 mm (23.6 in) and 800 mm (31.5 in). The cabinet
- includes equipment mounting rails spaced for 482.6 mm (19"EIA) rack-mount equipment.
- 3. Depth: Four depths are available: 800 mm (31.5 in), 1000 mm (39.4 in), 1100 mm (43.3 in) and 1200 mm (47.2 in). Doors add approximately 25 mm (1 in) to overall depth. See DIMENSIONS for details.
- 4. Side Panels: Three configurations are available: no sides, one side or both sides.
- 5. Finish: Black and Glacier White. Vertical Exhaust Duct version is only available in black.



GT-1C420-CA







THERMAL MANAGEMENT ACCESSORIES

Enhance thermal performance by controlling airflow through the cabinet using the following accessories.



Bottom Panel

The Bottom Panel prevents airflow form entering the bottom of the cabinet.Solid panel with one brush-covered opening at the

- rear.
- Match to the width and depth of the cabinet.



Side Panel

One locking side panel with key, allowing easy installation.



Air Dam Kit

Use in the 800 mm (31.5"W) cabinet to seal the space between the equipment mounting rails and the side panels within the cabinet. With 8 cable pass ports, includes a set of equipment rail grommet kit (P/N 39133-001). Use with Snap-In Filler Panels.



Snap-In Filler Panels

Use Snap-In Filler Panels to seal any open rack-mount spaces in the cabinet. Snap-In Filler Panels combine with Air Dam Kit to create a one-way airflow pathway within the cabinet that separates hot and cold air. Snap-In Filler Panels are available in 1U and 2U versions.



Equipment Rail Grommet Kit

Set of plastic grommets that cover cable openings in the equipment mounting rails in the 800 mm wide cabinets to block airflow around equipment.

- Grommets are plastic, snap on, seal cable openings and can be cut to pass cables
- Includes: (8) grommets
- Material: Plastic

Fixed Shelf

Fixed shelf with 445 mm (17.5") W x 653 mm (25.7") D surface, supports up to 100 kg (220 lb) of equipment. Mounting hardware included.

Part Number	Description						
	Bottom Panel						
26130-X08	For 800 mm x 800 mm (31.5"D x 31.5"W) Cabinets	9.9 (22)					
26130-X11	For 800 mm x 1000 mm (31.5"W x 39.4"D) to 800 mm x 1200 mm (31.5"W x 47.2"D) Cabinets	15.0 (33)					
26130-X03	For 600 mm x 1000 mm (23.6"W x 39.4"D) to 600 mm x 1200 mm (23.6"W x 47.2"D) Cabinets	13.2 (29)					
	Side Panel						
26330-X00	For 42U x 800 mm (31.5"D) Cabinets	13.5 (30)					
26330-X01	For 42U x 1000 mm (39.4"D) Cabinets	16.1 (35)					
26330-X02	For 42U x 1100 mm (43.3"D) Cabinets	17.4 (38)					
26330-X03	For 42U x 1200 mm (47.2"D) Cabinets	18.6 (41)					
26330-X04	For 45U x 800 mm (31.5"D) Cabinets	14.9 (33)					
26330-X05	For 45U x 1000 mm (39.4"D) Cabinets	17.4 (38)					
26330-X06	330-X06 For 45U x 1100 mm (43.3"D) Cabinets						
26330-X07	For 45U x 1200 mm (47.2"D) Cabinets	20.0 (44)					
26330-X08	For 48U x 800 mm (31.5"D) Cabinets	16.3 (36)					
26330-X09	For 48U x 1000 mm (39.4"D) Cabinets	18.9 (41.7)					
26330-X10	For 48U x 1100 mm (43.3"D) Cabinets	20.2 (44.6)					
26330-X11	For 48U x 1200 mm (47.2"D) Cabinets	21.5 (47.4)					
	Air Dam Kit						
26250-X00	For 42U x 800 mm (31.5"W) Cabinets	7.7 (17)					
26250-X01	For 45U x 800 mm (31.5"W) Cabinets	7.9 (17)					
26250-X02	For 48U x 800 mm (31.5"W) Cabinets	7.9 (17)					
	Snap-In Filler Panels						
34537-001	1U x 19"EIA, Pack of 6, Black	1.8 (4)					
34538-001	2U x 19"EIA, Pack of 6, Black	1.8 (4)					
	Equipment Rail Grommet Kit						
39133-001	Equipment Rail Kit, Pack of 8	0.9 (2)					
	Fixed Shelf						
26573-X19 X=color: C=Black	1U x 19"EIA	8.1 (18)					

X=color; C=Black, E=Glacier White

ADDITIONAL ACCESSORIES



Vertical Power Strips

Power Strips attach to the PDU Mounting Brackets and distribute power to multiple devices from a single power connection. Choice of plug and outlet styles to match site requirements. Available with a thermal circuit breaker to protect circuits from overload. Optional surge-protection to protect equipment from power spikes. Optional local meters to provide easy voltage and current monitoring. Horizontal Rack-Mount versions also available.

Part N	lumber	Des	cription	Shipping
Non-Surge	Surge- Protected	Plug	Outlets	Weight kg (lb)
15642-212	15642-112	IEC 16A 2P+E	(10)C13/(4)C19	3.6 (8)
15644-212	15644-112	IEC 16A 2P+E	(20)C13/(4)C19	5.0 (11)
15642-222	15642-122	IEC 32A 2P+E	(10)C13/(4)C19	3.6 (8)
15644-222	15644-122	IEC 32A 2P+E	(20)C13/(4)C19	5.0 (11)
		Metered		
15643-212	15643-112	IEC 16A 2P+E	(10)C13/(4)C19	3.6 (8)
15645-212	15645-112	IEC 16A 2P+E	(20)C13/(4)C19	5.0 (11)
15643-222	15643-222 15643-122		(10)C13/(4)C19	3.6 (8)
15645-222	15645-122	IEC 32A 2P+E	(20)C13/(4)C19	5.0 (11)

Other options available. Contact CPI.

CABLE MANAGEMENT ACCESSORIES

Keep network, KVM and power cables separate and organized using the following cable management accessories.



26110-XXX

26120-XXX

Cable Ring Kit

The Cable Ring Kit includes eight plastic D-rings that snap onto the equipment mounting rails inside the cabinet, creating a vertical pathway for cables. Select the kit to match cabinet width. There are two ring sizes (depths) for 800 mm (31.5") wide cabinets. Each rail can support seven rings. Mounting rails in the 600 mm (23.6") wide cabinet must be setback a minimum of 137.5 mm (5.4") to provide clearance for the cable rings. Mounting rails in the 800 mm (31.5") wide cabinet must be setback a minimum of 125 mm (4.9") to provide clearance for the medium cable ring and a minimum of 250 mm (9.8") to provide clearance for the large cable rings. Cable Ring Kit cannot be used with Vertical Cable Managers (P/Ns 26120-XXX 0r 26110-XXX).

Part Number	Description	Shipping Weight kg (lb)
26104-001	Rings For 600 mm Cabinets, Black 43 x 127 (1.7 x 5.0), Outside, 25 x 112 (1.0 x 4.4), Inside	9.9 (22)
26106-002	Medium Rings For 800 mm Cabinets, Black 114 x 119 (4.5 x 4.7), Outside - 81 x 89 (3.2 x 3.5), Inside	15.0 (33)
26106-001	Large Rings For 800 mm Cabinets, Black 114 x 249 (4.5 x 9.8), Outside - 81 x 218 (3.2 x 8.6), Inside	13.2 (29)

Color is Black

Part N	umber		Shipping		
600 mm	800 mm	Description	Weight kg (lb)		
26110-X00	26120-X00	For 42U Cabinets	6.8 (15)		
26110-X01	26120-X01	For 45U Cabinets	8.6 (19)		
26110-X02	26120-X02	For 48U Cabinets	10.4 (23)		

X=color; C=Black, E=Glacier White. For Glacier White finish, the plastic fingers are black finish, the metal finish is white. Shipping weights are for the 800 mm part numbers.

Description	Shipping Weight kg (lb)
Single PDU Mounting Bracket, 42U	6.4 (14)
Double PDU Mounting Bracket, 42U	6.9 (15)
Single PDU Mounting Bracket, 45U	6.5 (14.4)
Double PDU Mounting Bracket, 45U	7.1 (15.7)
Single PDU Mounting Bracket, 48U	6.6 (14.8)
Double PDU Mounting Bracket, 48U	7.3 (15.4)
	Single PDU Mounting Bracket, 42U Double PDU Mounting Bracket, 42U Single PDU Mounting Bracket, 45U Double PDU Mounting Bracket, 45U Single PDU Mounting Bracket, 48U

X=color; C=Black, E=Glacier White.

Part Number	Description	Shipping Weight kg (lb)
26403-X00	For 42U Cabinets	12.6 (28)
26403-X01	For 45U Cabinets	13.5 (30)
26403-X02	For 48U Cabinets	14.4 (32)

X=color: C=Black F=Glacier White

Part Number	Description	Shipping Weight kg (lb)
76543-001	Clik-Nut Hardware Kit, Cage Nuts, Screws, M6, 25 Pack, Zinc	1 (0.5)
76544-001	Clik-Nut Hardware Kit, Cage Nuts, Screws, #12-24, 25 Pack, Zinc	1 (0.5)
76545-001	Clik-Nut Hardware Kit, Cage Nuts, Screws, #10-32, 25 Pack, Zinc	1 (0.5)

Note: Additional quantities available

Finger Cable Manager

The Finger Cable Manager attaches to the cabinet's equipment mounting rails, and provides vertical cable management with plastic T-shaped cable guides and openings that align with each rack-mount space (U) in the cabinet to organize patch cords. The manager for the 600 mm (23.6") wide cabinet includes standard fingers only and can be used in either width cabinet. The manager for the 800 mm (31.5") wide cabinet is available with extended fingers and also includes a cover that partially encloses cables. Standard fingers require a 175 mm (6.9") rail setback, and the Extended fingers require a 237.5 mm (9.35") rail setback. The managers cannot be used with Cable Ring Kit (P/Ns 25104-001, 26106-001 or 26106-002). Select to match cabinet width.

The PDU Mounting Brackets attach to the cabinet frame and provides one or two attachment points for CPI vertical PDUs or power strips for cabinets, and multiple tie points for power cables. Secure cables to the bracket using Saf-T-Grip Straps or cable ties. Tool-less PDU attachment points are located 1645 mm and 1556 mm (64.75" and 61.25") apart. The Single PDU Mounting Bracket is 89 mm (3.5") wide. The double bracket supports two 56 mm (2.2") wide or narrower PDUs side-by-side. The Double PDU Mounting Bracket is 117 mm (4.6") wide and requires a minimum 200 mm (7.8") rail setback in 600 mm wide cabinets and a minimum 187.5 mm (7.4") rail setback in



Cable Lashing Bracket

Clik-Nut® Hardware Kit

maintaining load-bearing

· Easy, tool-less attachment and removal • Fits .375" (9.5 mm) square hole

to 2.67 mm panel thickness) Includes mounting screws

strength.

other cabinets

PDU Mounting Brackets

The Cable Lashing Bracket Kit attaches to the cabinet frame and provides multiple tie points for cables. Secure cables to the bracket using Saf-T-Grip Straps or cable ties. The kit includes one full height bracket with U-shaped cable tie points and installation hardware. The Cable Lashing Bracket is 124 mm (4.9") wide with two vertical columns of tie points for cables and has a 6500 mm² (10.0 in²) cable fill area. The bracket requires a 175 mm (6.9") rail setback in 600 mm (23.6") wide cabinets and a 125 mm (4.9") rail setback in 800 mm (31.5") wide cabinets.

Redefining the Cage Nut. The design eliminates the need for tools, resulting in easier and faster installation, while

• Grip range 16 ga to 12 ga, .060" to .105" (1.52 mm

PATENTED





CPI Passive Cooling[®], The Simply Efficient[™] Choice

CPI Passive Cooling[®] Solutions offer innovative techniques that allow you to manage the flow of air throughout your data center without the need for added cooling system units, in-row air conditioners or risky liquid cooling solutions. From small applications with heat loads of 2 kW per cabinet to large data centers with high heat densities up to 32 kW, CPI Passive Cooling Solutions offer smart, proven technology to reduce your data center cooling cost. As the Simply Efficient[™] choice, CPI Passive Cooling Solutions allow you to meet tiered requirements for operation of your IT equipment and to deploy the latest servers, switches and blade servers from HP, IBM, Dell, Huawei, Cisco, Juniper Networks and Brocade with confidence.

How Passive Cooling Solutions work:

- Controls Airflow CPI Passive Cooling Solutions control airflow through the cabinet using a specific combination of thermal management accessories. Solutions are available for traditional hot aisle/cold aisle environments and containment.
- Eliminates Re-circulation CPI Passive Cooling Solutions create a one-way airflow pathway through the cabinet that eliminates the mixing of hot and cold air. The high-density solution, which includes a Vertical Exhaust Duct to isolate hot air from the room, guarantees heat transfer directly from equipment to the cooling unit.
- Increases Cabinet Density With a Vertical Exhaust Duct, there is no hot aisle, so cabinet heat loads are not limited by the amount of air that can be delivered through the access floor tiles positioned directly in front of the cabinet.
- Uses Existing Standard Cooling Equipment If the cooling capacity of your existing chilled water computer room air conditioners (CRACs) or air handlers (CRAHs) exceeds your heat load, there is no need to add expensive supplemental in-row cooling.

Low Heat Density


Combine:


- GT-Series GlobalFrame Gen 2 with:
 - Perforated Front Door
 - Perforated Rear Door
 - Solid Side Panels
- Solid Top Panel
- Bottom Panel
- Air Dam Kit
- Equipment Rail Grommet Kit
- Snap-In Filler Panels

High Heat Density

Combine

- GT-Series GlobalFrame Gen 2 with:
- Perforated Front Door
- Solid Rear Door
- Solid Side Panels
- Solid Top Panel and Vertical Exhaust Duct
- Bottom Panel
- Air Dam Kit
- Equipment Rail Grommet Kit
- Snap-In Filler Panels







Advantages of using CPI Passive Cooling Solutions – High Heat Density Solution with Vertical Exhaust Duct

- Eliminates hot spots isolating and removing hot exhaust air creates a uniform temperature in the room.
- No additional power or redundancy requirements include no active components.
- Improves cooling system utilization capturing hot exhaust air means higher temperature return air, which improves utilization of chilled water CRACs and CRAHs.
- Increases chiller efficiency or "free cooling" hours isolating hot air allows you to confidently raise the supply air temperature, which allows you to raise the chilled water temperature, and increase potential free cooling hours in most locations.
- Lowers your operating costs the combined effect of better cooling system utilization and more free cooling hours provides lower operating costs.



hile every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products. ©2018 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, Clik-Nut, CPI, CPI Passive Cooling, eConnect, volution, GlobalFrame, MegaFrame, Motive, OnTrac, QuadraRack, RMR, Saf-T-Grip, Secure Array, SeismicFrame, SlimFrame, Frame and Velocity are federally registered trademarks of Chatsworth Products. CUBE-iT, EuroFrame and Simply Efficient are trademarks of Chatsworth Products. All other trademarks belong to their respective companies.