


SOLUTIONS SHEET

Structured Cabling Support Solutions

Chatsworth Products, Inc. (CPI) delivers innovative, high quality and cost effective Structured Cabling Solutions for optimizing, storing and securing network cabling and equipment in both large and small applications. Combine CPI Rack Systems, Cable Management Products, Cable Runway and Tray and Grounding and Bonding Products to support standard wiring closets, or use Wall-Mount Systems to support smaller networks and zone applications.

Make the choice to simplify everyday cabling concerns with CPI's comprehensive Structured Cabling Solutions.



1 13902-703
Velocity Single-Sided
Cable Manager
80.5"H x 6"W x 9.8"D
(2045 mm x 152 mm x 249 mm)

2 55053-703
Standard Rack,
45U x 19"EIA,
7'H x 20.3"W x 15"D
(2.1 m x 516 mm x 380 mm)

3 10250-712
Universal Cable Runway
1.5"H x 12"W x 9'-11.5"L
(38 mm x 300 mm x 3035 mm)

4 40153-020
Busbar
4"H x 20"W x 1/4"D
(100 mm x 510 mm x 6.4 mm)

5 13050-712
ThinLine II Wall-Mount Cabinet
26"H x 26"W x 8.5"D, 4U
(660 mm x 660 mm x 216 mm)

1 Cable Management Products - Velocity® Cable Management is an economical solution for everyday use in telecommunications rooms, equipment rooms and lab spaces and that creates a complete vertical and horizontal pathway for premise cabling and patch cords on CPI Rack Systems.

2 Rack Systems - Unsurpassed strength, stability and durability for supporting patch panels, high-density blocks, cabling and other equipment. With the addition of shelves and special brackets, racks can be quickly adapted for changing needs or to hold larger devices and computer hardware.

3 Cable Runway and Tray - CPI's Cable Runway and OnTrac® Wire Mesh Cable Tray System make up a vital part of the IT infrastructure solution by providing horizontal, vertical and backbone pathways from the data center to workstations.

4 Grounding and Bonding Products - CPI's comprehensive line of UL® Listed Grounding and Bonding Products bond racks, cable runway and tray, and provide protection for electronic equipment.

5 Wall-Mount Systems - Store and secure equipment on the wall inside or outside of the data center or equipment room and connect remote groups of users to the network.

+1-800-834-4969

techsupport@chatsworth.com
www.chatsworth.com

ORDERING INFORMATION

Rack Systems

| CPI Rack Systems | | |
|------------------|---|----------------------------|
| Part Number | Description H x W x D in (mm) | Shipping Weight lb (kg) |
| 55053-703 | Standard Rack, 45U x 19"EIA 7'H (2.1 m) x 20.3 x 15 (516 x 380), 1,000 lb (453.6 kg) load, UL Listed, Black | 31 (14.1) |
| 48353-703 | Universal Rack, 45U x 19"EIA 7'H (2.1 m) x 20.3 x 15 (516 x 380), 1,500 lb (680.4 kg) load, UL Listed, Black | 39 (17.7) |
| 15218-703 | Adjustable QuadraRack®, 45U x 19"EIA 7'H (2.1 m) x 20.3 (516), Adjustable Depth 36.42 to 42.32 (925 to 1075), 2,000 lb (907.2 kg) load, Black | 54 (24.5) |

Other sizes and configurations available. Contact CPI at +86-21-6880-0266.

Cable Management Products

| Velocity® Single-Sided Vertical Cable Managers | | |
|--|--|----------------------------|
| Part Number | Description H x W x D in (mm) | Shipping Weight lb (kg) |
| For 7'H (2.1 m), 45U Racks | | |
| 13901-703 | 80.5 x 3.6 x 9.7 (2045 x 91 x 246), Black | 18 (8.2) |
| 13902-703 | 80.5 x 6 x 9.8 (2045 x 152 x 249), Black | 20 (9.1) |
| 13904-703 | 80.5 x 10 x 10.3 (2045 x 254 x 262), Black | 32 (14.5) |
| 13905-703 | 80.5 x 12 x 10.4 (2045 x 305 x 264), Black | 34 (15.4) |
| Velocity® Double-Sided Vertical Cable Managers | | |
| For 7'H (2.1 m), 45U Racks | | |
| 13911-703 | 80.5 x 3.6 x 16.4 (2045 x 91 x 417) | 25 (11.3) |
| 13912-703 | 80.5 x 6 x 16.6 (2045 x 152 x 422) | 28 (12.7) |
| 13914-703 | 80.5 x 10 x 17.5 (2045 x 254 x 445) | 40 (18.1) |
| 13915-703 | 80.5 x 12 x 17.8 (2045 x 305 x 446) | 43 (19.5) |
| Velocity® Horizontal Cable Managers | | |
| 13930-701 | 1U x 19" EIA x 5.9 (150) | 2 (0.9) |
| 13930-702 | 2U x 19" EIA x 5.9 (150) | 3 (1.4) |
| 13930-703 | 3U x 19" EIA x 5.9 (150) | 3 (1.4) |

Other sizes available. Contact CPI at 800-834-4969.

| Velocity® Standard Pack | | |
|---|---|----------------------------|
| Part Number | Description | Shipping Weight lb (kg) |
| Rack, Cable Management & Hardware Package | | |
| 57011-703 | (1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Single-Sided Vertical Cable Manager, 3.6"W (91 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc | 47 (21.3) |
| 57012-703 | (1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Double-Sided Vertical Cable Manager, 3.6"W (91 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc | 60 (27.2) |
| 57013-703 | (1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Single-Sided Vertical Cable Manager, 6"W (152 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc | 50 (22.7) |
| 57014-703 | (1) Standard Rack, 45U x 19" EIA, UL Listed, Black (1) Velocity® Double-Sided Vertical Cable Manager, 6"W (152 mm), Black (1) Rack Installation Kit for concrete floor, 1/2" hardware, Zinc | 68 (30.8) |

Not exactly what you need? Additional products, sizes and configurations are available from CPI. Visit www.chatsworth.com or call +1-800-834-4969.

Cable Runway and Tray

| Cable Runway | | |
|------------------------------|---|----------------------------|
| Part Number | Description H x W x L in (mm) | Shipping Weight lb (kg) |
| 10250-712 | Universal Cable Runway 1.5 x 12 (38 x 300) x 9'-11.5"L (3 m) | 25 (11.3) |
| 10250-718 | Universal Cable Runway 1.5 x 18 (38 x 460) x 9'-11.5"L (3 m) | 29 (13.2) |
| 11301-701 | Butt-Splice Kit (end-to-end splice) | 1 (0.5) |
| 11302-701 | Junction-Splice Kit (L or T intersection) | 1 (0.5) |
| 10506-706 | Cable Runway Elevation Kit, 4", 5" or 6"H (100 mm, 130 mm or 150 mm) | 3 (1.4) |
| 12730-712 | Rack-To-Runway Mounting Plate, For 12"W (300 mm) Runway, Black | 5 (2.3) |
| 12730-718 | Rack-To-Runway Mounting Plate, For 18"W (460 mm) Runway, Black | 7 (3.2) |
| 11421-712 | Wall Angle Support Kit, For 12"W (300 mm) Runway, Black | 7 (3.2) |
| 11421-718 | Wall Angle Support Kit, For 18"W (460 mm) Runway, Black | 7 (3.2) |
| 11310-093 | Threaded Ceiling Kit, with M10 x 2m L Rod | 3 (1.4) |
| OnTrac® Wire Mesh Cable Tray | | |
| 34811-512 | Tray, 2 x 12 (50 x 300) x 10'L (3 m), Zinc Plated | 17 (7.7) |
| 34821-512 | Tray, 4 x 12 (100 x 300) x 10'L (3 m), Zinc Plated | 21 (8.5) |
| 34738-501 | Standard Splice Kit, Pack of 50 | 11 (5.0) |
| 34746-501 | Clamp Washer, Pack of 25 | 2 (0.9) |
| 34730-512 | Trapeze Support Bracket, For 12"W (300 mm) Tray | 2 (0.9) |

Grounding and Bonding

| Part Number | Description H x W x D in (mm) | Shipping Weight lb (kg) |
|-------------|---|----------------------------|
| 40153-020 | Busbar, 4 x 20 x 1/4 (100 x 510 x 6.4) | 8 (3.6) |
| 10610-019 | Horizontal Rack Busbar, 19" EIA | 2 (0.9) |
| 40161-072 | Vertical Rack Busbar Kit | 7 (3.2) |
| 40164-025 | Cable Runway Ground Strap Kit, #6 AWG, Pack of 25 | 12 (5.0) |

Wall-Mount Systems

| Part Number | Description H x W x D in (mm) | Shipping Weight lb (kg) |
|-------------|--|----------------------------|
| 13602-708 | EasySwing Wall-Mount Rack, 11U x 19"EIA x 6.5 (35), 24.5 x 20.3 x 8.0 (622 x 516 x 200), 100 lb (45.4 kg) load, Black | 22 (10.0) |
| 13050-712 | 4U x 19"EIA, ThinLine II Wall-Mount Cabinet, 26 x 26 x 8.5 (660 x 660 x 216) | 54 (24.5) |
| 13051-001 | Intelligent Fan Kit, 115 VAC, 60 Hz | 2 (0.9) |

Accessories

| Part Number | Description | Shipping Weight lb (kg) |
|-------------|--|----------------------------|
| 40074-700 | Single-Sided Shelf, 3U x 19"EIA x 15"D (380 mm), 50 lb (22.7 kg) load, Black | 6 (2.7) |
| 40108-719 | Double-Sided Shelf, 4U x 19"EIA x 21.5"D (546 mm), 100 lb (45.4 kg) load, Black | 8 (3.6) |

