

FRAME GROUND CONNECTOR

Use ground connector with 6 AWG solid and stranded copper conductors.

Included Items:


M6 x 12mm Screw, 4 ea.

Antioxidant joint compound, 0.5oz

Tools Required:

T25 Torx driver

TOP LATERAL MOUNTING



Tighten ground conductor wire binding screws to 50-55 in-lb (5.6-6.2 N-m)

Apply generous coating of antioxidant compound to the ribbed section with threaded holes on the ground connector before installing on frame.
Tighten ground connector frame mounting screws to 90 in-lb (10 N-m)

Apply generous coating of antioxidant compound to the ribbed section with threaded holes on the ground connector before installing on frame.
Tighten ground connector frame mounting screws to 90 in-lb (10 N-m)

Tighten ground conductor wire binding screws to 50-55 in-lb (5.6-6.2 N-m)

BOTTOM LATERAL MOUNTING

