


RMR Industrial Enclosure Systems and Solutions

Chatsworth Products (CPI) is a global manufacturer of products and solutions that protect your technology investment with expert consultation and product customization for a variety of applications.



- Wide range of high-quality, standard solutions
- Quick selection with CPI Product Designer
- Kitting of accessories to simplify ordering
- Preinstallation of accessories to save you time
- Modified standard enclosures to match specific HMI requirements
- Competitive lead times to match your schedule
- Contact Tech Support at techsupport@chatsworth.com



RMR® Wall-Mount Enclosures



- UL® Listed Industrial Control Panel Enclosure, Type 12 and IP 55 ratings
- For indoor use, protects against the ingress of dust and dripping non-corrosive liquids
- Swing-out or fixed styles
- Continuous foam gasket seal
- Wide range of sizes available
- Solid or tempered glass door option
- 19"EIA mounting rails or adjustable mounting plate
- Optional cable and thermal management accessories

RMR® Modular Enclosures



- UL Listed Industrial Control Panel Enclosure, Type 12 and IP 55 ratings
- For indoor use, protects against the ingress of dust and dripping non-corrosive liquids
- Continuous foam gasket seal
- High-strength, roll-formed steel frame
- Removable, bolt-on top, side, bottom and rear panels
- Wide range of sizes available
- 19"EIA mounting rails or adjustable mounting plate
- Optional cable and thermal management accessories

RMR® Free-Standing Enclosures



- NEMA Type 4, 4X, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Available in stainless steel with brushed finish for corrosive environments
- Easy-to-use side channels for mounting
- Continuous foam gasket seal
- Wide range of sizes available
- Single- and double-door options
- 3-point latch with choice of lock
- Optional adjustable-depth mounting plate

RMR® Standard Wall-Mount Enclosures



- NEMA Type 4, 4X, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Available in stainless steel with brushed finish for corrosive environments
- Continuous foam gasket seal
- Wide range of sizes available
- Single- and double-door options
- 3-point or 1/4-turn latch with choice of lock
- Optional rear mounting plate

RMR® Floor-Mount Enclosures



- NEMA Type 4, 4X, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Floor stands provide additional clearance and easy access to bottom of the enclosure
- Available in stainless steel with brushed finish for corrosive environments
- Continuous foam gasket seal
- Solid double door
- Three lock styles: keyed, double bit and square
- Wide range of sizes available

RMR® Disconnect Enclosures



- NEMA Type 4, 4X, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Available in Wall-Mount, Free-Standing and Floor-Mount configurations
- Standard cutout on the right flange provides mounting for major brands of disconnect switches and circuit breakers
- Available in stainless steel with brushed finish for corrosive environments
- Continuous foam gasket seal
- Wide range of sizes available

US & Canada

+1-800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com
techsupport@chatsworth.com

Latin America

+52-55-5203-7525
Toll Free within Mexico
800-201-7592
chatsworth.com

Europe

+Buckinghamshire, UK
+44-1628-524-834
chatsworth.com

Middle East & Africa

Dubai, UAE
+971-4-2602125
Doha, Qatar
+974-4-267422
chatsworth.com

Asia Pacific

Shanghai
+86 21 6880-0266
chatsworth.com.cn



RMR Industrial Enclosure Systems and Solutions

NEMA-Rated Air Conditioners



- NEMA Type 12 Indoor Cooling Units; 900-1300 BTU/hr; 3000-4000 BTU/hr; 5000-7000 BTU/hr
- Side or front mounting
- Hermetically sealed compressors prevent refrigerant loss
- Performs efficiently in high temperature areas
- Uses environmentally friendly HFC-free R134a refrigerant

Filter Fans



- Forced convection with Filter Fans
- Multiple sizes available
- Top-, side- or front-mounting
- Easy, tool-less installation
- Maintains NEMA Type 12 protection rating
- High-performance seal
- 300% longer service life
- High system airflow
- Easy filter change

Accessories for RMR® Industrial Enclosures




- Roxtec grommets are rated IP 55 and seal cable openings and support multiple cables of different diameters
- Polyvent Protective Vent Kit provides ventilation and equalizes air pressure; Use to meet NEMA Type 3R requirements
- Threaded Drain Plug Kit drains accumulated or condensed water out the bottom of the enclosure
- LED Light Kit provides additional lighting inside the enclosure; 100-240 Volts
- Drip Shield Assembly provides additional protection against ice and rain; Use to meet NEMA Type 3R requirements

eConnect® Power Distribution Units




- Intelligent power solution ; Monitored, Monitored Pro, Switched, Switched Pro configurations
- Locking outlets
- +/- 1% power metering accuracy
- High temperature rating
- Multifunctional display
- Secure Array® IP Consolidation
- Integrated environmental monitoring and access control
- Vertical and horizontal configurations

Pemsa® Rejiband® Wire Mesh Cable Tray



- UL® Certified
- BLACK C8 finish option meets resistance class IEC 61537 Class C8, delivering corrosion resistance almost equivalent to stainless steel.
- Available in 2 heights and 6 widths
- Tray can be cut and formed into turns and transitions using standard splices
- Tops of trays are rounded and smooth to protect installers and cables from cuts

Grounding and Bonding Solutions




- Busbars allow central ground attachment points
- Ground terminal blocks provide convenient ways to bond wires to enclosures
- Grounding Busbar Kits include bonding strip for consolidating equipment grounds
- Compounds improve metal-to-metal bond between grounding components



CPI now offers Extended Limited Warranties on CPI-Branded Electronic products, available for two additional years beyond the expiration of the Original Warranty Period (3 years).

Contact CPI Customer Service, or visit www.chatsworth.com/warranty for more information.

Interested in learning more about our RMR Industrial Enclosures? Call us at 800-834-4969, or email Technical Support at techsupport@chatsworth.com.



While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products. ©2019 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, Click-Nut, CPI, CPI Passive Cooling, eConnect, Evolution, GlobalFrame, MegaFrame, Motive, QuadraRack, RMR, Saf-T-Grip, Secure Array, SeismicFrame, SlimFrame, TeraFrame and Velocity are federally registered trademarks of Chatsworth Products. CUBE-IT, EuroFrame and Simply Efficient are trademarks of Chatsworth Products. All other trademarks belong to their respective companies. Rev.3 08/19 MKT-60020-691