

| PARTS LIST | | |
|------------|-----|---|
| ITEM | QTY | DESCRIPTION |
| 1 | 1 | Oberon Environmental Enclosure |
| 2 | 4 | Wall Mount Bracket |
| 3 | 1 | Plastic Internal Panel |
| 5 | 8 | Cross Recessed Pan Head Machine Screw - Type I - Metric |
| 6 | 4 | Countersunk Flat Head Screw |
| 7 | 4 | #6 x 5/16" Plastic Thread Forming Screw |




NOTES:

- Material for -C Covers:
UL 94V-0 Clear Polycarbonate
- Material for Base and other Covers:
UL94-5VA Light Gray Polycarbonate
- Material for Internal Mounting Panel:
UL 94-HB Light Gray ABS Plastic Universal
- Material for T-Bar Bracket:
18 Ga. White Powder Coated Steel
- Finish: UV Stabilized Light Gray
- Designed to NEMA 1, 2, 4, 4X, 12, and 13,
and IEC529-IP66

| WEIGHT | |
|--------------|--------|
| SKU | Weight |
| 1024-00 | 5 lbs |
| 1024-C | 5 lbs |
| 1024-18137 | 9 lbs |
| 1024-18137-C | 9 lbs |
| 1024-31237 | 18 lbs |
| 1024-31237-C | 18 lbs |


Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801

| | | |
|--------------------------------|--------------|----------|
| TITLE | | |
| Model 1024 Specification Sheet | | |
| SIZE | DWG NO | DATE |
| C | SPEC-OB1024 | 9/3/2025 |
| SCALE | SHEET 1 OF 2 | |



SECTION A-A
SCALE 1/2.5

| Dimensions by Part (inches) | | | | | | |
|-----------------------------|------|------|------|------|-----|-----|
| Model | A | B | C | D | E | F |
| 1024-00 | 15.7 | 14.8 | 11.8 | 10.9 | 4.9 | 4.0 |
| 1024-C | 15.7 | 14.8 | 11.8 | 10.9 | 4.9 | 4.0 |
| 1024-18137 | 19.2 | 18.2 | 14.7 | 13.3 | 8.0 | 7.1 |
| 1024-18137-C | 19.2 | 18.2 | 14.7 | 13.3 | 8.0 | 7.1 |
| 1024-31237 | 33.0 | 31.3 | 24.8 | 23.4 | 7.3 | 6.5 |
| 1024-31237-C | 33.0 | 31.3 | 24.8 | 23.4 | 7.3 | 6.5 |



SECTION B-B
SCALE 1/2.5

| | | |
|--|-----------------------|------------------|
| Oberon, Inc. - 1315 S. Allen St. - State College, PA 16801 | | |
| TITLE Model 1024 Specification Sheet | | |
| SIZE C | DWG NO SPEC-OB1024 | DATE 9/3/2025 |
| SCALE | SHEET 2 OF 2 | |