



CHATSWORTH
PRODUCTS

Switched eConnect® PDUs

Switched eConnect® PDUs provide remote monitoring of power at the rack level and individual outlet control, making it possible to remotely turn power on or off at each outlet.

KEY FEATURES

Reduced Networking Costs and Complexity

– Secure Array® allows the use of a single IP address for up to 48 connected PDUs (32 when electronic locks are integrated). Second IP address for the entire array provides failover capability.

Resistance to High Temperature – Market-leading temperature ratings of up to 149°F (65°C) ensures reliability when mounted toward hot aisles.

Simplified Load Balancing – Phase-balance outlets on three-phase models ensure equal loading across all phases; allows use of shorter equipment power cords for better cable and airflow management.

No Accidental Disconnections – Patented, low-profile locking outlets prevent accidental disconnections without requiring special cords.

Easy Identification of Failover Unit – Redundancy Pack includes 2 PDUs (one in Black and one in Glacier White) for easy identification of the primary and secondary unit.

Electronic Lock Integration – Patented technology seamlessly integrates PDU, environmental sensors and electronic locks into a single hardware and software solution.

Gigabit Ethernet – Ensures compatibility with enterprise routers and switches.

Latest UL Compliance – Meets UL and IEC 62368 for compliance with new listing requirements for North America and the European Union.

Cabinet Preinstallation – Complete ecosystem ships ready for IT equipment integration, and saves deployment time and reduces packaging waste.



Additional Features:

- Individual outlet switching; outlet grouping
- Field-replaceable controller module for easy serviceability and upgradeability while maintaining power to critical loads; SD-card transfers PDU configuration
- Bistable latching relays for reduced energy consumption and increased service reliability
- Input and branch circuit monitoring
- Onboard GUI, RESTful API, SNMP v1/v2/v3, Command Line Interface (CLI), RedFish, and native Power IQ® DCIM software integration allows users to easily manage PDUs
- Zero Touch Provisioning (ZTP) automates configuration and provisioning of large deployments of PDUs
- HTTPs support, 802.1x support, RADIUS and LDAP integration for enhanced authentication and security
- Customization capabilities: outlet configurations, color options, power cord length, input connection types and more
- Patent: chatsworth.com/patents
- Made in the United States; TAA compliant; BAA COTS compliant (*applies only to standard configurations with EA-5xxx-x SKUs*)

Availability: Global

United States & Canada
Simi Valley, CA
800-834-4969
Toronto, Ontario, Canada
+905-850-7770
chatsworth.com
techsupport@chatsworth.com

Latin America
Mexico City, Mexico
+52-55-5203-7525
Toll Free within Mexico
800-201-7592
chatsworth.com.co

Europe
Buckinghamshire
England, UK
+44-1628-524-834

Middle East & Africa
Dubai, UAE
+971-4-2602125

Asia Pacific
Jing'an District,
Shanghai, China
+86 21 6880-0266
chatsworth.com.cn




SPECIFICATIONS

Description:	Single-input, vertical and horizontal rack-mount PDUs
Use:	For indoor use in environmentally controlled areas or within environmental enclosures that maintain Operating Conditions (listed below)
Power Input:	<ul style="list-style-type: none"> • Alternating current, 50/60 Hz, 10 ft (3 m) input cord or Terminal Block available as standard; custom lengths between 3 - 15 ft. available • Voltage, maximum current, and inlet/plug type varies per model (see ordering table)
Power Capacity:	Specific to PDU, limited by circuit breakers or power input (see ordering table)
Power Output:	NEMA 5-20R, Locking IEC C13 and/or IEC C19 Outlets, specific to PDU with up to 48 outlets (see order table)
Circuit Protection:	<ul style="list-style-type: none"> • UL 489 listed, single- or two-pole, hydraulic-magnetic breakers available on single- and three-phase models with 30A and above input • Low-profile design prevents accidental disconnection
Metering:	<ul style="list-style-type: none"> • Input line currents • Voltage, current, power, energy and power factor at branch circuits • +/- 1% billing-grade
Switching:	<ul style="list-style-type: none"> • Ability to turn on/off and cycle power to individual or group of outlets using bistable latching relays • Ability to name individual outlets to identify attached equipment • Status indicator LED light for individual outlets • Grouping of outlets for consolidated power control
Local Display: (Vertical PDUs only)	<ul style="list-style-type: none"> • Liquid Crystal Display (LCD) with power-on autotext orientation, color • Provides PDU information; allows initial IP setup, restore defaults and upgrade firmware • Displays voltage, current, power for input lines and breakers • Displays environmental parameters when temperature / humidity sensors are attached to the unit • Displays alarm notifications – separate LED flashes red on alarm
Networking:	<ul style="list-style-type: none"> • 10/100/1000MB Ethernet Port • Secure Array IP Consolidation for up to 48 PDUs with no integrated electronic locks or 32 PDUs with integrated electronic locks • Secure Array IP Consolidation supports alternate/failover network connection through a second PDU • Static IP and Dynamic Host Configuration Protocol (DHCP) Support, Zero Touch Provisioning (ZTP)
Remote Management:	<p>HTTP/HTTPS compatible onboard Web GUI, SNMP v1/v2/v3; RESTful API, CLI, RedFish</p> <p>Native Software Integration:</p> <ul style="list-style-type: none"> - Sunbird Power IQ® DCIM and dcTrack DCIM - ZPE Systems Nodegrid Manager™ - RF Code Centerscape Software - Nlyte DCIM
Console Access:	Through serial console port connection and Command Line Interface (CLI)
Security:	<ul style="list-style-type: none"> • LDAP and Radius Authentication • Password protection • Separate user- and admin-level permissions • Ability to upload custom HTTPS certificate • Secure Shell (SSH) • 802.1x Support
Controller:	Field-replaceable controller module; SD-card transfers PDU configuration
Firmware:	Flash upgradeable through USB port, Web interface, CLI, API or Power IQ.
Environmental Sensor Integration:	Temperature & Humidity, Leak detection, Electronic Locks, Door Status, Cabinet Status Light, Cabinet Work Light
Electronic Lock Integration:	<ul style="list-style-type: none"> • Front and rear cabinet door locks (ordered separately) connected to AUX ports on the PDU • Door locks are powered from and remotely accessed through the PDU
Mounting:	<p>Vertical PDUs: 2 preinstalled tool-less mounting buttons; adjustable positions / Top or bottom power cord entry orientation</p> <p>Horizontal PDUs: Include rack-mount brackets for 19"EIA (482.6 mm) racks</p>
Grounding/Bonding:	<ul style="list-style-type: none"> • Bonded power inlet/plug and external bond connection with a threaded M5 attachment point • Includes a bonding kit for CPI cabinets
Color Options:	<ul style="list-style-type: none"> • Black or Glacier White available as standard options; other colors available as custom solutions • Redundancy Pack includes (1) Black PDU and (1) Glacier White PDU
Operating Conditions:	<ul style="list-style-type: none"> • Temperature: 32°F – 149°F (0°C – 65°C) at Input Power Rating (kW) • Relative Humidity: 5% – 95%, noncondensing • Elevation: 0 – 10,000' (0 – 3,000 m)
Storage Non-operating Conditions:	<ul style="list-style-type: none"> • Temperature: -13°F – 149°F (-25°C – 65°C) • Relative Humidity: 5% – 95%, noncondensing • Elevation: 0 – 50,000' (0 – 15,000 m)
Shipping Weight:	Vertical PDUs: 27 lb (12 kg) single unit; 54 lb (24 kg) Redundancy Pack
Certifications:	<p>NEMKO certified to UL/IEC62368, CE (EU), FCC Part 15, Class A, EN 55022, RoHS Compliant</p> <ul style="list-style-type: none"> • Patent: chatsworth.com/patents
Warranty:	3 years standard with advanced replacement; 2 additional years optional

VERTICAL CONFIGURATION


Use Vertical eConnect PDUs in data centers and equipment rooms with 42U or higher racks, cabinets and enclosures to provide power connections alongside equipment for higher-density applications. Use Redundancy Pack to support redundant power circuits.



Hydraulic-Magnetic Breakers




Locking Outlets



Color-Coded Tabs on Outlets



Status LED Light



Field-Replaceable Controller Module for Vertical eConnect PDUs



- 1 Proprietary Auxiliary Ports for Sensor Array and Lock Kits
- 2 Serial Console Port - USB Mini Type B
- 3 Status LED
- 4 Ethernet Port - RJ45
- 5 Serial Console Port - RJ45
- 6 USB Type A Ports for Firmware and Temperature/Humidity Sensors
- 7 Secure Array Ports - RJ45 - for linking of up to 48 PDUs
- 8 LCD Local Display

ORDERING INFORMATION

Switched eConnect PDU, Vertical - North America*							
Part Number			Input Amperage	Input Plug	Outlets	kW Capacity (UL)	Cabinet Compatibility
Black	Glacier White	Redundancy Pack**					
120 Volt, Single-Phase Input							
EA-5001-C	EA-5001-E	EA-5001-CE	20A	C20 Inlet to NEMA L5-20P	(24) 5-20	1.9 kW	42U & higher
EA-5002-C	EA-5002-E	EA-5002-CE	30A	NEMA L5-30P	(24) 5-20	2.9 kW	42U & higher
208 Volt, Single-Phase Input							
EA-5069-C	EA-5069-E	EA-5069-CE	20A	C20 Inlet to NEMA L6-20P	(18) C13/C15 + (6) C19	3.3 kW	42U & higher
EA-5070-C	EA-5070-E	EA-5070-CE	20A	C20 Inlet to NEMA L6-20P	(24) C13/C15	3.3 kW	42U & higher
EA-5004-C	EA-5004-E	EA-5004-CE	30A	NEMA L6-30P	(24) C13/C15	5 kW	42U & higher
EA-5012-C	EA-5012-E	EA-5012-CE	30A	NEMA L6-30P	(18) C13/C15 + (6) C19	5 kW	42U & higher
120/208 Volt, Three-Phase Input***							
EA-5006-C	EA-5006-E	EA-5006-CE	20A	NEMA L21-20P	(24) C13/C15	5.7 kW	42U & higher
EA-5014-C	EA-5014-E	EA-5014-CE	20A	NEMA L21-20P	(18) C13/C15 + (6) C19	5.7 kW	42U & higher
EA-5025-C	EA-5025-E	EA-5025-CE	20A	NEMA L21-20P	(18) C13/C15 + (6) C19 + (3) 5-20 convenience outlets***	5.7 kW	42U & higher
EA-5007-C	EA-5007-E	EA-5007-CE	30A	NEMA L21-30P	(24) C13/C15	8.6 kW	42U & higher
EA-5015-C	EA-5015-E	EA-5015-CE	30A	NEMA L21-30P	(18) C13/C15 + (6) C19	8.6 kW	42U & higher
EA-5026-C	EA-5026-E	EA-5026-CE	30A	NEMA L21-30P	(18) C13/C15 + (6) C19 + (3) 5-20 convenience outlets***	8.6 kW	42U & higher
EA-5035-C	EA-5035-E	EA-5035-CE	30A	NEMA L21-30P	(36) C13/C15	8.6 kW	42U & higher
208 Volt, Three-Phase Input							
EA-5005-C	EA-5005-E	EA-5005-CE	30A	NEMA L15-30P	(24) C13/C15	8.6 kW	42U & higher
EA-5013-C	EA-5013-E	EA-5013-CE	30A	NEMA L15-30P	(18) C13/C15 + (6) C19	8.6 kW	42U & higher
EA-5034-C	EA-5034-E	EA-5034-CE	30A	NEMA L15-30P	(36) C13/C15	8.6 kW	42U & higher
EA-5016-C	EA-5016-E	EA-5016-CE	50A	CS8365C	(18) C13/C15 + (6) C19	14.4 kW	42U & higher
EA-5027-C	EA-5027-E	EA-5027-CE	50A	CS8365C	(12) C13/C15 + (12) C19	14.4 kW	42U & higher
EA-5136-C	EA-5136-E	EA-5136-CE	50A	CS8365C	(36) C13/C15	14.4 kW	45U & higher
EA-5144-C	EA-5144-E	EA-5144-CE	50A	CS8365C	(24) C13/C15 + (12) C19	14.4 kW	45U & higher
EA-5017-C	EA-5017-E	EA-5017-CE	60A	IEC 60309 60A 3P+E	(18) C13/C15 + (6) C19	17.2 kW	42U & higher
EA-5028-C	EA-5028-E	EA-5028-CE	60A	IEC 60309 60A 3P+E	(12) C13/C15 + (12) C19	17.2 kW	42U & higher
EA-5137-C	EA-5137-E	EA-5137-CE	60A	IEC 60309 60A 3P+E	(36) C13/C15	17.2 kW	45U & higher
EA-5145-C	EA-5145-E	EA-5145-CE	60A	IEC 60309 60A 3P+E	(24) C13/C15 + (12) C19	17.2 kW	45U & higher
240/415 Volt, Three-Phase Input							
EA-5018-C	EA-5018-E	EA-5018-CE	30A	NEMA L22-30P	(18) C13/C15 + (6) C19	17.2 kW	42U & higher
EA-5029-C	EA-5029-E	EA-5029-CE	30A	NEMA L22-30P	(12) C13/C15 + (12) C19	17.2 kW	42U & higher
EA-5038-C	EA-5038-E	EA-5038-CE	30A	NEMA L22-30P	(36) C13/C15	17.2 kW	42U & higher
EA-5046-C	EA-5046-E	EA-5046-CE	30A	NEMA L22-30P	(24) C13/C15 + (12) C19	17.2 kW	42U & higher

Notes: *All vertical PDU's are 2.2" wide

**Redundancy Pack includes 2 PDUs in Black and Glacier White for easy identification of the primary and secondary unit.

***Convenience 5-20 outlets do not provide monitoring or switching capabilities.

ORDERING INFORMATION





















Switched eConnect PDU, Vertical - Worldwide*								
Part Number			Input Amperage	Input Plug	Outlets	kW Capacity Worldwide (CE)	kW Capacity North America (UL)	Cabinet Compatibility
Black	Glacier White	Redundancy Pack**						
220 - 240 Volt, Single-Phase Input								
EA-5008-C	EA-5008-E	EA-5008-CE	16A	C20 Inlet to IEC 60309 16A 1P+N+E	(24) C13/C15	3.8 kW	3.8 kW	42U & higher
EA-5019-C	EA-5019-E	EA-5019-CE	16A	C20 Inlet to IEC 60309 16A 1P+N+E	(18) C13/C15 + (6) C19	3.8 kW	3.8 kW	42U & higher
EA-5009-C	EA-5009-E	EA-5009-CE	32A	IEC 60309 32A 1P+N+E	(24) C13/C15	7.7 kW	6.1 kW	42U & higher
EA-5020-C	EA-5020-E	EA-5020-CE	32A	IEC 60309 32A 1P+N+E	(18) C13/C15 + (6) C19	7.7 kW	6.1 kW	42U & higher
220 - 240/380 - 415 Volt, Three-Phase Input								
EA-5010-C	EA-5010-E	EA-5010-CE	16	IEC 60309 16A 3P+N+E	(24) C13/C15	11.5 kW	11.5 kW	42U & higher
EA-5021-C	EA-5021-E	EA-5021-CE	16	IEC 60309 16A 3P+N+E	(18) C13/C15 + (6) C19	11.5 kW	11.5 kW	42U & higher
EA-5030-C	EA-5030-E	EA-5030-CE	16	IEC 60309 16A 3P+N+E	(12) C13/C15 + (12) C19	11.5 kW	11.5 kW	42U & higher
EA-5039-C	EA-5039-E	EA-5039-CE	16	IEC 60309 16A 3P+N+E	(36) C13/C15	11.5 kW	11.5 kW	42U & higher
EA-5047-C	EA-5047-E	EA-5047-CE	16/20A	IEC 60309 16/20A 3P+N+E	(24) C13/C15 + (12) C19	11.5 kW	11.5 kW	42U & higher
EA-5022-C	EA-5022-E	EA-5022-CE	32A	IEC 60309 32A 3P+N+E	(18) C13/C15 + (6) C19	23 kW	18.4 kW	42U & higher
EA-5031-C	EA-5031-E	EA-5031-CE	32A	IEC 60309 32A 3P+N+E	(12) C13/C15 + (12) C19	23 kW	18.4 kW	42U & higher
EA-5040-C	EA-5040-E	EA-5040-CE	32A	IEC 60309 32A 3P+N+E	(36) C13/C15	23 kW	18.4 kW	42U & higher
EA-5048-C	EA-5048-E	EA-5048-CE	32A	IEC 60309 32A 3P+N+E	(24) C13/C15 + (12) C19	23 kW	18.4 kW	42U & higher

Notes:




Notes: *All vertical PDU's are 2.2" wide

**Redundancy Pack includes 2 PDUs in Black and Glacier White for easy identification of the primary and secondary unit.

PLUG/INLET TABLE

Single-Phase									
	NEMA L5-20P 110-125 VAC/20A	NEMA L5-30P 110-125 VAC/30A	NEMA L6-20P 200-240 VAC/20A	NEMA L6-30P 200-240 VAC/30A	IEC C20 200-240VAC/20A				
									
	IEC 16A 1P+N+E 200-240VAC/16A	IEC 32A 1P+N+E 200-240VAC/32A							
Three-Phase									
	NEMA L15-20P 208 VAC/20A	NEMA L15-30P 208 VAC/30A	NEMA L21-20P 120/208 VAC/20A	NEMA L21-30P 120/208 VAC/30A	NEMA L22-20P 240/415 VAC, 20A	NEMA L22-30P 380/415 VAC/30A	50A CS8365 208 VAC/50A	IEC 60A 3P+E 208V/60A	IEC 100A 3P+E 208V/100A
									
	IEC 16A 3P+N+E 240/415VAC/16A	IEC 32A 3P+N+E 240/415VAC/32A	IEC 60A 3P+N+E 240/415VAC/60A	IEC 100A 3P+N+E 240/415VAC/100A					

POWER RECEPTACLE/OUTLET TABLE

Receptacles/ Outlets			
	NEMA 5-20R 120 VAC/20A	IEC C13 100-240V/10A	IEC C19 200-240 VAC/16A

ACCESSORIES



Extended Limited Warranties

Extended Limited Warranties on CPI-Branded Electronic products, available for two additional years beyond the expiration of the Original Warranty Period (3 years).

Contact CPI Customer Service, or visit chatsworth.com/warranty for more information.

Part Number	Description
L1-2YEXTWAR-ELECTRONICS-C	2-Year Warranty Extension for PDUs with MSRP up to \$1700
L2-2YEXTWAR-ELECTRONICS-C	2-Year Warranty Extension for PDUs with MSRP \$1701 - \$3400
L3-2YEXTWAR-ELECTRONICS-C	2-Year Warranty Extension for PDUs with MSRP > \$3400



14676-001



14812-001

Field-Replaceable Controller Module


Field-replaceable controller module for eConnect® Power Distribution Unit (PDU). Compatible with eConnect Monitored, Monitored Pro, Switched or Switched Pro eConnect PDUs. Allows replacement of controller module while maintaining power to critical loads. Ability to use an SD-card to transfer PDU configuration. Available in two options, to match to either a Vertical or Horizontal eConnect PDU form factor. Both controller modules include connections for ethernet, Secure Array IP Consolidation, temperature and humidity sensors, RFID Electronic Locks and serial/console interface. Controller module for Vertical eConnect PDUs also includes a local display.

Part Number	Description	Shipping Weight lb (kg)
14676-001	eConnect Controller 4 (MCM4) for Vertical eConnect PDUs	1 (0.5)
14812-001	eConnect Controller 4H (MCM4) for Horizontal eConnect PDUs	1 (0.5)

Note: Compatible with PDU P/Ns: EA-3xxx, EA-4xxx, EA-5xxx, EA-6xxx.

ACCESSORIES

POWER MANAGEMENT, ENVIRONMENTAL MONITORING AND PHYSICAL SECURITY INTEGRATION



eConnect® Sensor Array
Integrates complete cabinet-level management under a single network connection, one user interface, and one user database— dramatically reducing deployment time and cost. The array connects to the eConnect auxiliary (AUX) ports and can receive redundant power from a second eConnect PDU. Environmental monitoring options include temperature and humidity sensing, leak detection, cabinet door status, cabinet status light, and a cabinet work light triggered by door-status sensors.



eConnect® RFID Electronic Lock Kit
Integrated cabinet access control simplifies electronic lock deployment and provides IT organizations with a complete audit trail of all cabinet access attempts. Fully compatible with DCIM software.



Power IQ® (PIQ) for eConnect
Power IQ® is a data center energy, power, environmental and access control monitoring software that provides out-of-the-box support for eConnect PDUs, Networked Control Module as well as devices from many other manufacturers.

Part Number	Description
15013-701	eConnect® Sensor Hub – Temp & Humidity
14980-701	eConnect® Temp & Humidity Sensor – For use with Sensor Hub – Temp & Humidity
15014-701	eConnect® Sensor Hub – Door, Lights & Access
14978-701	eConnect® Door Control Sensor – For use with Sensor Hub – Door, Lights & Access for ZetaFrame cabinets
15016-001	eConnect® Cabinet Status Lights – For use with Sensor Hub – Door, Lights & Access
14994-701	eConnect® Cabinet Work Light – For use with Sensor Hub – Door, Lights & Access
15015-701	eConnect® Sensor Hub – Leak Detection
14983-701	eConnect® Leak Detector Spot Sensor (Water Only) – For use with Sensor Hub – Leak Detection
14995-701	eConnect® Leak Detector Spot Sensor (Dielectric) – For use with Sensor Hub – Leak Detection
15024-001	eConnect® Leak Detector Rope Sensor (Water Only) – For use with Sensor Hub – Leak Detection
Part Number	Description
15026-001	eConnect® Sensor Hub – Access
15027-001	eConnect RFID Electronic Lock Kit - Includes Sensor Hub Access, Front & Rear Door Locks & RFID readers and 3 Door contact sensors

Power IQ for eConnect Software and License, With 1-Year Maintenance Plan			
Part Number	Number of Licenses	Part Number	Number of Licenses
36603-001	Up to 10 Devices	36603-020	Up to 200 Devices
36603-002	Up to 20 Devices	36603-030	Up to 300 Devices
36603-005	Up to 50 Devices	36603-040	Up to 400 Devices
36603-010	Up to 100 Devices	36603-050	Up to 500 Devices



Order locks and PDUs preinstalled into your cabinet. Add power. Make it easy.

chatsworth.com
techsupport@chatsworth.com
800-834-4969

Simplify ordering, shipping and installation by requesting eConnect PDUs and RFID Electronic Lock Kit to be installed in CPI's ZetaFrame® Cabinets before they leave the factory. Request Redundancy Pack for easy identification of primary and secondary units.



While every effort has been made to ensure the accuracy of all information, CPI does not accept liability for any errors or omissions and reserves the right to change information and descriptions of listed services and products.

©2026 Chatsworth Products, Inc. All rights reserved. Chatsworth Products, Click-Nut, CPI, CPI Passive Cooling, CUBE-iT, Secure Array, eConnect, Evolution, GlobalFrame, MegaFrame, QuadraRack, RMR, Saf-T-Grip, SeismicFrame, SlimFrame, TeraFrame, Motive, Velocity, Oberon, Wi-Tile and ZetaFrame are federally registered trademarks of Chatsworth Products. EuroFrame, H-Plane, Hi-Bar, In-Plane, M-Frame, NetPoint, Simply Efficient, Skybar, Elevate, and VersaEdge Wall-Mount Cabinet are trademarks of Chatsworth Products and Oberon, a division of Chatsworth Products. All other trademarks belong to their respective companies. Rev. 02/26 MKT60020-722