




CHATSWORTH
PRODUCTS

RMR
Industrial Enclosures

RMR® Industrial Enclosure Systems and Solutions

Chatsworth Products (CPI) is a global manufacturer of products and solutions that power and protect your technology investment with expert consultation and product customization for a variety of applications. That includes NEMA-rated RMR® Industrial Enclosures and solutions that can withstand the elements to provide protection in virtually any environment



CPI Product Designer

- Wide range of high-quality, standard solutions
- Fast, easy configuration and ordering
- Kitting of accessories to simplify ordering
- Preinstallation of accessories to save you time
- Modified standard enclosures to match specific Human Machine Interface (HMI) requirements
- Competitive lead times to match your schedule

chatsworth.com/product-designer

RMR Free-Standing Enclosures



- NEMA Type 4, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Available in stainless steel with brushed finish for corrosive environments
- Easy-to-use side channels for mounting
- Continuous foam gasket seal
- Wide range of sizes available
- Single- and double-door options
- 3-point latch with choice of lock
- Optional adjustable-depth mounting plate

RMR Wall-Mount Enclosures



- NEMA Type 4, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Continuous foam gasket seal
- Wide range of sizes available
- Single- and double-door options
- 3-point or 1/4-turn latch with choice of lock
- Optional rear mounting plate
- Available with solid metal or tempered glass door
- Disconnect Enclosures with standard cutout on the right flange are also available

RMR Swing Wall-Mount Enclosures



- UL® Listed Industrial Control Panel Enclosure, Type 12 and IP 55 ratings
- For indoor use, protects against the ingress of dust and dripping noncorrosive liquids
- Swing-out or fixed styles
- Continuous foam gasket seal
- Wide range of sizes available
- Solid or tempered glass door option
- 19" EIA mounting rails or adjustable mounting plate
- Optional cable and thermal management accessories

RMR Modular Enclosures



Shown in painted Hammer Gray RAL7035 finish.

- UL Listed Industrial Control Panel Enclosure, Type 12 and IP 55 ratings
- For indoor use, protects against the ingress of dust and dripping noncorrosive liquids
- Continuous foam gasket seal
- High-strength, roll-formed steel frame
- Removable, bolt-on top, side, bottom and rear panels
- Wide range of sizes available
- 19" EIA mounting rails or adjustable mounting plate
- Optional cable and thermal management accessories

RMR Floor-Mount Enclosures



Shown in painted Gray ANSI 61 finish.

- NEMA Type 4, 12, 3, 3R, 5, 2 and 1
- For indoor and outdoor use
- Floor stands provide additional clearance and easy access to bottom of the enclosure
- Available in stainless steel with brushed finish for corrosive environments
- Continuous foam gasket seal
- Solid double door
- Three lock styles: keyed, double bit and square
- Wide range of sizes available

Thermal Management Accessories



- NEMA Type 12 Indoor Cooling Units; 900-1300 BTU/hr; 3000-4000 BTU/hr; 5000-7000 BTU/hr
- Closed-loop cooling eliminates the risk of contaminants entering the enclosure
- Cooling unit uses environmentally friendly HFC-free R134a refrigerant
- Forced convection with Filter Fans
- Filter Fans feature a high performance seal and 300% longer service life
- NEMA Type 4 Cooling Units also available.

Power, Environmental Monitoring & Software



- eConnect® Power Distribution Units (PDUs) – 6 progressive functionality levels allowing local metering, remote monitoring and switching, integrated environmental monitoring at the device level with industry-leading temperature rating of 149° F supporting power densities up to 34.5 kW/cabinet
- Power strips – 120V, 15A and 20A economical power distribution solutions available with integrated supplemental surge protection and local metering
- Uninterruptible power supplies (UPS) – Double conversion online models up to 10kVA include Lithium-Ion based solutions with 6 years of warranty, providing highest levels of protection for industrial environments
- Power IQ software – Centralized vendor neutral management software solution for distributed and centralized environments



Accessories for RMR Industrial Enclosures



- Roxtec grommets are rated IP 55 and seal cable openings
- Polyvent Protective Vent Kit provides ventilation and equalizes air pressure; Use to meet NEMA Type 3R requirements
- Threaded Drain Plug Kit drains accumulated or condensed water out the bottom of the enclosure
- LED Light Kit provides additional lighting; 100-240 Volts
- Drip Shield Assembly provides additional protection against ice and rain; Use to meet NEMA Type 3R requirements

Oberon NetPoint Bollards



- Unique solutions to secure, protect, and conceal wireless access points, antennas, and associated cabling
- NEMA Type 3R to protect from weather, spilling liquids, and tampering
- Rugged plastic material is virtually transparent to wireless signal
- Bollards are available in different heights and finishes
- Access points are not included

chatsworth.com
techsupport@chatsworth.com
800-834-4969