

CUBE-iT™ Wall-Mount Cabinet

Standard Wall-Mount Cabinet

ThinLine II Wall-Mount Cabinet

Standard Swing Gate Wall Rack

EasySwing Wall-Mount Rack

Fixed Wall-Mount Rack

Application:
Designed to secure information and communications equipment (ICT) in a telecommunications room or any public spaces where floor space is limited.

Key Features:

- Easy access to the front and rear of equipment with a three-part, swing-out body; EIA-310-D compliant
- Attractive design with multiple door styles and colors make it suitable for public areas
- Removable top and bottom panels with a rectangular knockout provide retrofit capability
- Increased security with access to the rear only through the keyed front door
- Variety of cable management options and accessories such as low-decibel dual-fan kit

Heights:

- 24" (610 mm), 12U
- 36" (910 mm), 19U
- 48" (1220 mm), 26U

Depths:

- 24" (610 mm), 12U
- 36" (910 mm), 19U
- 48" (1220 mm), 26U

Load Bearing:

- Supports 300 lb (136 kg)

Construction:

- Riveted and bolted; powder coat finish

Application:
Designed to provide secure storage for ICT equipment in remote locations.

Key Features:

- Ships partially assembled in a compact, flat pack and is easy to maneuver
- Cabinet chassis is vented on top and bottom; EIA-310-D compliant
- Simplified assembly process by using a simple slot-and-hook design

Heights:

- 14.8" (375 mm), 6U
- 20.0" (508 mm), 9U
- 25.2" (640 mm), 12U

Depths:

- 19.7" (500 mm)
- 23.6" (600 mm)

Load Bearing:

- 6U, 60 lb (27.2 kg)
- 9U, 90 lb (40.8 kg)
- 12U, 130 lb (58.9 kg)

Construction:

- Slot-and-hook/bolted frame; mounting rails bolt to frame

Application:
Space-saving with minimal intrusion into the room – perfect for high-traffic, tight areas.

Key Features:

- Individual rails can be easily rotated for horizontal or vertical mounting and then bolted into place making patch panel punchdown easier.
- Removable top panel provides direct access to equipment without disturbing other devices
- Ships fully assembled with mounting hardware
- Multiple sets of knockouts allow flexibility in cable organization
- Cabinet includes a junction box 2" x 4" (50 mm x 100 mm) to hold optional surge-suppression duplex outlet
- EIA-310-D compliant

Heights:

- 26" (660 mm)
- 36" (910 mm)

Depths:

- 5" (130 mm), 2U
- 8.5" (216 mm), 4U
- 12" (300 mm), 6U

Load Bearing:

- Static load, 100 lb (45.4 kg)

Construction:

- Steel

Application:
Provides easy access to the rear of equipment, making it the ideal choice for supporting patch panels and switches.

Key Features:

- Dual hinges open to the right or left, stopping at 90°
- Supports single- and double-sided shelves
- Ships partially assembled with installation hardware
- EIA-310-D compliant; rack-mount spaces are marked and numbered

Heights:

- 29.1" (739 mm), 12U
- 43.1" (1095 mm), 20U
- 53.6" (1361 mm), 26U
- 78.1" (1984 mm), 40U

Depths:

- 12.2" (310 mm)
- 18.2" (462 mm)
- 25.2" (640 mm)

Load Bearing:

- Supports 100 lb (45.4 kg) in open position; can increase to 150 lb (45.4 kg) with optional kit

Construction:

- Steel and Aluminum

Application:
Cost-effective 19" EIA swing gate rack for mounting network, ICT and security equipment in a telecommunications or equipment room where floor space is limited.

Key Features:

- Opens 180° to right or left, locking latch pin secures gate in the closed position
- Ships fully assembled and flat; simply unfold and mount to wall
- Keyhole wall mounting holes with mounting template included on carton
- EIA-310-D compliant

Heights:

- 24.5" (622 mm), 11U
- 38.5" (978 mm), 19U
- 51.5" (1308 mm), 26U

Depths:

- 8.0" (204 mm)
- 12.0" (305 mm)
- 18.0" (457 mm)
- 25.0" (635 mm)

Load Bearing:

- 85 lb (38.6 kg)

Construction:

- Welded and bolted steel

Application:
Space-saving, sturdy platform for wall-mounting equipment.

Key Features:

- EIA-310-D compliant; rack-mount spaces are marked and numbered
- Supports single- and double-sided shelves
- Tapped #12-24 roll-formed threads; includes equipment mounting screws

Heights:

- 27.4" (696 mm), 12U
- 41.4" (1052 mm), 20U
- 76.4" (1361 mm), 40U

Depths:


- 6.6" (168 mm)
- 12.6" (320 mm)
- 18.6" (472 mm)

Load Bearing:

- Supports 200 lb (90.7 kg) of equipment; securely mounts to wall using eight leg mounting holes

Construction:

- Aluminum



CUBE-iT™ Wall-Mount Cabinet	Standard Wall-Mount Cabinet	ThinLine II Wall-Mount Cabinet	Standard Swing Gate Wall Rack	EasySwing Wall-Mount Rack	Fixed Wall-Mount Rack
-----------------------------	-----------------------------	--------------------------------	-------------------------------	---------------------------	-----------------------

Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)			
11900-X24	24"H x 24"W x 24"D; 12U (610 mm x 610 mm x 610 mm) Tempered Glass Door	101 (45.8)	25500-706	19"W x 14.8"H x 13.75"D (600 mm x 375 mm x 349 mm) 6U, Solid Metal Door	48 (21.8)	13050-X11	26"H x 26"W x 5"D, 2U (660 mm x 660 mm x 130 mm), Black finish	47 (21.3)	11790-X18	29.1"H x 19"W x 17"D, 12U (739 mm x 600 mm x 430 mm)	24 (10.9)	13602-X12	24.5"H x 19"W x 10.5"D 11U, (622 mm x 600 mm x 266 mm)	24 (10.9)	11960-X06	27.4"H x 19"W x 6"D, 12U (696 mm x 600 mm x 150 mm)	9 (4.1)
11840-X24	24"H x 24"W x 24"D; 12U (610 mm x 610 mm x 610 mm) Solid Metal Door	101 (45.8)	25501-709	19"W x 20.0"H x 13.75"D (600 mm x 508 mm x 349 mm) 9U, Tempered Glass Door	54 (24.5)	13050-X12	26"H x 26"W x 8.5"D, 4U (660 mm x 660 mm x 216 mm) Black finish	54 (24.5)	11791-X18	43.1"H x 19"W x 17"D, 20U (1095 mm x 600 mm x 430 mm)	26 (11.8)	13604-X12	38.5"H x 19"W x 10.5"D 19U, (978 mm x 600 mm x 266 mm)	24 (10.9)	11961-X06	41.4"H x 19"W x 6"D, 20U (1052 mm x 600 mm x 150 mm)	10 (4.5)
11900-X36	36"H x 24"W x 24"D; 19U (910 mm x 610 mm x 610 mm) Tempered Glass Door	128 (58.2)	25502-712	19"W x 25.2"H x 13.75"D (600 mm x 640 mm x 349 mm) 12U, Perforated Metal Door	58 (26.3)	13050-X13	26"H x 26"W x 12"D, 6U (660 mm x 660 mm x 300 mm) Black finish	60 (27.2)	11792-X18	78.1"H x 19"W x 17"D, 40U (1984 mm x 600 mm x 430 mm)	33 (15.0)	13608-X12	51.5"H x 19"W x 10.5"D 26U, (1308 mm x 600 mm x 266 mm)	24 (10.9)	11962-X06	76.4"H x 19"W x 6"D, 40U (1941 mm x 600 mm x 150 mm)	15 (6.8)
12419-X36	36"H x 24"W x 30"D; 19U (910 mm x 610 mm x 760 mm) Tempered Glass Door	142 (64.4)	25503-706	19"W x 14.8"H x 17.7"D (600 mm x 375 mm x 449 mm) 6U, Solid Metal Door	53 (24.0)	13050-X21	36"H x 26"W x 5"D, 2U (910 mm x 660 mm x 130 mm) Black finish	60 (27.2)	11790-X25	29.1"H x 19"W x 24"D, 12U (739 mm x 600 mm x 610 mm)	42 (19.1)	<i>X=Color; 1=Gray, 2=Computer Beige, and 7=Black. Other sizes and styles available.</i>	11960-X12	27.4"H x 19"W x 12"D, 12U (696 mm x 600 mm x 300 mm)	12 (5.4)		
12419-X48	48"H x 24"W x 30"D; 26U (1220 mm x 610 mm x 760 mm) Tempered Glass Door	171 (77.6)	25504-709	19"W x 20.0"H x 17.7"D (600 mm x 508 mm x 449 mm) 9U, Tempered Glass Door	54 (24.5)	13050-X22	36"H x 26"W x 8.5"D, 4U (910 mm x 660 mm x 216 mm) Black finish	54 (24.5)	11791-X25	43.1"H x 19"W x 24"D, 20U (1095 mm x 600 mm x 610 mm)	46 (20.9)		11961-X12	41.4"H x 19"W x 12"D, 20U (1052 mm x 600 mm x 300 mm)	13 (5.9)		
11996-X36	36"H x 24"W x 30"D; 19U (910 mm x 610 mm x 760 mm) Solid Metal Door	142 (64.4)	25505-712	19"W x 25.2"H x 17.7"D (600 mm x 640 mm x 449 mm) 12U, Perforated Metal Door	58 (26.3)	13050-X23	26"H x 26"W x 12"D, 6U (910 mm x 660 mm x 300 mm) Black finish	60 (27.2)	11792-X25	78.1"H x 19"W x 24"D, 40U (1984 mm x 600 mm x 610 mm)	60 (27.2)	<i>X=Color; 1=Gray, 2=Computer Beige, 7=Black and E=Glacier White. Other sizes and styles available.</i>	11962-X12	76.4"H x 19"W x 12"D, 40U (1941 mm x 600 mm x 300 mm)	16 (7.3)		
<i>X=Color; E=Glacier White; 7=Black. Other sizes and styles available.</i>			<i>X=Color; E=Glacier White; 7=Black. Other sizes and styles available.</i>			<i>X=Color; 1=Gray, 2=Computer Beige, and 7=Black. Other sizes and styles available.</i>							<i>X=Color; E=Glacier White; 7=Black. Other sizes and styles available.</i>				
Key Accessories			Key Accessories			Key Accessories			Key Accessories			Key Accessories					
Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)	Part No.	Description	Wt. lb (kg)			
40972-001	Standard Fan and Filter Kit	2 (0.9)	25515-001	Fan Kit, 100 CFM	5 (2.3)	12955-719	Fiber Slack Mgr Panel	2 (0.9)	12795-X01	Heavy-Duty Swing Gate Kit (2) Brackets	4 (1.8)	12858-001	Corner Cushions, Set of 4	1 (0.5)			
40975-001	Low-Decibel Dual-Fan Kit	4 (1.8)	25514-706	Ring Cble Mgr for 6U	2 (0.9)	12934-001	Surge-Suppressed Duplex Receptacle	2 (0.9)									
40970-704	Vertical Cabling Section, 4U	5 (2.5)	25512-706	Cable Lashing Brkt, 6U	2 (0.9)	13051-001	Intelligent Fan Kit	2 (0.9)									
25190-000	Cable Port Brush Kit	2 (0.9)	25513-706	Finger Cable Mgr for 6U	2 (0.9)		115 VAC, 60 Hz	2 (0.9)									
11837-701	Horizontal Wire Mgmt	4 (1.8)	25521-701	Rear Brkt Cable Mgr	3 (1.4)												
12803-701	LED Light Kit, 4W, 120V	2 (0.9)															